

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563796

Luminaire Tested: **SQ4-PP3-150U-075D-935-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563796  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-150U-075D-935-1D-UNV-STD-W-8  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 15464.5 lumens  
Efficiency: N/A  
Efficacy: 118.0 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 131.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563796  
CATALOG NUMBER: SQ4-PP3-150U-075D-935-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P563796

CATALOG NUMBER: SQ4-PP3-150U-075D-935-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	32				
1	94	90	86	83	84	81	78	75	65	62	60	49	48	47	35	35	34	27				
2	86	79	73	68	77	71	66	62	57	53	50	43	41	39	31	30	29	23				
3	78	69	62	56	70	62	56	52	50	46	42	38	36	33	28	26	25	20				
4	71	61	53	48	64	55	49	44	44	40	36	34	31	28	25	23	21	17				
5	65	54	46	41	59	49	42	37	40	35	31	31	27	25	22	20	18	15				
6	60	49	41	35	54	44	37	32	36	31	27	28	24	21	20	18	16	13				
7	56	44	36	31	50	40	33	28	32	27	24	25	22	19	19	16	14	12				
8	51	40	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13	10				
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	13	12	9				
10	45	33	26	21	40	30	24	20	25	20	17	19	16	14	14	12	10	8				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8999	8999	8999
5°	9065	9010	8978
10°	9050	8986	8946
15°	8990	8941	8892
20°	8930	8880	8813
25°	8824	8763	8676
30°	8661	8615	8506
35°	8434	8376	8271
40°	8165	8113	8020
45°	7942	7885	7808
50°	7656	7607	7533
55°	7260	7164	7109
60°	6610	6420	6388
65°	5822	5580	5561
70°	5027	4819	4819
75°	4328	4267	4205
80°	3815	3860	3770
85°	2985	3255	3255



TEST NUMBER: P563796

CATALOG NUMBER: SQ4-PP3-150U-075D-935-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	184.5	1.2
10°-20°	526.7	3.4
20°-30°	788.9	5.1
30°-40°	925.4	6.0
40°-50°	928.3	6.0
50°-60°	791.9	5.1
60°-70°	516.4	3.3
70°-80°	259.1	1.7
80°-90°	75.1	0.5
90°-100°	754.6	4.9
100°-110°	2040.2	13.2
110°-120°	2145.0	13.9
120°-130°	1742.3	11.3
130°-140°	1366.7	8.8
140°-150°	1049.0	6.8
150°-160°	754.4	4.9
160°-170°	460.8	3.0
170°-180°	155.4	1.0
0°-30°	1500.1	9.7
0°-40°	2425.5	15.7
0°-60°	4145.6	26.8
0°-90°	4996.2	32.3
90°-120°	4939.8	31.9
90°-150°	9097.7	58.8
90°-180°	10468.0	67.7
0°-180°	15464.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1951	1951	1951	1951	1951	
5°	1958	1939	1946	1939	1939	186
15°	1882	1864	1872	1865	1862	531
25°	1734	1714	1722	1706	1705	797
35°	1498	1483	1487	1470	1469	936
45°	1217	1209	1209	1197	1197	937
55°	903	899	891	886	884	802
65°	533	523	511	508	510	532
75°	243	243	239	238	236	263
85°	56	61	62	62	62	66
90°	4	10	23	24	23	10
95°	117	411	1255	649	386	123
105°	379	586	2263	3339	3202	399
115°	668	816	1877	3634	4102	659
125°	914	1047	1692	2855	3354	815
135°	1096	1226	1646	2305	2609	847
145°	1274	1370	1624	1973	2124	797
155°	1438	1495	1610	1770	1828	663
165°	1566	1581	1617	1680	1688	441
175°	1625	1624	1618	1639	1636	154
180°	1624	1624	1624	1624	1624	

TEST NUMBER: P563796

CATALOG NUMBER: SQ4-PP3-150U-075D-935-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1950.7	1950.7	1950.7	1950.7	1950.7
2.5°	1963.1	1947.0	1950.7	1947.8	1939.8
5°	1957.6	1939.2	1945.6	1938.8	1938.8
7.5°	1944.3	1924.2	1930.6	1923.7	1923.4
10°	1931.9	1911.9	1918.3	1911.4	1909.7
12.5°	1914.2	1894.1	1901.9	1893.6	1893.3
15°	1882.4	1864.0	1872.1	1865.2	1861.8
17.5°	1846.5	1826.4	1836.2	1826.6	1825.3
20°	1819.1	1799.0	1808.8	1795.2	1795.2
22.5°	1786.3	1766.2	1777.4	1759.6	1759.6
25°	1733.6	1713.6	1721.7	1706.2	1704.6
27.5°	1671.0	1651.3	1659.8	1642.3	1642.0
30°	1625.9	1607.5	1617.4	1598.5	1596.8
32.5°	1576.7	1559.6	1566.8	1547.9	1546.2
35°	1497.7	1482.6	1487.4	1470.3	1468.6
37.5°	1414.6	1399.2	1404.7	1390.0	1389.3
40°	1355.8	1345.7	1347.2	1335.2	1331.8
42.5°	1301.1	1289.7	1291.2	1279.2	1278.5
45°	1217.3	1208.9	1208.7	1196.8	1196.8
47.5°	1128.4	1122.0	1120.2	1110.3	1109.9
50°	1066.8	1061.8	1060.0	1051.4	1049.7
52.5°	1002.6	1000.2	994.4	987.2	986.8
55°	902.7	899.4	890.7	885.6	883.9
57.5°	794.3	787.6	777.9	770.4	771.8
60°	716.4	709.7	695.8	692.4	692.4
62.5°	641.1	633.1	619.2	614.5	617.2
65°	533.4	523.4	511.2	507.8	509.5
67.5°	435.6	426.6	413.4	413.4	412.0
70°	372.7	367.7	357.3	357.3	357.3
72.5°	316.6	314.3	306.7	306.7	305.3
75°	242.8	242.8	239.4	237.6	235.9
77.5°	181.9	182.6	180.9	179.1	176.1
80°	143.6	147.0	145.3	143.6	141.9
82.5°	108.1	111.4	111.1	108.0	107.7
85°	56.4	61.4	61.5	61.5	61.5
87.5°	15.7	22.5	26.4	26.8	27.8
90°	3.5	10.3	22.7	24.4	22.7
92.5°	49.6	180.9	356.9	154.9	112.2
95°	117.1	411.0	1254.9	649.4	386.3
97.5°	188.1	471.4	1956.1	1618.8	1188.8
100°	241.2	495.8	2174.2	2267.5	1833.4
102.5°	290.1	529.7	2251.1	2759.3	2434.6
105°	379.3	586.0	2263.3	3338.6	3201.9
107.5°	461.8	650.4	2164.4	3700.0	3745.4
110°	526.1	697.0	2076.3	3797.0	3990.1



TEST NUMBER: P563796

CATALOG NUMBER: SQ4-PP3-150U-075D-935-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	583.4	743.4	1995.2	3777.6	4102.0
115°	667.6	816.3	1877.1	3633.7	4102.0
117.5°	750.1	889.6	1799.1	3413.9	3944.7
120°	800.5	937.2	1753.0	3256.1	3797.9
122.5°	848.0	982.0	1725.0	3087.0	3632.9
125°	914.1	1047.4	1691.8	2854.9	3353.9
127.5°	974.9	1105.8	1672.2	2665.5	3104.4
130°	1008.5	1143.5	1663.9	2548.5	2945.0
132.5°	1043.4	1177.0	1655.5	2442.9	2807.9
135°	1095.8	1225.7	1646.4	2305.2	2609.4
137.5°	1148.6	1271.3	1638.7	2193.5	2441.3
140°	1185.0	1299.5	1635.9	2121.5	2342.0
142.5°	1219.9	1327.6	1630.3	2056.6	2249.7
145°	1274.1	1369.8	1623.7	1973.1	2123.5
147.5°	1323.4	1408.2	1616.0	1897.5	2013.1
150°	1359.7	1434.9	1613.2	1856.5	1948.7
152.5°	1393.3	1458.9	1611.8	1818.3	1894.2
155°	1438.4	1494.8	1609.7	1770.0	1828.1
157.5°	1485.2	1524.5	1610.0	1736.4	1774.7
160°	1511.8	1544.3	1611.4	1715.2	1742.5
162.5°	1532.8	1559.8	1612.8	1698.2	1718.7
165°	1566.0	1581.4	1616.7	1679.8	1688.3
167.5°	1588.7	1599.3	1617.0	1664.0	1668.1
170°	1602.7	1607.8	1618.4	1656.9	1656.9
172.5°	1613.9	1614.9	1618.4	1648.4	1647.1
175°	1625.4	1623.7	1618.4	1639.3	1635.9
177.5°	1629.3	1625.2	1618.1	1632.0	1627.9
180°	1623.7	1623.7	1623.7	1623.7	1623.7

(END OF REPORT)