

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P518988

Luminaire Tested: **SQ4-WB-025U-050D-935-1D-UNV-STD-W-4**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P518988
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-025U-050D-935-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2306.9 lumens
Efficiency: N/A
Efficacy: 104.4 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 22.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P518988
CATALOG NUMBER: SQ4-WB-025U-050D-935-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P518988

CATALOG NUMBER: SQ4-WB-025U-050D-935-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69	64		
1	102	98	95	92	96	93	90	87	82	80	78	72	70	69	63	62	61	56		
2	94	88	82	78	89	83	78	74	74	70	67	65	62	60	57	55	54	50		
3	87	79	72	67	82	74	68	64	66	62	58	59	56	53	52	50	47	44		
4	81	71	63	58	76	67	61	56	60	55	51	54	50	47	48	45	42	39		
5	75	64	56	51	70	61	54	49	55	49	45	49	45	41	44	41	38	35		
6	69	58	51	45	65	55	48	44	50	44	40	45	41	37	40	37	34	32		
7	65	53	46	40	61	51	44	39	46	40	36	42	37	34	37	34	31	29		
8	60	49	41	36	57	47	40	35	42	37	33	38	34	31	35	31	28	26		
9	57	45	38	33	53	43	37	32	39	34	30	36	31	28	32	29	26	24		
10	53	42	35	30	50	40	34	29	37	31	28	33	29	26	30	27	24	22		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9288	9288	9288
5°	9173	9139	9193
10°	8666	8745	8947
15°	8000	8186	8553
20°	7265	7538	8036
25°	6516	6871	7487
30°	5826	6207	6917
35°	5094	5463	6244
40°	4288	4628	5405
45°	3539	3844	4513
50°	2954	3221	3759
55°	2508	2763	3104
60°	2144	2397	2478
65°	1707	2015	1600
70°	1513	1573	977
75°	1401	1276	599
80°	1291	1174	515
85°	1164	1080	423



TEST NUMBER: P518988

CATALOG NUMBER: SQ4-WB-025U-050D-935-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.3	4.0
10°-20°	240.2	10.4
20°-30°	311.1	13.5
30°-40°	304.6	13.2
40°-50°	233.2	10.1
50°-60°	155.4	6.7
60°-70°	84.8	3.7
70°-80°	35.3	1.5
80°-90°	10.7	0.5
90°-100°	63.1	2.7
100°-110°	165.9	7.2
110°-120°	172.0	7.5
120°-130°	138.0	6.0
130°-140°	108.3	4.7
140°-150°	83.1	3.6
150°-160°	59.9	2.6
160°-170°	36.6	1.6
170°-180°	12.4	0.5
0°-30°	643.6	27.9
0°-40°	948.3	41.1
0°-60°	1336.8	57.9
0°-90°	1467.7	63.6
90°-120°	401.1	17.4
90°-150°	730.4	31.7
90°-180°	839.0	36.4
0°-180°	2306.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1007	1007	1007	1007	1007	
5°	990	980	987	989	993	92
15°	838	834	857	880	895	234
25°	640	642	675	704	736	294
35°	452	454	485	518	554	281
45°	271	276	295	317	346	211
55°	156	162	172	178	193	141
65°	78	85	92	81	73	81
75°	39	39	36	25	17	42
85°	11	11	10	7	4	12
90°	1	2	7	3	3	1
95°	8	33	109	56	38	9
105°	30	45	183	278	260	32
115°	53	64	147	293	334	52
125°	74	83	134	226	266	66
135°	88	97	130	182	207	68
145°	102	109	128	156	168	64
155°	115	119	128	140	144	53
165°	124	126	128	133	134	35
175°	130	130	129	130	130	12
180°	130	130	130	130	130	

TEST NUMBER: P518988

CATALOG NUMBER: SQ4-WB-025U-050D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1006.7	1006.7	1006.7	1006.7	1006.7
2.5°	1009.2	1000.2	1002.5	1002.4	999.6
5°	990.4	980.4	986.8	989.1	992.6
7.5°	953.6	946.1	957.8	966.4	973.4
10°	925.0	918.5	933.4	946.0	955.0
12.5°	891.8	886.3	904.8	921.6	933.5
15°	837.5	834.5	857.0	880.3	895.4
17.5°	779.5	778.0	803.8	831.0	850.3
20°	739.9	739.5	767.7	796.1	818.5
22.5°	700.0	700.9	730.6	760.1	785.7
25°	640.1	641.8	675.0	704.4	735.5
27.5°	584.7	585.5	619.7	650.8	684.0
30°	546.9	549.0	582.6	614.8	649.3
32.5°	509.1	511.6	544.5	577.7	612.9
35°	452.3	454.5	485.0	517.7	554.4
37.5°	393.8	396.8	423.9	454.7	490.9
40°	356.0	360.4	384.3	413.4	448.8
42.5°	319.6	325.0	347.2	374.8	406.7
45°	271.2	276.4	294.6	316.9	345.9
47.5°	229.5	235.5	249.5	268.7	293.4
50°	205.8	211.5	224.4	238.6	261.9
52.5°	185.0	190.6	202.1	213.1	233.0
55°	155.9	162.4	171.8	178.4	193.0
57.5°	132.1	138.3	145.8	148.7	157.6
60°	116.2	123.1	129.9	129.5	134.3
62.5°	101.7	107.6	114.3	109.6	109.9
65°	78.2	84.7	92.3	80.7	73.3
67.5°	63.2	64.5	72.4	56.3	47.5
70°	56.1	56.1	58.3	43.6	36.2
72.5°	49.4	49.4	47.4	35.4	27.7
75°	39.3	39.3	35.8	24.6	16.8
77.5°	30.3	30.0	27.4	18.3	12.2
80°	24.3	24.3	22.1	14.5	9.7
82.5°	19.0	19.0	17.1	11.3	7.2
85°	11.0	11.0	10.2	6.6	4.0
87.5°	4.1	4.4	4.9	2.8	2.4
90°	0.8	2.5	6.6	3.3	3.3
92.5°	3.5	16.8	37.2	16.5	10.6
95°	8.3	32.6	108.7	56.0	38.2
97.5°	14.4	35.9	162.7	129.4	95.3
100°	19.1	38.6	179.3	181.7	141.1
102.5°	23.1	41.3	183.9	226.3	191.6
105°	29.9	45.3	183.4	278.5	259.8
107.5°	36.9	51.1	173.0	305.6	310.1
110°	41.5	54.5	164.3	312.5	332.0

TEST NUMBER: P518988

CATALOG NUMBER: SQ4-WB-025U-050D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	46.2	58.5	156.4	308.1	338.0
115°	53.1	64.5	146.9	293.1	334.5
117.5°	59.9	70.3	140.4	272.3	318.2
120°	63.9	73.7	137.8	258.3	303.0
122.5°	67.9	77.6	135.8	244.4	288.4
125°	73.9	82.8	133.6	225.9	266.4
127.5°	78.7	87.8	131.8	210.9	245.2
130°	81.3	91.1	131.1	201.6	233.2
132.5°	84.0	93.7	130.5	193.5	222.0
135°	88.0	96.9	129.5	182.3	206.7
137.5°	92.1	100.9	129.3	173.9	193.9
140°	95.5	103.6	128.7	167.3	185.9
142.5°	98.1	105.6	128.7	162.6	178.6
145°	102.1	108.6	127.8	155.5	167.7
147.5°	106.1	112.4	127.8	149.6	159.7
150°	108.7	114.4	127.8	146.3	154.4
152.5°	111.4	115.8	127.8	143.6	149.7
155°	115.4	118.6	127.8	140.4	144.4
157.5°	118.4	121.4	127.8	137.5	140.4
160°	120.4	122.8	127.8	136.2	137.8
162.5°	122.3	124.1	127.8	134.8	136.5
165°	124.5	126.1	127.8	132.8	134.5
167.5°	126.5	127.3	128.7	132.0	132.6
170°	127.8	128.6	128.7	132.0	132.0
172.5°	128.5	128.7	128.7	131.3	130.6
175°	129.5	129.5	128.7	130.3	130.3
177.5°	129.5	129.5	128.8	130.1	129.5
180°	129.5	129.5	129.5	129.5	129.5

(END OF REPORT)