

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563844

Luminaire Tested: **SQ4-PP3-150U-125D-935-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563844  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-150U-125D-935-1D-UNV-STD-W-8  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 18937.6 lumens  
Efficiency: N/A  
Efficacy: 112.9 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 167.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563844  
CATALOG NUMBER: SQ4-PP3-150U-125D-935-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P563844

CATALOG NUMBER: SQ4-PP3-150U-125D-935-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45
1	97	93	89	85	89	85	82	79	71	68	66	58	56	55	46	45	44	38
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	40	39	37	32
3	81	71	64	58	74	66	59	54	55	50	47	45	42	39	36	34	32	27
4	74	63	55	49	67	58	51	46	49	44	40	40	36	33	32	29	27	24
5	68	56	48	42	62	52	45	40	44	38	34	36	32	29	29	26	24	20
6	62	50	42	37	57	47	40	34	39	34	30	33	28	25	26	23	21	18
7	58	45	38	32	53	42	35	30	36	30	26	30	25	22	24	21	19	16
8	53	41	34	28	49	38	31	27	32	27	23	27	23	20	22	19	17	14
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	20	17	15	13
10	46	34	27	23	43	32	26	21	27	22	19	23	19	16	19	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15259	15259	15259
5°	15371	15277	15223
10°	15345	15236	15168
15°	15243	15160	15077
20°	15142	15057	14943
25°	14962	14859	14711
30°	14685	14608	14423
35°	14301	14203	14024
40°	13844	13757	13599
45°	13465	13371	13239
50°	12982	12899	12775
55°	12310	12148	12054
60°	11207	10886	10832
65°	9873	9462	9430
70°	8524	8172	8172
75°	7338	7235	7131
80°	6469	6546	6392
85°	5065	5526	5526



TEST NUMBER: P563844

CATALOG NUMBER: SQ4-PP3-150U-125D-935-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	312.8	1.7
10°-20°	893.1	4.7
20°-30°	1337.7	7.1
30°-40°	1569.1	8.3
40°-50°	1574.0	8.3
50°-60°	1342.7	7.1
60°-70°	875.7	4.6
70°-80°	439.3	2.3
80°-90°	125.0	0.7
90°-100°	754.6	4.0
100°-110°	2040.2	10.8
110°-120°	2145.0	11.3
120°-130°	1742.3	9.2
130°-140°	1366.7	7.2
140°-150°	1049.0	5.5
150°-160°	754.4	4.0
160°-170°	460.8	2.4
170°-180°	155.4	0.8
0°-30°	2543.5	13.4
0°-40°	4112.6	21.7
0°-60°	7029.3	37.1
0°-90°	8469.3	44.7
90°-120°	4939.8	26.1
90°-150°	9097.7	48.0
90°-180°	10468.0	55.3
0°-180°	18937.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3308	3308	3308	3308	3308	
5°	3319	3288	3299	3287	3287	315
15°	3192	3161	3174	3163	3157	900
25°	2940	2906	2919	2893	2890	1352
35°	2540	2514	2522	2493	2490	1586
45°	2064	2050	2050	2029	2029	1589
55°	1531	1525	1510	1502	1499	1360
65°	904	888	867	861	864	903
75°	412	412	406	403	400	447
85°	96	104	104	104	104	112
90°	4	10	23	24	23	11
95°	117	411	1255	649	386	123
105°	379	586	2263	3339	3202	399
115°	668	816	1877	3634	4102	659
125°	914	1047	1692	2855	3354	815
135°	1096	1226	1646	2305	2609	847
145°	1274	1370	1624	1973	2124	797
155°	1438	1495	1610	1770	1828	663
165°	1566	1581	1617	1680	1688	441
175°	1625	1624	1618	1639	1636	154
180°	1624	1624	1624	1624	1624	



TEST NUMBER: P563844

CATALOG NUMBER: SQ4-PP3-150U-125D-935-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3307.7	3307.7	3307.7	3307.7	3307.7
2.5°	3328.6	3301.4	3307.7	3302.7	3289.1
5°	3319.3	3288.1	3299.0	3287.4	3287.4
7.5°	3296.7	3262.7	3273.5	3261.9	3261.3
10°	3275.8	3241.8	3252.6	3241.0	3238.1
12.5°	3245.7	3211.6	3224.8	3210.9	3210.3
15°	3191.7	3160.6	3174.3	3162.6	3157.0
17.5°	3130.9	3096.8	3113.5	3097.2	3094.9
20°	3084.5	3050.5	3067.1	3043.9	3043.9
22.5°	3028.8	2994.8	3013.7	2983.6	2983.6
25°	2939.5	2905.5	2919.2	2893.1	2890.2
27.5°	2833.4	2800.0	2814.3	2784.7	2784.1
30°	2756.9	2725.7	2742.4	2710.4	2707.6
32.5°	2673.4	2644.5	2656.6	2624.6	2621.8
35°	2539.5	2514.0	2522.1	2493.0	2490.2
37.5°	2398.6	2372.5	2381.8	2356.8	2355.7
40°	2298.9	2281.9	2284.4	2263.9	2258.3
42.5°	2206.1	2186.8	2189.3	2169.0	2167.8
45°	2064.0	2049.9	2049.6	2029.3	2029.3
47.5°	1913.3	1902.5	1899.4	1882.6	1882.0
50°	1808.9	1800.4	1797.3	1782.8	1780.0
52.5°	1699.9	1696.0	1686.0	1673.8	1673.3
55°	1530.6	1525.0	1510.4	1501.6	1498.8
57.5°	1346.8	1335.5	1319.0	1306.3	1308.6
60°	1214.7	1203.3	1179.9	1174.1	1174.1
62.5°	1087.1	1073.5	1050.0	1042.0	1046.5
65°	904.5	887.5	866.8	861.1	863.9
67.5°	738.7	723.3	701.0	700.9	698.6
70°	632.0	623.5	605.9	605.9	605.9
72.5°	536.9	532.9	520.1	520.0	517.8
75°	411.7	411.7	405.9	402.9	400.1
77.5°	308.4	309.6	306.7	303.7	298.6
80°	243.5	249.2	246.4	243.4	240.6
82.5°	183.2	188.9	188.4	183.2	182.6
85°	95.7	104.2	104.4	104.4	104.4
87.5°	26.2	36.6	41.7	42.0	44.0
90°	3.5	10.3	22.7	24.4	22.7
92.5°	49.6	180.9	356.9	154.9	112.2
95°	117.1	411.0	1254.9	649.4	386.3
97.5°	188.1	471.4	1956.1	1618.8	1188.8
100°	241.2	495.8	2174.2	2267.5	1833.4
102.5°	290.1	529.7	2251.1	2759.3	2434.6
105°	379.3	586.0	2263.3	3338.6	3201.9
107.5°	461.8	650.4	2164.4	3700.0	3745.4
110°	526.1	697.0	2076.3	3797.0	3990.1



TEST NUMBER: P563844

CATALOG NUMBER: SQ4-PP3-150U-125D-935-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	583.4	743.4	1995.2	3777.6	4102.0
115°	667.6	816.3	1877.1	3633.7	4102.0
117.5°	750.1	889.6	1799.1	3413.9	3944.7
120°	800.5	937.2	1753.0	3256.1	3797.9
122.5°	848.0	982.0	1725.0	3087.0	3632.9
125°	914.1	1047.4	1691.8	2854.9	3353.9
127.5°	974.9	1105.8	1672.2	2665.5	3104.4
130°	1008.5	1143.5	1663.9	2548.5	2945.0
132.5°	1043.4	1177.0	1655.5	2442.9	2807.9
135°	1095.8	1225.7	1646.4	2305.2	2609.4
137.5°	1148.6	1271.3	1638.7	2193.5	2441.3
140°	1185.0	1299.5	1635.9	2121.5	2342.0
142.5°	1219.9	1327.6	1630.3	2056.6	2249.7
145°	1274.1	1369.8	1623.7	1973.1	2123.5
147.5°	1323.4	1408.2	1616.0	1897.5	2013.1
150°	1359.7	1434.9	1613.2	1856.5	1948.7
152.5°	1393.3	1458.9	1611.8	1818.3	1894.2
155°	1438.4	1494.8	1609.7	1770.0	1828.1
157.5°	1485.2	1524.5	1610.0	1736.4	1774.7
160°	1511.8	1544.3	1611.4	1715.2	1742.5
162.5°	1532.8	1559.8	1612.8	1698.2	1718.7
165°	1566.0	1581.4	1616.7	1679.8	1688.3
167.5°	1588.7	1599.3	1617.0	1664.0	1668.1
170°	1602.7	1607.8	1618.4	1656.9	1656.9
172.5°	1613.9	1614.9	1618.4	1648.4	1647.1
175°	1625.4	1623.7	1618.4	1639.3	1635.9
177.5°	1629.3	1625.2	1618.1	1632.0	1627.9
180°	1623.7	1623.7	1623.7	1623.7	1623.7

(END OF REPORT)