

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563916

Luminaire Tested: **SQ4-PR1-025U-100D-935-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563916
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-025U-100D-935-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8274.7 lumens
Efficiency: N/A
Efficacy: 100.7 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 82.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563916
CATALOG NUMBER: SQ4-PR1-025U-100D-935-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P563916

CATALOG NUMBER: SQ4-PR1-025U-100D-935-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	114	114	114	114	109	109	109	109	100	100	100	91	91	91	83	83	83	80				
1	105	101	97	93	100	96	93	90	88	86	83	81	79	77	74	73	71	68				
2	96	88	82	77	92	85	79	74	78	74	70	72	68	65	66	63	61	58				
3	88	78	71	65	84	75	68	63	69	64	59	64	59	56	59	55	52	49				
4	81	70	61	55	77	67	60	54	62	56	51	57	52	48	53	49	45	43				
5	74	62	54	48	71	60	52	47	56	49	44	52	46	42	48	43	40	37				
6	69	56	48	42	66	54	47	41	50	44	39	47	41	37	44	39	35	33				
7	64	51	43	37	61	49	42	36	46	39	35	43	37	33	40	35	31	29				
8	59	47	39	33	57	45	38	32	42	36	31	39	34	30	37	32	28	26				
9	55	43	35	30	53	41	34	29	39	32	28	36	31	27	34	29	26	24				
10	52	39	32	27	50	38	31	26	36	30	25	34	28	24	31	27	23	21				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12169	12169	12169
5°	12279	12184	12121
10°	12240	12155	12091
15°	12186	12111	12045
20°	12125	12047	11958
25°	12040	11958	11820
30°	11910	11825	11655
35°	11734	11631	11465
40°	11466	11343	11138
45°	10999	10806	10584
50°	10175	9931	9735
55°	8882	8680	8498
60°	7484	7422	7275
65°	6473	6498	6449
70°	5945	5976	5976
75°	5711	5711	5752
80°	5372	5433	5372
85°	4330	4811	4811



TEST NUMBER: P563916

CATALOG NUMBER: SQ4-PR1-025U-100D-935-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	249.5	3.0
10°-20°	713.7	8.6
20°-30°	1076.5	13.0
30°-40°	1282.7	15.5
40°-50°	1264.6	15.3
50°-60°	966.5	11.7
60°-70°	598.1	7.2
70°-80°	339.7	4.1
80°-90°	104.7	1.3
90°-100°	126.2	1.5
100°-110°	331.8	4.0
110°-120°	344.1	4.2
120°-130°	276.0	3.3
130°-140°	216.6	2.6
140°-150°	166.2	2.0
150°-160°	119.7	1.4
160°-170°	73.2	0.9
170°-180°	24.7	0.3
0°-30°	2039.8	24.7
0°-40°	3322.5	40.2
0°-60°	5553.6	67.1
0°-90°	6596.2	79.7
90°-120°	802.1	9.7
90°-150°	1460.9	17.7
90°-180°	1679.0	20.3
0°-180°	8274.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2638	2638	2638	2638	2638	
5°	2652	2623	2631	2622	2618	252
15°	2552	2525	2536	2527	2522	720
25°	2365	2336	2349	2324	2322	1089
35°	2084	2059	2065	2038	2036	1300
45°	1686	1664	1656	1627	1622	1292
55°	1104	1086	1079	1061	1057	989
65°	593	589	595	591	591	601
75°	320	320	320	323	323	338
85°	82	86	91	91	91	95
90°	2	5	13	7	7	5
95°	17	65	218	112	76	19
105°	60	91	367	557	520	63
115°	106	129	294	586	669	105
125°	148	166	267	452	533	131
135°	176	194	259	365	413	136
145°	204	217	256	311	335	128
155°	231	237	256	281	289	106
165°	249	252	256	266	269	70
175°	259	259	257	261	261	25
180°	259	259	259	259	259	

TEST NUMBER: P563916

CATALOG NUMBER: SQ4-PR1-025U-100D-935-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2638.0	2638.0	2638.0	2638.0	2638.0
2.5°	2654.4	2631.3	2638.0	2632.3	2619.8
5°	2651.7	2622.8	2631.2	2622.0	2617.6
7.5°	2631.2	2602.8	2611.2	2602.1	2599.4
10°	2613.0	2586.4	2594.8	2585.7	2581.2
12.5°	2593.0	2564.6	2574.9	2563.8	2559.4
15°	2551.7	2525.0	2535.8	2526.6	2522.1
17.5°	2506.2	2477.8	2488.5	2477.9	2472.1
20°	2469.9	2443.2	2454.0	2438.0	2435.8
22.5°	2429.9	2403.2	2414.0	2392.6	2392.2
25°	2365.4	2336.5	2349.4	2324.4	2322.2
27.5°	2288.6	2261.9	2272.6	2247.1	2244.5
30°	2235.8	2209.2	2219.9	2192.6	2188.1
32.5°	2175.9	2151.0	2159.9	2132.6	2130.0
35°	2083.6	2059.2	2065.4	2038.1	2035.9
37.5°	1978.6	1956.4	1960.0	1930.0	1927.7
40°	1904.1	1881.9	1883.6	1851.8	1849.6
42.5°	1822.3	1800.1	1798.2	1766.4	1764.1
45°	1686.0	1663.8	1656.4	1626.8	1622.3
47.5°	1530.6	1508.3	1494.6	1470.5	1467.4
50°	1417.8	1395.6	1383.8	1363.2	1356.5
52.5°	1296.1	1273.8	1263.8	1245.0	1238.3
55°	1104.3	1086.5	1079.3	1061.0	1056.6
57.5°	922.1	910.1	908.0	890.2	888.4
60°	811.2	804.5	804.4	788.5	788.5
62.5°	716.7	711.8	715.3	704.8	703.0
65°	593.0	588.6	595.3	590.8	590.8
67.5°	495.3	495.3	499.4	497.6	497.6
70°	440.8	440.8	443.1	443.1	443.1
72.5°	391.7	389.9	395.8	395.8	394.0
75°	320.4	320.4	320.4	322.7	322.7
77.5°	249.5	249.9	251.8	251.3	249.5
80°	202.2	204.4	204.5	202.2	202.2
82.5°	155.0	157.2	157.2	156.7	155.0
85°	81.8	86.2	90.9	90.9	90.9
87.5°	24.0	31.7	39.0	37.6	35.9
90°	1.7	4.9	13.3	6.6	6.6
92.5°	7.0	33.6	74.4	32.9	21.2
95°	16.6	65.3	217.5	112.1	76.4
97.5°	28.9	71.7	325.4	258.8	190.6
100°	38.2	77.1	358.6	363.4	282.2
102.5°	46.2	82.5	367.9	452.6	383.1
105°	59.8	90.6	366.9	556.9	519.6
107.5°	73.7	102.3	346.0	611.1	620.2
110°	83.0	109.0	328.7	625.1	664.0



TEST NUMBER: P563916

CATALOG NUMBER: SQ4-PR1-025U-100D-935-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	92.3	117.0	312.8	616.3	676.0
115°	106.2	129.0	293.8	586.2	669.0
117.5°	119.9	140.6	280.9	544.6	636.5
120°	127.8	147.3	275.6	516.7	605.9
122.5°	135.8	155.3	271.6	488.7	576.7
125°	147.7	165.6	267.3	451.7	532.9
127.5°	157.4	175.6	263.6	421.9	490.4
130°	162.7	182.2	262.3	403.2	466.5
132.5°	168.0	187.5	261.0	387.1	443.9
135°	176.0	193.8	259.0	364.7	413.4
137.5°	184.3	201.8	258.6	347.9	387.8
140°	190.9	207.1	257.3	334.5	371.9
142.5°	196.2	211.2	257.3	325.1	357.3
145°	204.2	217.2	255.7	311.0	335.3
147.5°	212.2	224.8	255.7	299.3	319.4
150°	217.5	228.8	255.7	292.5	308.8
152.5°	222.8	231.5	255.7	287.1	299.5
155°	230.8	237.2	255.7	280.7	288.9
157.5°	236.7	242.9	255.7	275.0	280.9
160°	240.7	245.6	255.7	272.3	275.6
162.5°	244.7	248.3	255.7	269.7	272.9
165°	249.0	252.3	255.7	265.7	268.9
167.5°	253.0	254.6	257.3	264.0	265.3
170°	255.7	257.3	257.3	264.0	264.0
172.5°	257.0	257.3	257.3	262.6	261.3
175°	259.0	259.0	257.3	260.6	260.6
177.5°	259.0	259.0	257.6	260.3	259.0
180°	259.0	259.0	259.0	259.0	259.0

(END OF REPORT)