

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: CORELITE

Report Number: P564276

Luminaire Tested: **SQ4-PR1-100U-075D-935-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P564276  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2106-289-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PR1-100U-075D-935-1D-UNV-STD-W-8  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 1000 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 11945.0 lumens  
Efficiency: N/A  
Efficacy: 115.0 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35  
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 103.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P564276  
CATALOG NUMBER: SQ4-PR1-100U-075D-935-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P564276

CATALOG NUMBER: SQ4-PR1-100U-075D-935-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	42
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	35
2	88	81	75	70	80	74	69	64	61	57	54	49	47	44	38	37	35	30
3	80	71	64	58	73	65	59	54	54	49	46	44	40	38	34	32	30	26
4	73	63	55	49	67	58	51	46	48	43	39	39	35	33	31	28	26	22
5	67	56	48	42	61	52	45	39	43	38	34	35	31	28	28	25	23	19
6	62	50	42	37	56	46	39	34	39	33	29	32	28	25	25	22	20	17
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	34	28	48	38	31	27	32	27	23	26	22	20	21	18	16	14
9	49	38	30	25	45	35	28	24	29	24	21	24	20	18	19	17	15	12
10	46	34	27	23	42	32	25	21	27	22	19	22	19	16	18	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9159	9159	9159
5°	9242	9170	9123
10°	9212	9148	9100
15°	9172	9115	9065
20°	9126	9067	8999
25°	9061	9000	8896
30°	8963	8900	8772
35°	8831	8754	8629
40°	8630	8537	8383
45°	8278	8133	7966
50°	7658	7474	7327
55°	6684	6533	6396
60°	5633	5586	5475
65°	4872	4890	4853
70°	4475	4498	4498
75°	4297	4297	4328
80°	4043	4088	4043
85°	3260	3620	3620



TEST NUMBER: P564276

CATALOG NUMBER: SQ4-PR1-100U-075D-935-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	187.8	1.6
10°-20°	537.2	4.5
20°-30°	810.2	6.8
30°-40°	965.4	8.1
40°-50°	951.8	8.0
50°-60°	727.4	6.1
60°-70°	450.1	3.8
70°-80°	255.7	2.1
80°-90°	80.0	0.7
90°-100°	503.0	4.2
100°-110°	1388.8	11.6
110°-120°	1432.3	12.0
120°-130°	1150.9	9.6
130°-140°	904.5	7.6
140°-150°	693.7	5.8
150°-160°	498.6	4.2
160°-170°	304.9	2.6
170°-180°	102.8	0.9
0°-30°	1535.1	12.9
0°-40°	2500.5	20.9
0°-60°	4179.7	35.0
0°-90°	4965.5	41.6
90°-120°	3324.1	27.8
90°-150°	6073.2	50.8
90°-180°	6979.0	58.4
0°-180°	11945.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1985	1985	1985	1985	1985	
5°	1996	1974	1980	1973	1970	189
15°	1920	1900	1908	1902	1898	542
25°	1780	1758	1768	1749	1748	819
35°	1568	1550	1554	1534	1532	979
45°	1269	1252	1247	1224	1221	972
55°	831	818	812	798	795	745
65°	446	443	448	445	445	452
75°	241	241	241	243	243	255
85°	62	65	68	68	68	72
90°	3	7	14	16	17	8
95°	74	272	913	375	244	79
105°	248	382	1528	2333	2196	263
115°	443	536	1231	2436	2770	436
125°	608	692	1115	1888	2215	541
135°	732	811	1084	1529	1724	566
145°	849	908	1071	1302	1401	532
155°	957	989	1062	1168	1205	441
165°	1036	1050	1067	1109	1117	292
175°	1074	1076	1069	1084	1081	102
180°	1074	1074	1074	1074	1074	

TEST NUMBER: P564276

CATALOG NUMBER: SQ4-PR1-100U-075D-935-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1985.4	1985.4	1985.4	1985.4	1985.4
2.5°	1997.7	1980.3	1985.4	1981.1	1971.7
5°	1995.7	1973.9	1980.3	1973.4	1970.0
7.5°	1980.3	1958.9	1965.2	1958.3	1956.3
10°	1966.6	1946.5	1952.9	1946.0	1942.7
12.5°	1951.5	1930.1	1937.9	1929.6	1926.2
15°	1920.4	1900.4	1908.5	1901.5	1898.2
17.5°	1886.2	1864.8	1872.9	1864.9	1860.6
20°	1858.9	1838.8	1846.9	1834.9	1833.2
22.5°	1828.8	1808.7	1816.8	1800.7	1800.4
25°	1780.2	1758.5	1768.2	1749.4	1747.7
27.5°	1722.4	1702.3	1710.4	1691.2	1689.2
30°	1682.7	1662.7	1670.8	1650.2	1646.8
32.5°	1637.6	1618.9	1625.6	1605.0	1603.0
35°	1568.1	1549.8	1554.5	1533.9	1532.2
37.5°	1489.1	1472.4	1475.1	1452.5	1450.8
40°	1433.1	1416.3	1417.7	1393.7	1392.0
42.5°	1371.5	1354.8	1353.4	1329.4	1327.7
45°	1268.9	1252.2	1246.7	1224.3	1221.0
47.5°	1151.9	1135.2	1124.9	1106.7	1104.4
50°	1067.1	1050.4	1041.4	1025.9	1020.9
52.5°	975.4	958.7	951.1	937.0	932.0
55°	831.1	817.7	812.3	798.5	795.2
57.5°	694.0	684.9	683.4	670.0	668.6
60°	610.5	605.5	605.4	593.4	593.4
62.5°	539.4	535.7	538.3	530.4	529.1
65°	446.3	443.0	448.0	444.6	444.6
67.5°	372.8	372.8	375.9	374.5	374.5
70°	331.8	331.8	333.5	333.5	333.5
72.5°	294.8	293.5	297.9	297.9	296.5
75°	241.1	241.1	241.1	242.8	242.8
77.5°	187.8	188.1	189.5	189.1	187.8
80°	152.2	153.9	153.9	152.2	152.2
82.5°	116.6	118.3	118.3	118.0	116.6
85°	61.6	64.9	68.4	68.4	68.4
87.5°	18.5	24.5	30.1	30.4	29.4
90°	3.4	6.8	13.7	15.5	17.2
92.5°	30.9	128.4	229.6	83.8	65.3
95°	73.9	272.2	912.6	375.1	244.1
97.5°	122.4	304.9	1351.9	1040.9	753.8
100°	158.1	324.5	1514.2	1524.9	1239.2
102.5°	192.5	346.8	1545.8	1884.1	1613.2
105°	247.5	381.9	1527.9	2332.6	2196.5
107.5°	305.9	425.6	1442.7	2548.9	2598.7
110°	347.2	454.7	1376.7	2595.5	2756.8



TEST NUMBER: P564276

CATALOG NUMBER: SQ4-PR1-100U-075D-935-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	384.3	487.8	1314.8	2558.7	2796.7
115°	443.4	535.9	1230.6	2436.1	2770.5
117.5°	495.0	587.1	1175.2	2263.6	2644.0
120°	529.4	620.1	1153.2	2146.8	2529.9
122.5°	562.4	649.1	1135.4	2037.7	2400.7
125°	608.4	692.4	1115.4	1887.7	2215.4
127.5°	647.6	731.6	1103.7	1760.9	2043.5
130°	673.7	757.8	1098.2	1683.3	1940.4
132.5°	698.5	778.5	1092.7	1618.1	1851.0
135°	732.2	811.1	1084.5	1528.9	1723.9
137.5°	770.0	841.9	1080.4	1454.0	1620.4
140°	790.6	861.2	1077.6	1404.1	1550.3
142.5°	814.0	879.2	1074.9	1359.7	1488.4
145°	849.0	907.9	1070.7	1301.6	1400.7
147.5°	882.7	934.1	1067.0	1252.6	1329.6
150°	907.5	949.5	1065.6	1223.4	1285.6
152.5°	926.7	966.0	1064.2	1198.4	1249.8
155°	957.3	989.2	1062.2	1167.8	1204.8
157.5°	985.5	1010.0	1062.5	1145.6	1170.8
160°	1002.0	1023.8	1063.9	1133.0	1151.5
162.5°	1015.8	1034.9	1065.2	1122.0	1136.4
165°	1036.4	1049.8	1067.3	1108.8	1117.2
167.5°	1052.2	1060.3	1069.0	1100.7	1103.4
170°	1060.4	1067.2	1069.0	1096.5	1096.5
172.5°	1067.3	1071.3	1069.0	1091.0	1089.7
175°	1074.2	1075.9	1069.0	1084.4	1081.1
177.5°	1076.9	1075.6	1068.7	1078.2	1075.6
180°	1074.2	1074.2	1074.2	1074.2	1074.2

(END OF REPORT)