

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P564660

Luminaire Tested: **SQ4-PW1-050U-075D-935-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564660
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-050U-075D-935-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8401.9 lumens
Efficiency: N/A
Efficacy: 107.6 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 78.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564660
CATALOG NUMBER: SQ4-PW1-050U-075D-935-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P564660

CATALOG NUMBER: SQ4-PW1-050U-075D-935-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	96	92	88	93	89	86	83	78	75	73	67	65	63	57	56	55	50
2	91	84	77	72	85	78	73	68	68	64	60	59	56	53	50	48	46	42
3	83	74	66	60	77	69	62	57	60	55	51	52	48	45	45	42	39	36
4	76	65	57	51	71	61	54	48	54	48	43	46	42	39	40	37	34	31
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	36	32	30	27
6	64	52	44	38	60	49	42	36	43	37	33	38	33	29	33	29	26	23
7	60	47	39	33	55	44	37	32	39	33	29	34	30	26	30	26	23	21
8	55	43	35	30	52	40	33	28	36	30	26	31	27	23	27	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23	29	24	21	25	22	19	17
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8954	8954	8954
5°	9012	8941	8901
10°	8940	8868	8820
15°	8845	8747	8714
20°	8739	8605	8588
25°	8617	8461	8435
30°	8435	8308	8253
35°	8196	8080	8032
40°	7940	7817	7785
45°	7631	7531	7497
50°	7315	7254	7204
55°	6973	6973	6863
60°	6548	6674	6437
65°	5992	6291	5843
70°	5282	5789	5144
75°	4511	5181	4390
80°	3499	4362	3544
85°	2265	3350	2985



TEST NUMBER: P564660

CATALOG NUMBER: SQ4-PW1-050U-075D-935-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.8	2.2
10°-20°	516.0	6.1
20°-30°	765.4	9.1
30°-40°	895.6	10.7
40°-50°	891.6	10.6
50°-60°	769.9	9.2
60°-70°	554.2	6.6
70°-80°	290.6	3.5
80°-90°	74.1	0.9
90°-100°	254.5	3.0
100°-110°	691.4	8.2
110°-120°	710.8	8.5
120°-130°	568.3	6.8
130°-140°	446.6	5.3
140°-150°	342.4	4.1
150°-160°	246.2	2.9
160°-170°	150.6	1.8
170°-180°	50.7	0.6
0°-30°	1464.2	17.4
0°-40°	2359.8	28.1
0°-60°	4021.4	47.9
0°-90°	4940.3	58.8
90°-120°	1656.7	19.7
90°-150°	3014.0	35.9
90°-180°	3462.0	41.2
0°-180°	8401.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1941	1941	1941	1941	1941	
5°	1946	1924	1931	1926	1922	184
15°	1852	1829	1832	1828	1825	522
25°	1693	1665	1662	1652	1657	778
35°	1455	1435	1435	1421	1426	910
45°	1170	1160	1154	1151	1149	903
55°	867	865	867	855	853	774
65°	549	566	576	554	535	544
75°	253	276	291	271	246	271
85°	43	56	63	60	56	56
90°	2	7	12	15	15	4
95°	38	139	443	193	130	40
105°	123	191	760	1158	1089	130
115°	218	265	609	1211	1379	215
125°	300	342	551	928	1094	267
135°	361	401	535	756	852	279
145°	418	448	528	642	690	262
155°	472	489	525	577	593	218
165°	511	518	527	549	551	144
175°	530	532	528	535	534	50
180°	530	530	530	530	530	

TEST NUMBER: P564660

CATALOG NUMBER: SQ4-PW1-050U-075D-935-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1941.0	1941.0	1941.0	1941.0	1941.0
2.5°	1951.9	1935.8	1941.0	1936.6	1927.3
5°	1946.1	1924.3	1930.7	1925.5	1922.1
7.5°	1926.2	1906.2	1910.9	1905.3	1903.3
10°	1908.5	1888.4	1893.1	1886.2	1882.8
12.5°	1887.9	1866.5	1871.2	1864.3	1862.3
15°	1852.0	1828.6	1831.5	1828.0	1824.7
17.5°	1810.3	1786.6	1787.0	1781.6	1780.9
20°	1780.2	1755.1	1752.8	1746.1	1749.4
22.5°	1747.4	1721.0	1718.6	1709.2	1713.9
25°	1693.0	1664.6	1662.2	1652.1	1657.1
27.5°	1630.1	1602.0	1602.0	1587.8	1593.1
30°	1583.5	1556.8	1559.6	1542.7	1549.3
32.5°	1534.3	1510.2	1511.7	1494.8	1501.5
35°	1455.3	1435.2	1434.8	1421.2	1426.2
37.5°	1374.6	1356.8	1354.0	1346.2	1347.6
40°	1318.5	1303.4	1298.0	1292.8	1292.8
42.5°	1259.7	1245.9	1240.5	1236.7	1235.4
45°	1169.7	1159.7	1154.3	1150.9	1149.2
47.5°	1080.8	1071.4	1066.8	1064.3	1062.7
50°	1019.2	1012.5	1010.7	1005.5	1003.8
52.5°	957.7	953.6	951.8	945.3	943.6
55°	867.0	865.3	867.0	855.0	853.3
57.5°	772.6	775.3	780.8	764.7	760.6
60°	709.7	716.4	723.4	704.4	697.7
62.5°	645.4	656.1	665.9	644.1	634.8
65°	548.9	565.7	576.3	553.7	535.3
67.5°	455.9	476.6	489.4	465.0	444.3
70°	391.6	415.0	429.2	404.8	381.4
72.5°	335.5	361.6	373.1	350.0	326.6
75°	253.1	276.5	290.7	271.3	246.3
77.5°	179.6	201.6	213.4	196.5	175.8
80°	131.7	155.1	164.2	150.1	133.4
82.5°	93.4	112.8	119.0	110.6	99.2
85°	42.8	56.1	63.3	59.8	56.4
87.5°	11.3	21.6	28.4	29.1	30.4
90°	1.7	6.7	11.9	15.3	15.3
92.5°	15.3	69.7	121.0	52.0	44.0
95°	37.5	139.2	443.2	192.9	129.6
97.5°	62.1	153.7	679.5	528.6	371.3
100°	78.4	163.4	751.8	762.1	615.4
102.5°	94.8	173.1	770.9	942.5	813.1
105°	122.7	191.1	760.3	1157.6	1089.3
107.5°	151.7	212.1	716.3	1268.7	1287.7
110°	172.2	227.2	683.6	1290.6	1372.3



TEST NUMBER: P564660

CATALOG NUMBER: SQ4-PW1-050U-075D-935-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	189.9	242.2	650.8	1272.4	1395.4
115°	218.2	264.9	608.6	1210.7	1379.1
117.5°	244.8	289.5	581.6	1123.3	1312.9
120°	262.5	305.9	569.4	1064.6	1252.9
122.5°	277.5	320.9	561.2	1005.8	1187.5
125°	300.0	341.7	550.6	927.7	1094.4
127.5°	320.1	361.5	544.8	868.5	1011.6
130°	332.4	372.4	542.1	831.4	959.7
132.5°	344.7	384.7	539.4	799.7	913.4
135°	361.4	401.4	535.3	755.7	852.3
137.5°	379.5	415.8	533.2	716.8	798.1
140°	390.4	425.4	531.9	692.1	765.4
142.5°	401.3	433.6	530.5	672.7	734.0
145°	417.6	447.6	528.4	642.1	690.4
147.5°	436.1	461.7	526.7	618.0	656.0
150°	448.3	470.0	526.7	604.1	634.1
152.5°	457.9	476.9	525.4	591.7	616.4
155°	472.2	488.9	525.0	576.6	593.2
157.5°	486.2	499.2	525.0	566.2	578.9
160°	494.4	506.0	525.0	559.4	569.4
162.5°	502.5	511.5	526.4	553.8	561.2
165°	511.4	518.1	526.7	548.9	550.6
167.5°	520.6	523.9	528.4	543.1	544.5
170°	523.3	526.7	528.4	540.4	540.4
172.5°	526.1	528.1	528.4	537.7	537.7
175°	530.2	531.8	528.4	535.2	533.6
177.5°	531.5	531.5	527.4	532.8	530.2
180°	530.2	530.2	530.2	530.2	530.2

(END OF REPORT)