

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: CORELITE

Report Number: P565044

Luminaire Tested: **SQ4-PW1-125U-075D-935-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P565044  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PW1-125U-075D-935-1D-UNV-STD-W-8  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 13629.2 lumens  
Efficiency: N/A  
Efficacy: 117.5 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31  
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 116  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P565044  
CATALOG NUMBER: SQ4-PW1-125U-075D-935-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P565044

CATALOG NUMBER: SQ4-PW1-125U-075D-935-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36
1	95	91	87	83	86	82	79	76	66	64	62	52	50	49	39	38	37	31
2	86	79	73	68	78	72	67	62	58	55	52	46	43	41	34	32	31	26
3	79	70	62	57	71	63	57	52	51	47	43	40	37	35	30	28	27	22
4	72	61	54	48	65	56	49	44	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	24	22	20	16
6	61	49	41	35	55	45	38	33	37	31	28	29	25	23	22	19	18	14
7	56	44	36	31	51	40	34	29	33	28	24	26	23	20	20	17	16	13
8	52	40	32	27	47	37	30	25	30	25	21	24	20	18	18	16	14	11
9	48	36	29	24	44	33	27	22	28	23	19	22	18	16	17	14	13	10
10	45	33	26	22	41	31	24	20	25	20	17	20	17	14	16	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8954	8954	8954
5°	9012	8941	8901
10°	8940	8868	8820
15°	8845	8747	8714
20°	8739	8605	8588
25°	8617	8461	8435
30°	8435	8308	8253
35°	8196	8080	8032
40°	7940	7817	7785
45°	7631	7531	7497
50°	7315	7254	7204
55°	6973	6973	6863
60°	6548	6674	6437
65°	5992	6291	5843
70°	5282	5789	5144
75°	4511	5181	4390
80°	3499	4362	3544
85°	2265	3350	2985



TEST NUMBER: P565044

CATALOG NUMBER: SQ4-PW1-125U-075D-935-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	182.8	1.3
10°-20°	516.0	3.8
20°-30°	765.4	5.6
30°-40°	895.6	6.6
40°-50°	891.6	6.5
50°-60°	769.9	5.6
60°-70°	554.2	4.1
70°-80°	290.6	2.1
80°-90°	75.2	0.6
90°-100°	629.6	4.6
100°-110°	1695.9	12.4
110°-120°	1779.8	13.1
120°-130°	1444.2	10.6
130°-140°	1132.7	8.3
140°-150°	869.6	6.4
150°-160°	625.2	4.6
160°-170°	382.0	2.8
170°-180°	128.8	0.9
0°-30°	1464.2	10.7
0°-40°	2359.8	17.3
0°-60°	4021.4	29.5
0°-90°	4941.5	36.3
90°-120°	4105.2	30.1
90°-150°	7551.7	55.4
90°-180°	8688.0	63.7
0°-180°	13629.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1941	1941	1941	1941	1941	
5°	1946	1924	1931	1926	1922	184
15°	1852	1829	1832	1828	1825	522
25°	1693	1665	1662	1652	1657	778
35°	1455	1435	1435	1421	1426	910
45°	1170	1160	1154	1151	1149	903
55°	867	865	867	855	853	774
65°	549	566	576	554	535	544
75°	253	276	291	271	246	271
85°	43	56	63	60	56	56
90°	3	10	21	22	22	8
95°	96	342	1032	528	365	100
105°	314	488	1876	2806	2633	330
115°	554	678	1562	3018	3413	545
125°	756	868	1402	2370	2789	675
135°	910	1016	1363	1912	2165	703
145°	1053	1135	1346	1635	1756	660
155°	1195	1238	1334	1467	1514	550
165°	1296	1311	1339	1392	1399	365
175°	1348	1346	1341	1359	1356	128
180°	1346	1346	1346	1346	1346	

TEST NUMBER: P565044

CATALOG NUMBER: SQ4-PW1-125U-075D-935-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1941.0	1941.0	1941.0	1941.0	1941.0
2.5°	1951.9	1935.8	1941.0	1936.6	1927.3
5°	1946.1	1924.3	1930.7	1925.5	1922.1
7.5°	1926.2	1906.2	1910.9	1905.3	1903.3
10°	1908.5	1888.4	1893.1	1886.2	1882.8
12.5°	1887.9	1866.5	1871.2	1864.3	1862.3
15°	1852.0	1828.6	1831.5	1828.0	1824.7
17.5°	1810.3	1786.6	1787.0	1781.6	1780.9
20°	1780.2	1755.1	1752.8	1746.1	1749.4
22.5°	1747.4	1721.0	1718.6	1709.2	1713.9
25°	1693.0	1664.6	1662.2	1652.1	1657.1
27.5°	1630.1	1602.0	1602.0	1587.8	1593.1
30°	1583.5	1556.8	1559.6	1542.7	1549.3
32.5°	1534.3	1510.2	1511.7	1494.8	1501.5
35°	1455.3	1435.2	1434.8	1421.2	1426.2
37.5°	1374.6	1356.8	1354.0	1346.2	1347.6
40°	1318.5	1303.4	1298.0	1292.8	1292.8
42.5°	1259.7	1245.9	1240.5	1236.7	1235.4
45°	1169.7	1159.7	1154.3	1150.9	1149.2
47.5°	1080.8	1071.4	1066.8	1064.3	1062.7
50°	1019.2	1012.5	1010.7	1005.5	1003.8
52.5°	957.7	953.6	951.8	945.3	943.6
55°	867.0	865.3	867.0	855.0	853.3
57.5°	772.6	775.3	780.8	764.7	760.6
60°	709.7	716.4	723.4	704.4	697.7
62.5°	645.4	656.1	665.9	644.1	634.8
65°	548.9	565.7	576.3	553.7	535.3
67.5°	455.9	476.6	489.4	465.0	444.3
70°	391.6	415.0	429.2	404.8	381.4
72.5°	335.5	361.6	373.1	350.0	326.6
75°	253.1	276.5	290.7	271.3	246.3
77.5°	179.6	201.6	213.4	196.5	175.8
80°	131.7	155.1	164.2	150.1	133.4
82.5°	93.4	112.8	119.0	110.6	99.2
85°	42.8	56.1	63.3	59.8	56.4
87.5°	11.6	22.3	30.1	30.5	31.8
90°	3.4	10.1	20.6	22.3	22.3
92.5°	41.8	147.8	292.1	140.6	97.7
95°	96.0	342.4	1032.0	527.8	365.2
97.5°	153.3	392.0	1618.7	1352.3	1019.7
100°	197.2	411.7	1805.2	1888.8	1566.9
102.5°	239.7	439.5	1866.9	2290.6	2026.4
105°	313.7	488.1	1875.5	2805.9	2633.3
107.5°	383.7	539.2	1795.6	3070.7	3115.3
110°	430.3	577.8	1722.9	3153.0	3315.6

TEST NUMBER: P565044

CATALOG NUMBER: SQ4-PW1-125U-075D-935-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	479.7	616.5	1653.0	3134.8	3402.0
115°	553.7	677.8	1561.8	3017.7	3413.3
117.5°	621.3	737.6	1491.2	2830.8	3271.3
120°	665.2	777.5	1455.5	2696.7	3149.3
122.5°	703.6	814.5	1429.4	2559.5	3010.8
125°	756.0	868.3	1402.3	2370.2	2789.3
127.5°	806.4	917.1	1385.2	2203.2	2577.4
130°	836.6	947.2	1378.3	2107.6	2436.1
132.5°	866.8	976.1	1371.5	2023.3	2325.0
135°	910.3	1015.9	1362.9	1912.1	2165.2
137.5°	951.8	1053.1	1358.5	1817.8	2025.7
140°	980.6	1077.8	1354.3	1759.8	1947.5
142.5°	1010.8	1101.3	1351.6	1705.6	1863.9
145°	1052.6	1134.8	1345.8	1634.8	1755.5
147.5°	1097.9	1169.3	1339.9	1575.3	1670.1
150°	1128.0	1190.1	1337.2	1537.9	1616.6
152.5°	1155.5	1209.5	1335.8	1507.3	1571.4
155°	1194.9	1238.5	1333.8	1466.8	1513.8
157.5°	1229.5	1263.4	1334.1	1438.4	1469.9
160°	1251.5	1280.0	1335.5	1421.7	1445.2
162.5°	1270.7	1293.8	1336.9	1407.9	1424.6
165°	1296.1	1311.1	1338.9	1392.2	1398.9
167.5°	1316.6	1325.3	1340.6	1380.1	1382.8
170°	1330.3	1333.7	1340.6	1373.2	1373.2
172.5°	1338.6	1339.2	1342.0	1366.3	1366.3
175°	1347.5	1345.8	1340.6	1359.4	1356.1
177.5°	1351.3	1348.6	1341.7	1352.6	1349.9
180°	1345.8	1345.8	1345.8	1345.8	1345.8

(END OF REPORT)