

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: CORELITE

Report Number: P562667

Luminaire Tested: **SQ4-PC3-050U-100D-935-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562667  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-050U-100D-935-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7620.7 lumens  
Efficiency: N/A  
Efficacy: 103.8 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 73.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562667  
CATALOG NUMBER: SQ4-PC3-050U-100D-935-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P562667

CATALOG NUMBER: SQ4-PC3-050U-100D-935-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66
1	101	97	93	90	95	91	88	85	81	78	76	72	70	68	63	61	60	56
2	92	85	78	73	87	80	74	70	71	67	63	63	60	57	55	53	51	47
3	84	75	67	61	79	70	64	58	63	57	53	56	51	48	49	46	43	39
4	77	66	58	52	72	62	55	49	56	50	45	49	45	41	44	40	37	34
5	71	59	50	44	66	56	48	42	50	44	39	44	39	36	39	35	32	29
6	65	53	44	38	61	50	43	37	45	39	34	40	35	31	36	32	28	26
7	60	48	40	34	57	45	38	33	41	35	30	37	31	28	32	28	25	23
8	56	43	35	30	53	41	34	29	37	31	27	33	28	25	30	26	22	20
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	23	20	18
10	49	36	29	24	46	35	28	23	32	26	22	28	23	20	26	21	18	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11321	11321	11321
5°	11406	11332	11290
10°	11378	11325	11293
15°	11318	11318	11307
20°	11244	11277	11277
25°	11138	11218	11184
30°	11002	11135	11087
35°	10838	11005	10927
40°	10659	10810	10700
45°	10465	10540	10376
50°	10192	10192	10029
55°	9868	9740	9594
60°	9392	9203	9056
65°	8681	8507	8433
70°	7600	7661	7631
75°	6115	6763	6804
80°	4346	5735	5795
85°	2646	4813	4813



TEST NUMBER: P562667

CATALOG NUMBER: SQ4-PC3-050U-100D-935-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	174.2	2.3
10°-20°	499.9	6.6
20°-30°	757.0	9.9
30°-40°	907.5	11.9
40°-50°	925.3	12.1
50°-60°	807.8	10.6
60°-70°	578.3	7.6
70°-80°	297.9	3.9
80°-90°	76.9	1.0
90°-100°	190.9	2.5
100°-110°	518.5	6.8
110°-120°	533.1	7.0
120°-130°	426.2	5.6
130°-140°	334.9	4.4
140°-150°	256.8	3.4
150°-160°	184.7	2.4
160°-170°	112.9	1.5
170°-180°	38.1	0.5
0°-30°	1431.0	18.8
0°-40°	2338.5	30.7
0°-60°	4071.6	53.4
0°-90°	5024.6	65.9
90°-120°	1242.5	16.3
90°-150°	2260.4	29.7
90°-180°	2596.0	34.1
0°-180°	7620.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1840	1840	1840	1840	1840	
5°	1847	1829	1835	1830	1829	175
15°	1777	1762	1777	1777	1776	501
25°	1641	1629	1653	1648	1648	755
35°	1443	1440	1466	1455	1455	903
45°	1203	1200	1212	1196	1193	926
55°	920	909	908	895	895	820
65°	596	583	584	579	579	590
75°	257	269	285	286	286	278
85°	38	58	68	70	68	51
90°	1	5	9	12	12	3
95°	28	104	332	145	97	30
105°	92	143	570	868	817	98
115°	164	199	456	908	1034	161
125°	225	256	413	696	821	201
135°	271	301	402	567	639	210
145°	313	336	396	482	518	197
155°	354	367	394	432	445	163
165°	384	389	395	412	413	108
175°	398	399	396	401	400	38
180°	398	398	398	398	398	

TEST NUMBER: P562667

CATALOG NUMBER: SQ4-PC3-050U-100D-935-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1840.5	1840.5	1840.5	1840.5	1840.5
2.5°	1851.4	1835.4	1840.5	1836.2	1829.6
5°	1847.3	1829.0	1835.4	1830.2	1828.6
7.5°	1834.0	1815.7	1824.1	1820.7	1819.0
10°	1821.7	1803.4	1813.2	1809.8	1808.1
12.5°	1805.4	1788.4	1799.6	1796.2	1795.8
15°	1777.4	1762.4	1777.4	1777.4	1775.7
17.5°	1742.3	1728.7	1744.7	1745.7	1744.7
20°	1717.8	1702.8	1722.9	1721.2	1722.9
22.5°	1687.8	1675.5	1697.0	1692.6	1694.3
25°	1641.1	1629.4	1653.0	1647.9	1647.9
27.5°	1585.9	1577.6	1603.3	1597.8	1597.8
30°	1549.1	1540.7	1567.8	1561.0	1561.0
32.5°	1508.2	1502.5	1528.3	1520.1	1520.1
35°	1443.4	1440.1	1465.6	1455.3	1455.3
37.5°	1376.6	1373.6	1396.7	1384.4	1380.4
40°	1327.5	1325.9	1346.3	1332.6	1332.6
42.5°	1278.5	1276.8	1294.5	1278.1	1278.1
45°	1203.1	1199.8	1211.7	1196.2	1192.9
47.5°	1121.0	1117.7	1125.1	1108.3	1106.7
50°	1065.1	1061.8	1065.1	1049.7	1048.1
52.5°	1007.8	1001.8	1002.4	987.0	986.7
55°	920.2	908.6	908.3	894.7	894.7
57.5°	827.5	812.2	813.6	801.9	800.3
60°	763.5	746.8	748.1	737.9	736.2
62.5°	700.7	681.4	685.4	673.8	673.5
65°	596.5	583.1	584.5	579.4	579.4
67.5°	496.2	483.9	492.8	488.7	488.4
70°	422.6	414.3	426.0	426.0	424.3
72.5°	354.5	354.1	368.8	368.8	369.8
75°	257.3	269.0	284.6	286.3	286.3
77.5°	171.8	192.4	209.6	210.3	210.0
80°	122.7	146.0	161.9	165.3	163.6
82.5°	83.2	107.8	121.0	124.4	122.7
85°	37.5	57.5	68.2	69.8	68.2
87.5°	11.2	23.9	29.1	29.5	26.8
90°	1.3	5.0	8.9	11.5	11.5
92.5°	11.5	52.3	90.8	39.0	33.0
95°	28.1	104.4	332.4	144.7	97.2
97.5°	46.5	115.3	509.6	396.5	278.5
100°	58.8	122.6	563.8	571.5	461.5
102.5°	71.1	129.8	578.1	706.9	609.8
105°	92.1	143.3	570.2	868.2	817.0
107.5°	113.8	159.0	537.2	951.5	965.8
110°	129.1	170.4	512.7	967.9	1029.2



TEST NUMBER: P562667

CATALOG NUMBER: SQ4-PC3-050U-100D-935-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	142.4	181.7	488.1	954.3	1046.6
115°	163.6	198.7	456.4	908.1	1034.3
117.5°	183.6	217.1	436.2	842.4	984.7
120°	196.9	229.4	427.0	798.4	939.7
122.5°	208.1	240.6	420.9	754.3	890.6
125°	225.0	256.3	413.0	695.8	820.8
127.5°	240.1	271.1	408.6	651.4	758.7
130°	249.3	279.3	406.6	623.5	719.8
132.5°	258.5	288.5	404.5	599.8	685.0
135°	271.0	301.0	401.5	566.7	639.3
137.5°	284.6	311.8	399.9	537.6	598.6
140°	292.8	319.0	398.9	519.0	574.0
142.5°	301.0	325.2	397.9	504.5	550.5
145°	313.2	335.7	396.3	481.5	517.8
147.5°	327.0	346.3	395.1	463.5	492.0
150°	336.2	352.5	395.1	453.1	475.6
152.5°	343.4	357.7	394.0	443.8	462.3
155°	354.1	366.6	393.8	432.4	444.9
157.5°	364.6	374.4	393.8	424.7	434.2
160°	370.8	379.5	393.8	419.5	427.0
162.5°	376.9	383.7	394.8	415.4	420.9
165°	383.6	388.6	395.1	411.7	413.0
167.5°	390.5	393.0	396.3	407.4	408.4
170°	392.5	395.0	396.3	405.3	405.3
172.5°	394.5	396.0	396.3	403.2	403.2
175°	397.6	398.9	396.3	401.4	400.2
177.5°	398.6	398.6	395.6	399.6	397.6
180°	397.6	397.6	397.6	397.6	397.6

(END OF REPORT)