

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562787

Luminaire Tested: **SQ4-PC3-075U-125D-935-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562787
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-075U-125D-935-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10313.5 lumens
Efficiency: N/A
Efficacy: 106.0 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 97.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562787
CATALOG NUMBER: SQ4-PC3-075U-125D-935-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P562787

CATALOG NUMBER: SQ4-PC3-075U-125D-935-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	60	58	57	53
2	92	84	78	73	86	79	73	69	69	65	62	61	57	55	52	50	48	44
3	84	74	66	60	78	70	63	57	61	56	52	54	50	46	46	43	41	37
4	76	65	57	51	71	62	54	49	54	49	44	48	43	40	42	38	35	32
5	70	58	50	44	66	55	47	42	49	43	38	43	38	34	37	34	31	28
6	65	52	44	38	60	49	42	36	44	38	33	39	34	30	34	30	27	24
7	60	47	39	33	56	45	37	32	40	34	29	35	30	27	31	27	24	21
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23	30	25	21	26	22	19	17
10	48	36	29	24	45	34	27	23	31	25	21	27	23	19	24	20	17	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14446	14446	14446
5°	14555	14461	14408
10°	14520	14452	14411
15°	14443	14443	14430
20°	14348	14391	14391
25°	14213	14316	14272
30°	14040	14210	14148
35°	13831	14044	13945
40°	13602	13794	13655
45°	13356	13450	13242
50°	13006	13006	12798
55°	12594	12430	12243
60°	11985	11744	11557
65°	11079	10856	10761
70°	9699	9778	9738
75°	7804	8631	8684
80°	5547	7318	7396
85°	3373	6140	6140



TEST NUMBER: P562787

CATALOG NUMBER: SQ4-PC3-075U-125D-935-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	222.3	2.2
10°-20°	637.9	6.2
20°-30°	966.0	9.4
30°-40°	1158.1	11.2
40°-50°	1180.8	11.4
50°-60°	1030.8	10.0
60°-70°	738.0	7.2
70°-80°	380.1	3.7
80°-90°	97.6	0.9
90°-100°	282.5	2.7
100°-110°	777.2	7.5
110°-120°	802.2	7.8
120°-130°	642.7	6.2
130°-140°	504.8	4.9
140°-150°	386.9	3.8
150°-160°	278.2	2.7
160°-170°	170.1	1.6
170°-180°	57.3	0.6
0°-30°	1826.1	17.7
0°-40°	2984.2	28.9
0°-60°	5195.9	50.4
0°-90°	6411.6	62.2
90°-120°	1861.9	18.1
90°-150°	3396.4	32.9
90°-180°	3902.0	37.8
0°-180°	10313.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2349	2349	2349	2349	2349	
5°	2357	2334	2342	2336	2334	224
15°	2268	2249	2268	2268	2266	640
25°	2094	2079	2110	2103	2103	964
35°	1842	1838	1870	1857	1857	1152
45°	1535	1531	1546	1527	1522	1182
55°	1174	1160	1159	1142	1142	1047
65°	761	744	746	739	739	753
75°	328	343	363	365	365	355
85°	48	73	87	89	87	65
90°	1	5	9	12	12	5
95°	42	154	500	214	136	44
105°	139	214	856	1304	1217	146
115°	246	300	687	1368	1552	243
125°	339	386	623	1054	1235	302
135°	409	454	605	852	965	316
145°	473	505	596	726	782	296
155°	535	553	593	653	672	246
165°	579	586	595	619	623	163
175°	599	600	596	604	603	57
180°	599	599	599	599	599	

TEST NUMBER: P562787

CATALOG NUMBER: SQ4-PC3-075U-125D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2348.7	2348.7	2348.7	2348.7	2348.7
2.5°	2362.6	2342.2	2348.7	2343.3	2334.8
5°	2357.4	2334.0	2342.2	2335.6	2333.5
7.5°	2340.4	2317.0	2327.8	2323.4	2321.3
10°	2324.8	2301.4	2313.9	2309.5	2307.4
12.5°	2303.9	2282.2	2296.5	2292.1	2291.7
15°	2268.2	2249.1	2268.2	2268.2	2266.1
17.5°	2223.4	2206.0	2226.5	2227.8	2226.5
20°	2192.1	2173.0	2198.6	2196.5	2198.6
22.5°	2153.8	2138.1	2165.6	2160.0	2162.1
25°	2094.3	2079.4	2109.5	2103.0	2103.0
27.5°	2023.8	2013.2	2046.0	2039.0	2039.0
30°	1976.8	1966.2	2000.7	1992.0	1992.0
32.5°	1924.6	1917.4	1950.3	1939.9	1939.9
35°	1842.0	1837.7	1870.3	1857.2	1857.2
37.5°	1756.7	1752.9	1782.4	1766.6	1761.5
40°	1694.1	1692.0	1718.0	1700.6	1700.6
42.5°	1631.5	1629.4	1651.9	1631.0	1631.0
45°	1535.4	1531.1	1546.2	1526.6	1522.3
47.5°	1430.5	1426.3	1435.8	1414.4	1412.3
50°	1359.2	1354.9	1359.2	1339.6	1337.5
52.5°	1286.1	1278.5	1279.2	1259.6	1259.2
55°	1174.4	1159.5	1159.1	1141.7	1141.7
57.5°	1056.0	1036.5	1038.2	1023.4	1021.3
60°	974.3	953.0	954.7	941.6	939.5
62.5°	894.2	869.6	874.7	859.9	859.5
65°	761.2	744.1	745.9	739.4	739.4
67.5°	633.3	617.5	628.9	623.7	623.3
70°	539.3	528.7	543.7	543.6	541.5
72.5°	452.3	451.9	470.6	470.6	471.9
75°	328.4	343.3	363.2	365.4	365.4
77.5°	219.2	245.6	267.5	268.4	267.9
80°	156.6	186.3	206.6	210.9	208.8
82.5°	106.1	137.6	154.4	158.7	156.6
85°	47.8	73.4	87.0	89.1	87.0
87.5°	14.2	30.2	36.6	37.0	33.6
90°	1.3	5.0	8.9	11.5	11.5
92.5°	17.6	75.2	130.2	50.0	41.0
95°	42.1	154.2	499.5	213.6	136.4
97.5°	68.6	171.0	762.3	587.4	414.4
100°	87.9	181.4	844.9	852.8	695.8
102.5°	106.3	193.8	866.3	1058.0	914.0
105°	138.9	213.7	856.4	1304.2	1217.0
107.5°	170.0	238.3	807.7	1424.8	1450.7
110°	192.4	254.7	771.0	1454.8	1544.5

TEST NUMBER: P562787

CATALOG NUMBER: SQ4-PC3-075U-125D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	212.8	273.1	734.3	1435.5	1572.1
115°	246.0	299.5	686.9	1367.8	1552.2
117.5°	277.6	326.9	656.8	1272.7	1481.3
120°	296.9	344.3	643.6	1201.5	1417.1
122.5°	314.3	361.6	634.4	1139.1	1343.7
125°	339.0	386.3	623.2	1054.2	1234.9
127.5°	362.4	407.5	615.8	983.3	1141.8
130°	374.7	420.8	611.7	941.2	1085.8
132.5°	388.9	435.0	608.6	904.2	1034.8
135°	409.1	453.9	605.3	852.5	964.7
137.5°	427.9	469.5	602.5	810.8	903.3
140°	442.2	480.8	601.5	783.1	866.6
142.5°	454.4	490.1	599.5	758.3	829.9
145°	472.8	505.2	596.4	726.4	782.5
147.5°	492.4	520.3	594.9	698.1	743.0
150°	504.6	529.6	593.9	682.6	717.5
152.5°	515.9	538.8	592.8	669.2	698.1
155°	535.2	552.7	592.6	652.9	671.6
157.5°	549.2	563.5	592.6	639.5	652.5
160°	559.4	570.7	592.6	632.3	642.3
162.5°	567.6	576.8	593.6	626.1	634.1
165°	578.6	586.0	595.1	619.4	623.2
167.5°	586.2	591.9	596.4	613.8	614.8
170°	591.3	595.0	596.4	611.7	611.7
172.5°	595.4	597.1	596.4	608.6	607.6
175°	598.9	600.2	596.4	604.0	602.8
177.5°	600.0	600.0	595.9	602.0	600.0
180°	598.9	598.9	598.9	598.9	598.9

(END OF REPORT)