

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P562931

Luminaire Tested: **SQ4-PC3-100U-075D-935-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562931
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-100U-075D-935-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9016.7 lumens
Efficiency: N/A
Efficacy: 115.6 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 78
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562931
CATALOG NUMBER: SQ4-PC3-100U-075D-935-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P562931

CATALOG NUMBER: SQ4-PC3-100U-075D-935-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42
1	96	92	88	85	87	84	81	78	69	67	65	56	54	53	43	42	41	35
2	87	80	74	69	80	73	68	64	61	57	54	49	46	44	38	36	35	30
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	34	31	30	25
4	73	62	54	48	66	57	50	45	47	42	38	38	35	32	30	27	25	22
5	67	55	47	41	61	51	44	39	42	37	33	34	30	27	27	24	22	19
6	61	50	42	36	56	46	39	33	38	33	29	31	27	24	24	22	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	18	15	13
9	49	37	29	24	45	34	27	23	29	23	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	20	26	21	18	22	18	15	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8520	8520	8520
5°	8584	8529	8497
10°	8563	8523	8499
15°	8518	8518	8510
20°	8462	8488	8488
25°	8382	8443	8417
30°	8281	8381	8344
35°	8157	8282	8224
40°	8022	8135	8053
45°	7877	7932	7810
50°	7670	7670	7548
55°	7427	7331	7220
60°	7069	6926	6816
65°	6533	6402	6347
70°	5721	5766	5744
75°	4603	5090	5121
80°	3269	4314	4360
85°	1990	3620	3620



TEST NUMBER: P562931

CATALOG NUMBER: SQ4-PC3-100U-075D-935-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.1	1.5
10°-20°	376.2	4.2
20°-30°	569.7	6.3
30°-40°	683.0	7.6
40°-50°	696.4	7.7
50°-60°	607.9	6.7
60°-70°	435.2	4.8
70°-80°	224.2	2.5
80°-90°	58.4	0.6
90°-100°	377.3	4.2
100°-110°	1041.6	11.6
110°-120°	1074.2	11.9
120°-130°	863.2	9.6
130°-140°	678.4	7.5
140°-150°	520.3	5.8
150°-160°	373.9	4.1
160°-170°	228.7	2.5
170°-180°	77.1	0.9
0°-30°	1077.0	11.9
0°-40°	1760.0	19.5
0°-60°	3064.3	34.0
0°-90°	3782.1	41.9
90°-120°	2493.0	27.6
90°-150°	4554.9	50.5
90°-180°	5235.0	58.1
0°-180°	9016.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1385	1385	1385	1385	1385	
5°	1390	1376	1381	1377	1376	132
15°	1338	1326	1338	1338	1336	377
25°	1235	1226	1244	1240	1240	568
35°	1086	1084	1103	1095	1095	679
45°	906	903	912	900	898	697
55°	693	684	684	673	673	617
65°	449	439	440	436	436	444
75°	194	202	214	216	216	209
85°	28	43	51	53	51	38
90°	3	5	10	12	13	5
95°	55	204	684	281	183	59
105°	186	286	1146	1750	1647	197
115°	333	402	923	1827	2078	327
125°	456	519	837	1416	1662	406
135°	549	608	813	1147	1293	425
145°	637	681	803	976	1051	399
155°	718	742	797	876	904	331
165°	777	787	800	832	838	219
175°	806	807	802	813	811	77
180°	806	806	806	806	806	

TEST NUMBER: P562931

CATALOG NUMBER: SQ4-PC3-100U-075D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1385.2	1385.2	1385.2	1385.2	1385.2
2.5°	1393.4	1381.3	1385.2	1382.0	1377.0
5°	1390.3	1376.5	1381.3	1377.4	1376.2
7.5°	1380.3	1366.5	1372.9	1370.3	1369.0
10°	1371.1	1357.3	1364.7	1362.1	1360.8
12.5°	1358.8	1346.0	1354.4	1351.8	1351.6
15°	1337.7	1326.4	1337.7	1337.7	1336.4
17.5°	1311.3	1301.0	1313.1	1313.8	1313.1
20°	1292.8	1281.5	1296.7	1295.4	1296.7
22.5°	1270.3	1261.0	1277.2	1273.9	1275.1
25°	1235.1	1226.3	1244.1	1240.2	1240.2
27.5°	1193.6	1187.3	1206.6	1202.5	1202.5
30°	1165.9	1159.6	1180.0	1174.8	1174.8
32.5°	1135.1	1130.8	1150.2	1144.0	1144.0
35°	1086.3	1083.8	1103.0	1095.3	1095.3
37.5°	1036.1	1033.8	1051.2	1041.9	1038.9
40°	999.1	997.9	1013.2	1003.0	1003.0
42.5°	962.2	960.9	974.2	961.9	961.9
45°	905.5	903.0	911.9	900.3	897.8
47.5°	843.7	841.2	846.8	834.2	832.9
50°	801.6	799.1	801.6	790.0	788.8
52.5°	758.5	754.0	754.4	742.9	742.6
55°	692.6	683.8	683.6	673.3	673.3
57.5°	622.8	611.3	612.3	603.5	602.3
60°	574.6	562.0	563.0	555.3	554.1
62.5°	527.4	512.8	515.8	507.1	506.9
65°	448.9	438.9	439.9	436.1	436.1
67.5°	373.5	364.2	370.9	367.8	367.6
70°	318.1	311.8	320.6	320.6	319.4
72.5°	266.8	266.5	277.5	277.6	278.3
75°	193.7	202.4	214.2	215.5	215.5
77.5°	129.3	144.8	157.8	158.3	158.0
80°	92.3	109.9	121.8	124.4	123.1
82.5°	62.6	81.1	91.1	93.6	92.3
85°	28.2	43.3	51.3	52.6	51.3
87.5°	8.7	18.3	22.6	22.8	21.0
90°	2.6	5.1	10.3	11.6	12.9
92.5°	23.2	96.3	172.2	62.8	49.0
95°	55.4	204.2	684.5	281.4	183.0
97.5°	91.8	228.7	1013.9	780.6	565.4
100°	118.6	243.4	1135.6	1143.7	929.4
102.5°	144.4	260.1	1159.3	1413.1	1209.9
105°	185.6	286.4	1145.9	1749.5	1647.4
107.5°	229.4	319.2	1082.0	1911.7	1949.0
110°	260.4	341.0	1032.5	1946.6	2067.6



TEST NUMBER: P562931

CATALOG NUMBER: SQ4-PC3-100U-075D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	288.2	365.9	986.1	1919.0	2097.5
115°	332.6	401.9	922.9	1827.1	2077.9
117.5°	371.2	440.3	881.4	1697.7	1983.0
120°	397.0	465.1	864.9	1610.1	1897.4
122.5°	421.8	486.8	851.5	1528.3	1800.5
125°	456.3	519.3	836.6	1415.8	1661.6
127.5°	485.7	548.7	827.8	1320.7	1532.6
130°	505.3	568.3	823.7	1262.5	1455.3
132.5°	523.9	583.9	819.6	1213.6	1388.3
135°	549.1	608.4	813.4	1146.7	1292.9
137.5°	577.5	631.4	810.3	1090.5	1215.3
140°	593.0	645.9	808.2	1053.0	1162.7
142.5°	610.5	659.4	806.2	1019.7	1116.3
145°	636.8	680.9	803.1	976.2	1050.6
147.5°	662.0	700.6	800.2	939.5	997.2
150°	680.6	712.1	799.2	917.6	964.2
152.5°	695.0	724.5	798.2	898.8	937.4
155°	718.0	741.9	796.6	875.9	903.6
157.5°	739.1	757.5	796.9	859.2	878.1
160°	751.5	767.9	797.9	849.8	863.6
162.5°	761.8	776.2	798.9	841.5	852.3
165°	777.3	787.4	800.5	831.6	837.9
167.5°	789.1	795.2	801.8	825.5	827.6
170°	795.3	800.4	801.8	822.4	822.4
172.5°	800.5	803.5	801.8	818.2	817.2
175°	805.6	806.9	801.8	813.3	810.8
177.5°	807.7	806.7	801.5	808.7	806.7
180°	805.6	805.6	805.6	805.6	805.6

(END OF REPORT)