

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519683

Luminaire Tested: **SQ4-050U-0D-935-1D-UNV-STD-W-12**

Issue Date: 4/29/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P519683  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21)  
Test Lab: INNOVATION CENTER  
Issue Date: 4/29/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-050U-0D-935-1D-UNV-STD-W-12  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5192.3 lumens  
Efficiency: N/A  
Efficacy: 198.2 lumens/watt  
N/A  
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')  
CIE Type: Indirect

Input Watts (W): 26.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P519683  
CATALOG NUMBER: SQ4-050U-0D-935-1D-UNV-STD-W-12

### Luminous Intensity Polar Plot





TEST NUMBER: P519683

CATALOG NUMBER: SQ4-050U-0D-935-1D-UNV-STD-W-12

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20								20				20				20	
RC	80								50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
95°	1987	23458	6856
100°	2083	19970	16349
105°	2188	13551	19415
110°	2323	9220	18509
115°	2382	6643	15053
120°	2422	5253	11560
125°	2413	4428	8802
130°	2386	3890	6888
135°	2358	3492	5561
140°	2351	3203	4609
145°	2352	2976	3888
150°	2388	2806	3378
155°	2403	2673	3019
160°	2427	2578	2795
165°	2442	2516	2630
170°	2451	2475	2531
175°	2455	2447	2471



TEST NUMBER: P519683

CATALOG NUMBER: SQ4-050U-0D-935-1D-UNV-STD-W-12

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	381.7	7.4
100°-110°	1037.0	20.0
110°-120°	1066.3	20.5
120°-130°	852.5	16.4
130°-140°	669.8	12.9
140°-150°	513.6	9.9
150°-160°	369.4	7.1
160°-170°	225.9	4.4
170°-180°	76.1	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	2485.0	47.9
90°-150°	4521.0	87.1
90°-180°	5192.0	100.0
0°-180°	5192.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
90°	3	10	18	23	23	
95°	56	209	665	289	194	63
105°	184	287	1140	1736	1634	196
115°	327	397	913	1816	2069	323
125°	450	512	826	1392	1642	401
135°	542	602	803	1134	1278	419
145°	626	672	793	963	1036	393
155°	708	733	788	865	890	327
165°	767	777	790	823	826	217
175°	795	798	793	803	800	76
180°	795	795	795	795	795	



TEST NUMBER: P519683

CATALOG NUMBER: SQ4-050U-0D-935-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
90°	2.6	10.1	17.9	23.0	23.0
92.5°	23.0	104.5	181.5	78.0	66.0
95°	56.3	208.8	664.8	289.3	194.3
97.5°	93.1	230.6	1019.2	792.9	556.9
100°	117.6	245.1	1127.6	1143.1	923.1
102.5°	142.2	259.7	1156.3	1413.7	1219.7
105°	184.1	286.6	1140.4	1736.4	1633.9
107.5°	227.6	318.1	1074.5	1903.1	1931.6
110°	258.3	340.8	1025.4	1935.9	2058.4
112.5°	284.9	363.4	976.3	1908.7	2093.2
115°	327.3	397.3	912.9	1816.1	2068.6
117.5°	367.2	434.2	872.5	1684.9	1969.4
120°	393.8	458.8	854.0	1596.9	1879.4
122.5°	416.3	481.3	841.8	1508.7	1781.2
125°	450.0	512.5	825.9	1391.6	1641.6
127.5°	480.2	542.2	817.2	1302.8	1517.3
130°	498.6	558.6	813.1	1247.1	1439.6
132.5°	517.0	577.0	809.0	1199.5	1370.0
135°	542.1	602.1	802.9	1133.5	1278.5
137.5°	569.2	623.7	799.8	1075.2	1197.2
140°	585.6	638.1	797.8	1038.1	1148.1
142.5°	601.9	650.4	795.7	1009.0	1101.0
145°	626.5	671.5	792.7	963.1	1035.6
147.5°	654.1	692.6	790.1	926.9	983.9
150°	672.5	705.0	790.1	906.2	951.2
152.5°	686.8	715.3	788.1	887.6	924.6
155°	708.3	733.3	787.6	864.8	889.8
157.5°	729.3	748.8	787.6	849.4	868.4
160°	741.5	759.0	787.6	839.0	854.0
162.5°	753.8	767.3	789.6	830.8	841.8
165°	767.1	777.1	790.1	823.4	825.9
167.5°	780.9	785.9	792.7	814.7	816.7
170°	785.0	790.0	792.7	810.6	810.6
172.5°	789.1	792.1	792.7	806.5	806.5
175°	795.2	797.7	792.7	802.8	800.3
177.5°	797.3	797.3	791.1	799.2	795.2
180°	795.2	795.2	795.2	795.2	795.2

(END OF REPORT)