

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563531

Luminaire Tested: **SQ4-PP3-0U-100D-935-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563531
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-0U-100D-935-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4975.5 lumens
Efficiency: N/A
Efficacy: 90.0 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Direct

Input Watts (W): 55.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563531
CATALOG NUMBER: SQ4-PP3-0U-100D-935-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563531

CATALOG NUMBER: SQ4-PP3-OU-100D-935-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	101	97	107	103	99	96	98	95	93	95	92	90	91	89	87	85
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74	72
3	92	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63	61
4	84	72	64	57	82	71	63	57	69	62	56	66	60	56	64	59	55	53
5	77	65	56	50	75	64	56	49	62	54	49	60	53	48	58	52	48	46
6	72	59	50	44	70	58	49	43	56	49	43	54	48	43	53	47	42	40
7	66	53	45	39	65	52	44	39	51	44	38	49	43	38	48	42	38	36
8	62	49	40	35	60	48	40	34	47	39	34	45	39	34	44	38	34	32
9	58	45	37	31	56	44	36	31	43	36	31	42	35	31	41	35	31	29
10	54	41	34	28	53	41	33	28	40	33	28	39	33	28	38	32	28	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11957	11957	11957
5°	12045	11971	11929
10°	12024	11939	11886
15°	11945	11880	11815
20°	11866	11799	11709
25°	11725	11644	11528
30°	11508	11447	11302
35°	11207	11130	10989
40°	10848	10780	10656
45°	10552	10477	10374
50°	10173	10108	10010
55°	9647	9519	9445
60°	8782	8530	8488
65°	7737	7414	7389
70°	6679	6404	6404
75°	5749	5668	5587
80°	5069	5129	5009
85°	3966	4326	4326



TEST NUMBER: P563531

CATALOG NUMBER: SQ4-PP3-0U-100D-935-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.8	3.7
10°-20°	524.9	10.5
20°-30°	786.2	15.8
30°-40°	922.2	18.5
40°-50°	925.0	18.6
50°-60°	789.1	15.9
60°-70°	514.7	10.3
70°-80°	258.2	5.2
80°-90°	71.4	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1494.9	30.0
0°-40°	2417.0	48.6
0°-60°	4131.2	83.0
0°-90°	4975.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4975.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1944	1944	1944	1944	1944	
5°	1951	1932	1939	1932	1932	185
15°	1876	1858	1866	1859	1855	529
25°	1728	1708	1716	1700	1699	794
35°	1492	1478	1482	1465	1464	932
45°	1213	1205	1204	1193	1193	934
55°	900	896	888	882	881	799
65°	532	522	509	506	508	531
75°	242	242	238	237	235	262
85°	56	61	61	61	61	68
90°	0	0	0	0	0	



TEST NUMBER: P563531

CATALOG NUMBER: SQ4-PP3-OU-100D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1944.0	1944.0	1944.0	1944.0	1944.0
2.5°	1956.2	1940.2	1944.0	1941.1	1933.1
5°	1950.8	1932.5	1938.9	1932.0	1932.0
7.5°	1937.5	1917.5	1923.9	1917.0	1916.7
10°	1925.2	1905.2	1911.6	1904.8	1903.1
12.5°	1907.5	1887.5	1895.2	1887.1	1886.7
15°	1875.8	1857.5	1865.6	1858.7	1855.4
17.5°	1840.0	1820.1	1829.8	1820.3	1818.9
20°	1812.8	1792.8	1802.6	1788.9	1788.9
22.5°	1780.1	1760.1	1771.2	1753.5	1753.5
25°	1727.6	1707.6	1715.7	1700.3	1698.6
27.5°	1665.2	1645.6	1654.0	1636.6	1636.3
30°	1620.3	1601.9	1611.7	1593.0	1591.3
32.5°	1571.2	1554.2	1561.3	1542.5	1540.9
35°	1492.5	1477.5	1482.3	1465.2	1463.5
37.5°	1409.7	1394.4	1399.8	1385.1	1384.5
40°	1351.1	1341.1	1342.6	1330.6	1327.2
42.5°	1296.6	1285.2	1286.7	1274.7	1274.1
45°	1213.1	1204.7	1204.5	1192.6	1192.6
47.5°	1124.5	1118.1	1116.3	1106.4	1106.1
50°	1063.1	1058.1	1056.3	1047.8	1046.1
52.5°	999.1	996.7	990.9	983.7	983.4
55°	899.6	896.2	887.7	882.5	880.8
57.5°	791.6	784.9	775.2	767.7	769.1
60°	713.9	707.2	693.4	690.0	690.0
62.5°	638.9	630.9	617.1	612.4	615.1
65°	531.6	521.6	509.4	506.1	507.7
67.5°	434.1	425.1	412.0	411.9	410.6
70°	371.4	366.4	356.1	356.1	356.1
72.5°	315.5	313.2	305.7	305.6	304.3
75°	241.9	241.9	238.5	236.8	235.1
77.5°	181.3	181.9	180.3	178.5	175.5
80°	143.1	146.4	144.8	143.1	141.4
82.5°	107.7	111.0	110.7	107.7	107.3
85°	56.2	61.2	61.3	61.3	61.3
87.5°	15.0	20.3	21.8	21.8	23.2
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)