

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519779

Luminaire Tested: **SQ4-150U-0D-935-1D-UNV-STD-W-12**

Issue Date: 4/29/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P519779  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25)  
Test Lab: INNOVATION CENTER  
Issue Date: 4/29/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-150U-0D-935-1D-UNV-STD-W-12  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 15702.5 lumens  
Efficiency: N/A  
Efficacy: 136.0 lumens/watt  
N/A  
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')  
CIE Type: Indirect

Input Watts (W): 115.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P519779  
CATALOG NUMBER: SQ4-150U-0D-935-1D-UNV-STD-W-12

### Luminous Intensity Polar Plot





TEST NUMBER: P519779

CATALOG NUMBER: SQ4-150U-0D-935-1D-UNV-STD-W-12

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20								20				20				20				20
RC	80								50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10				0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10				0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8				0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7				0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6				0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5				0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4				0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4				0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3				0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3				0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3				0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2				0

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
95°	6196	66419	20445
100°	6408	57759	48706
105°	6760	40341	57069
110°	7095	28005	53818
115°	7288	20489	44775
120°	7385	16174	35040
125°	7352	13607	26975
130°	7237	11941	21135
135°	7149	10741	17023
140°	7136	9851	14103
145°	7175	9144	11959
150°	7243	8593	10380
155°	7321	8193	9305
160°	7422	7911	8554
165°	7479	7721	8063
170°	7507	7581	7761
175°	7527	7494	7575



TEST NUMBER: P519779

CATALOG NUMBER: SQ4-150U-0D-935-1D-UNV-STD-W-12

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	1131.9	7.2
100°-110°	3060.3	19.5
110°-120°	3217.5	20.5
120°-130°	2613.5	16.6
130°-140°	2050.0	13.1
140°-150°	1573.4	10.0
150°-160°	1131.6	7.2
160°-170°	691.3	4.4
170°-180°	233.1	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	7409.7	47.2
90°-150°	13646.6	86.9
90°-180°	15703.0	100.0
0°-180°	15702.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
90°	5	16	34	37	34	
95°	176	616	1882	974	579	195
105°	569	879	3395	5008	4803	599
115°	1002	1224	2816	5451	6153	989
125°	1371	1571	2538	4282	5031	1222
135°	1644	1839	2470	3458	3914	1270
145°	1911	2055	2436	2960	3185	1196
155°	2158	2242	2414	2655	2742	995
165°	2349	2372	2425	2520	2532	662
175°	2438	2436	2428	2459	2454	231
180°	2436	2436	2436	2436	2436	



TEST NUMBER: P519779

CATALOG NUMBER: SQ4-150U-OD-935-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
90°	5.2	15.5	34.1	36.6	34.1
92.5°	74.5	271.3	535.3	232.4	168.3
95°	175.6	616.5	1882.3	974.1	579.4
97.5°	282.1	707.1	2934.1	2428.2	1783.2
100°	361.8	743.7	3261.3	3401.2	2750.1
102.5°	435.2	794.6	3376.7	4139.0	3651.9
105°	568.9	879.1	3395.0	5007.9	4802.8
107.5°	692.6	975.6	3246.6	5550.0	5618.1
110°	789.1	1045.4	3114.5	5695.5	5985.2
112.5°	875.1	1115.0	2992.8	5666.4	6153.0
115°	1001.5	1224.5	2815.6	5450.6	6153.0
117.5°	1125.2	1334.4	2698.7	5120.8	5917.0
120°	1200.7	1405.8	2629.5	4884.2	5696.8
122.5°	1272.0	1473.0	2587.5	4630.6	5449.3
125°	1371.1	1571.1	2537.7	4282.4	5030.9
127.5°	1462.3	1658.7	2508.4	3998.3	4656.5
130°	1512.7	1715.2	2495.8	3822.7	4417.4
132.5°	1565.1	1765.6	2483.2	3664.4	4211.9
135°	1643.8	1838.6	2469.6	3457.8	3914.1
137.5°	1722.9	1907.0	2458.0	3290.2	3661.9
140°	1777.5	1949.2	2453.8	3182.3	3513.0
142.5°	1829.9	1991.4	2445.5	3084.9	3374.6
145°	1911.2	2054.7	2435.5	2959.7	3185.3
147.5°	1985.1	2112.2	2424.0	2846.3	3019.6
150°	2039.6	2152.4	2419.8	2784.7	2923.1
152.5°	2090.0	2188.4	2417.7	2727.5	2841.3
155°	2157.6	2242.2	2414.5	2655.1	2742.2
157.5°	2227.9	2286.8	2415.0	2604.6	2662.0
160°	2267.7	2316.4	2417.1	2572.7	2613.8
162.5°	2299.2	2339.7	2419.2	2547.3	2578.1
165°	2349.0	2372.0	2425.0	2519.7	2532.5
167.5°	2383.1	2399.0	2425.5	2495.9	2502.1
170°	2404.0	2411.7	2427.6	2485.3	2485.3
172.5°	2420.8	2422.3	2427.6	2472.7	2470.6
175°	2438.1	2435.5	2427.6	2459.0	2453.8
177.5°	2443.9	2437.7	2427.1	2447.9	2441.8
180°	2435.5	2435.5	2435.5	2435.5	2435.5

(END OF REPORT)