

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563723

Luminaire Tested: **SQ4-PP3-125U-100D-935-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563723
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-125U-100D-935-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11493.7 lumens
Efficiency: N/A
Efficacy: 111.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 102.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563723
CATALOG NUMBER: SQ4-PP3-125U-100D-935-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563723

CATALOG NUMBER: SQ4-PP3-125U-100D-935-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43
1	96	92	88	85	88	85	81	78	70	68	66	57	55	54	44	43	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	47	45	39	38	36	31
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31	26
4	73	63	55	49	67	58	51	46	48	43	39	39	36	33	31	29	27	23
5	67	56	48	42	61	52	45	39	43	38	34	35	32	28	28	25	23	20
6	62	50	42	37	57	46	39	34	39	34	30	32	28	25	26	23	20	17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	21	18	16	14
9	49	37	30	25	45	35	28	24	29	24	21	24	20	18	20	17	15	12
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11957	11957	11957
5°	12045	11971	11929
10°	12024	11939	11886
15°	11945	11880	11815
20°	11866	11799	11709
25°	11725	11644	11528
30°	11508	11447	11302
35°	11207	11130	10989
40°	10848	10780	10656
45°	10552	10477	10374
50°	10173	10108	10010
55°	9647	9519	9445
60°	8782	8530	8488
65°	7737	7414	7389
70°	6679	6404	6404
75°	5749	5668	5587
80°	5069	5129	5009
85°	3966	4326	4326



TEST NUMBER: P563723

CATALOG NUMBER: SQ4-PP3-125U-100D-935-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.8	1.6
10°-20°	524.9	4.6
20°-30°	786.2	6.8
30°-40°	922.2	8.0
40°-50°	925.0	8.0
50°-60°	789.1	6.9
60°-70°	514.7	4.5
70°-80°	258.2	2.2
80°-90°	73.8	0.6
90°-100°	472.2	4.1
100°-110°	1271.9	11.1
110°-120°	1334.8	11.6
120°-130°	1083.2	9.4
130°-140°	849.5	7.4
140°-150°	652.2	5.7
150°-160°	468.9	4.1
160°-170°	286.5	2.5
170°-180°	96.6	0.8
0°-30°	1494.9	13.0
0°-40°	2417.0	21.0
0°-60°	4131.2	35.9
0°-90°	4977.9	43.3
90°-120°	3078.9	26.8
90°-150°	5663.8	49.3
90°-180°	6516.0	56.7
0°-180°	11493.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1944	1944	1944	1944	1944	
5°	1951	1932	1939	1932	1932	185
15°	1876	1858	1866	1859	1855	529
25°	1728	1708	1716	1700	1699	794
35°	1492	1478	1482	1465	1464	932
45°	1213	1205	1204	1193	1193	934
55°	900	896	888	882	881	799
65°	532	522	509	506	508	531
75°	242	242	238	237	235	262
85°	56	61	61	61	61	66
90°	3	8	15	17	17	7
95°	72	257	774	396	274	75
105°	235	366	1407	2104	1975	247
115°	415	508	1171	2263	2560	409
125°	567	651	1052	1778	2092	506
135°	683	762	1022	1434	1624	527
145°	790	851	1009	1226	1317	495
155°	896	929	1000	1100	1135	413
165°	972	983	1004	1044	1049	274
175°	1011	1009	1006	1020	1017	96
180°	1009	1009	1009	1009	1009	

TEST NUMBER: P563723

CATALOG NUMBER: SQ4-PP3-125U-100D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1944.0	1944.0	1944.0	1944.0	1944.0
2.5°	1956.2	1940.2	1944.0	1941.1	1933.1
5°	1950.8	1932.5	1938.9	1932.0	1932.0
7.5°	1937.5	1917.5	1923.9	1917.0	1916.7
10°	1925.2	1905.2	1911.6	1904.8	1903.1
12.5°	1907.5	1887.5	1895.2	1887.1	1886.7
15°	1875.8	1857.5	1865.6	1858.7	1855.4
17.5°	1840.0	1820.1	1829.8	1820.3	1818.9
20°	1812.8	1792.8	1802.6	1788.9	1788.9
22.5°	1780.1	1760.1	1771.2	1753.5	1753.5
25°	1727.6	1707.6	1715.7	1700.3	1698.6
27.5°	1665.2	1645.6	1654.0	1636.6	1636.3
30°	1620.3	1601.9	1611.7	1593.0	1591.3
32.5°	1571.2	1554.2	1561.3	1542.5	1540.9
35°	1492.5	1477.5	1482.3	1465.2	1463.5
37.5°	1409.7	1394.4	1399.8	1385.1	1384.5
40°	1351.1	1341.1	1342.6	1330.6	1327.2
42.5°	1296.6	1285.2	1286.7	1274.7	1274.1
45°	1213.1	1204.7	1204.5	1192.6	1192.6
47.5°	1124.5	1118.1	1116.3	1106.4	1106.1
50°	1063.1	1058.1	1056.3	1047.8	1046.1
52.5°	999.1	996.7	990.9	983.7	983.4
55°	899.6	896.2	887.7	882.5	880.8
57.5°	791.6	784.9	775.2	767.7	769.1
60°	713.9	707.2	693.4	690.0	690.0
62.5°	638.9	630.9	617.1	612.4	615.1
65°	531.6	521.6	509.4	506.1	507.7
67.5°	434.1	425.1	412.0	411.9	410.6
70°	371.4	366.4	356.1	356.1	356.1
72.5°	315.5	313.2	305.7	305.6	304.3
75°	241.9	241.9	238.5	236.8	235.1
77.5°	181.3	181.9	180.3	178.5	175.5
80°	143.1	146.4	144.8	143.1	141.4
82.5°	107.7	111.0	110.7	107.7	107.3
85°	56.2	61.2	61.3	61.3	61.3
87.5°	15.5	21.8	24.9	25.2	26.5
90°	2.6	7.6	15.4	16.7	16.7
92.5°	31.4	110.8	219.1	105.5	73.3
95°	72.0	256.8	774.0	395.8	273.9
97.5°	114.9	294.0	1214.0	1014.2	764.8
100°	147.9	308.8	1353.9	1416.6	1175.2
102.5°	179.8	329.6	1400.2	1717.9	1519.8
105°	235.3	366.0	1406.6	2104.4	1974.9
107.5°	287.8	404.4	1346.7	2303.1	2336.5
110°	322.7	433.4	1292.2	2364.7	2486.7



TEST NUMBER: P563723

CATALOG NUMBER: SQ4-PP3-125U-100D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	359.8	462.3	1239.7	2351.1	2551.5
115°	415.3	508.3	1171.3	2263.3	2560.0
117.5°	466.0	553.2	1118.4	2123.1	2453.5
120°	498.9	583.1	1091.6	2022.5	2362.0
122.5°	527.7	610.9	1072.1	1919.6	2258.1
125°	567.0	651.3	1051.8	1777.6	2091.9
127.5°	604.8	687.8	1038.9	1652.4	1933.0
130°	627.5	710.4	1033.8	1580.7	1827.1
132.5°	650.1	732.1	1028.6	1517.5	1743.8
135°	682.7	761.9	1022.2	1434.1	1623.9
137.5°	713.9	789.8	1018.8	1363.4	1519.3
140°	735.5	808.4	1015.8	1319.8	1460.6
142.5°	758.1	826.0	1013.7	1279.2	1397.9
145°	789.5	851.1	1009.3	1226.1	1316.6
147.5°	823.4	877.0	1005.0	1181.4	1252.6
150°	846.0	892.6	1002.9	1153.4	1212.5
152.5°	866.6	907.1	1001.9	1130.5	1178.5
155°	896.2	928.9	1000.3	1100.1	1135.3
157.5°	922.2	947.5	1000.6	1078.8	1102.4
160°	938.6	960.0	1001.6	1066.3	1083.9
162.5°	953.0	970.4	1002.6	1055.9	1068.5
165°	972.0	983.4	1004.2	1044.2	1049.2
167.5°	987.5	994.0	1005.5	1035.1	1037.1
170°	997.8	1000.3	1005.5	1029.9	1029.9
172.5°	1003.9	1004.4	1006.5	1024.8	1024.8
175°	1010.6	1009.4	1005.5	1019.6	1017.0
177.5°	1013.4	1011.4	1006.2	1014.4	1012.4
180°	1009.3	1009.3	1009.3	1009.3	1009.3

(END OF REPORT)