

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563771

Luminaire Tested: **SQ4-PP3-150U-050D-935-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563771  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-150U-050D-935-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 10394.4 lumens  
Efficiency: N/A  
Efficacy: 123.6 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 84.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563771  
CATALOG NUMBER: SQ4-PP3-150U-050D-935-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P563771

CATALOG NUMBER: SQ4-PP3-150U-050D-935-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	24
1	92	88	84	81	82	78	75	73	61	59	57	44	43	42	29	28	28	21
2	84	77	71	66	74	69	64	60	53	50	47	39	37	35	26	24	23	18
3	77	68	61	55	68	60	55	50	47	43	40	34	32	30	23	21	20	15
4	70	60	52	46	62	53	47	42	42	37	34	31	28	25	20	19	17	13
5	64	53	45	40	57	48	41	36	37	32	29	27	24	22	18	16	15	11
6	59	47	40	34	52	43	36	31	33	29	25	25	21	19	17	15	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12	9
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	14	12	10	8
9	47	35	28	23	42	32	25	21	25	20	17	19	15	13	13	11	9	7
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6106	6106	6106
5°	6150	6113	6092
10°	6140	6096	6070
15°	6100	6066	6033
20°	6059	6025	5979
25°	5987	5946	5887
30°	5876	5845	5771
35°	5722	5683	5611
40°	5539	5505	5441
45°	5388	5350	5297
50°	5195	5161	5112
55°	4926	4861	4823
60°	4484	4356	4334
65°	3950	3786	3774
70°	3412	3269	3269
75°	2935	2895	2854
80°	2589	2618	2557
85°	2025	2209	2209



TEST NUMBER: P563771

CATALOG NUMBER: SQ4-PP3-150U-050D-935-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	93.9	0.9
10°-20°	268.0	2.6
20°-30°	401.5	3.9
30°-40°	470.9	4.5
40°-50°	472.4	4.5
50°-60°	403.0	3.9
60°-70°	262.8	2.5
70°-80°	131.8	1.3
80°-90°	39.0	0.4
90°-100°	565.9	5.4
100°-110°	1530.2	14.7
110°-120°	1608.7	15.5
120°-130°	1306.7	12.6
130°-140°	1025.0	9.9
140°-150°	786.7	7.6
150°-160°	565.8	5.4
160°-170°	345.6	3.3
170°-180°	116.5	1.1
0°-30°	763.3	7.3
0°-40°	1234.2	11.9
0°-60°	2109.5	20.3
0°-90°	2543.2	24.5
90°-120°	3704.8	35.6
90°-150°	6823.3	65.6
90°-180°	7851.0	75.5
0°-180°	10394.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	993	993	993	993	993	
5°	996	987	990	987	987	95
15°	958	948	953	949	947	270
25°	882	872	876	868	867	406
35°	762	754	757	748	747	476
45°	619	615	615	609	609	477
55°	459	458	453	451	450	408
65°	271	266	260	258	259	271
75°	124	124	122	121	120	134
85°	29	31	31	31	31	34
90°	3	8	17	18	17	7
95°	88	308	941	487	290	92
105°	284	440	1698	2504	2401	300
115°	501	612	1408	2725	3076	494
125°	686	786	1269	2141	2515	611
135°	822	919	1235	1729	1957	635
145°	956	1027	1218	1480	1593	598
155°	1079	1121	1207	1328	1371	498
165°	1174	1186	1212	1260	1266	331
175°	1219	1218	1214	1230	1227	116
180°	1218	1218	1218	1218	1218	



TEST NUMBER: P563771

CATALOG NUMBER: SQ4-PP3-150U-050D-935-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	992.7	992.7	992.7	992.7	992.7
2.5°	998.9	990.8	992.7	991.2	987.1
5°	996.1	986.8	990.0	986.6	986.6
7.5°	989.4	979.1	982.4	978.9	978.7
10°	983.1	972.9	976.1	972.6	971.8
12.5°	974.0	963.8	967.8	963.6	963.4
15°	957.9	948.5	952.6	949.1	947.4
17.5°	939.6	929.4	934.4	929.5	928.8
20°	925.7	915.5	920.4	913.5	913.5
22.5°	909.0	898.8	904.4	895.4	895.4
25°	882.2	872.0	876.1	868.2	867.4
27.5°	850.3	840.3	844.6	835.7	835.5
30°	827.4	818.0	823.0	813.4	812.6
32.5°	802.3	793.6	797.3	787.7	786.8
35°	762.1	754.5	756.9	748.2	747.3
37.5°	719.8	712.0	714.8	707.3	707.0
40°	689.9	684.8	685.6	679.4	677.7
42.5°	662.1	656.3	657.0	650.9	650.6
45°	619.4	615.2	615.1	609.0	609.0
47.5°	574.2	571.0	570.0	565.0	564.8
50°	542.9	540.3	539.4	535.0	534.2
52.5°	510.2	509.0	506.0	502.3	502.2
55°	459.4	457.7	453.3	450.6	449.8
57.5°	404.2	400.8	395.8	392.0	392.7
60°	364.5	361.1	354.1	352.3	352.3
62.5°	326.2	322.2	315.1	312.7	314.1
65°	271.4	266.3	260.1	258.4	259.3
67.5°	221.7	217.1	210.4	210.3	209.7
70°	189.7	187.1	181.8	181.8	181.8
72.5°	161.1	159.9	156.1	156.1	155.4
75°	123.5	123.5	121.8	120.9	120.1
77.5°	92.6	92.9	92.0	91.1	89.6
80°	73.1	74.8	73.9	73.1	72.2
82.5°	55.0	56.7	56.5	55.0	54.8
85°	28.7	31.3	31.3	31.3	31.3
87.5°	8.2	11.9	14.5	14.8	15.2
90°	2.6	7.7	17.0	18.3	17.0
92.5°	37.2	135.7	267.7	116.2	84.2
95°	87.8	308.3	941.2	487.1	289.7
97.5°	141.0	353.5	1467.1	1214.1	891.6
100°	180.9	371.9	1630.7	1700.6	1375.0
102.5°	217.6	397.3	1688.3	2069.5	1826.0
105°	284.4	439.5	1697.5	2503.9	2401.4
107.5°	346.3	487.8	1623.3	2775.0	2809.1
110°	394.6	522.7	1557.2	2847.8	2992.6



TEST NUMBER: P563771

CATALOG NUMBER: SQ4-PP3-150U-050D-935-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	437.5	557.5	1496.4	2833.2	3076.5
115°	500.7	612.2	1407.8	2725.3	3076.5
117.5°	562.6	667.2	1349.4	2560.4	2958.5
120°	600.4	702.9	1314.7	2442.1	2848.4
122.5°	636.0	736.5	1293.8	2315.3	2724.7
125°	685.6	785.5	1268.9	2141.2	2515.4
127.5°	731.2	829.3	1254.2	1999.1	2328.3
130°	756.3	857.6	1247.9	1911.4	2208.7
132.5°	782.6	882.8	1241.6	1832.2	2106.0
135°	821.9	919.3	1234.8	1728.9	1957.0
137.5°	861.5	953.5	1229.0	1645.1	1830.9
140°	888.7	974.6	1226.9	1591.2	1756.5
142.5°	914.9	995.7	1222.7	1542.4	1687.3
145°	955.6	1027.4	1217.7	1479.8	1592.6
147.5°	992.5	1056.1	1212.0	1423.2	1509.8
150°	1019.8	1076.2	1209.9	1392.3	1461.6
152.5°	1045.0	1094.2	1208.8	1363.8	1420.7
155°	1078.8	1121.1	1207.3	1327.5	1371.1
157.5°	1113.9	1143.4	1207.5	1302.3	1331.0
160°	1133.9	1158.2	1208.6	1286.4	1306.9
162.5°	1149.6	1169.8	1209.6	1273.7	1289.1
165°	1174.5	1186.0	1212.5	1259.8	1266.2
167.5°	1191.5	1199.5	1212.8	1248.0	1251.0
170°	1202.0	1205.9	1213.8	1242.7	1242.7
172.5°	1210.4	1211.2	1213.8	1236.3	1235.3
175°	1219.1	1217.8	1213.8	1229.5	1226.9
177.5°	1221.9	1218.9	1213.6	1224.0	1220.9
180°	1217.7	1217.7	1217.7	1217.7	1217.7

(END OF REPORT)