

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563891

Luminaire Tested: **SQ4-PR1-025U-075D-935-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563891
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-025U-075D-935-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4982.4 lumens
Efficiency: N/A
Efficacy: 102.5 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 48.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563891
CATALOG NUMBER: SQ4-PR1-025U-075D-935-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563891

CATALOG NUMBER: SQ4-PR1-025U-075D-935-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	113	113	113	113	107	107	107	107	97	97	97	88	88	88	79	79	79	75				
1	104	99	96	92	99	95	91	88	86	83	81	78	76	74	70	69	67	64				
2	95	87	81	76	90	83	78	73	76	71	68	69	65	62	62	60	58	54				
3	87	77	70	64	82	74	67	62	67	62	57	61	57	53	56	52	49	46				
4	80	69	61	54	76	66	58	53	60	54	49	55	50	46	50	46	43	40				
5	73	62	53	47	70	59	51	46	54	48	43	50	44	40	45	41	38	35				
6	68	55	47	41	64	53	46	40	49	43	38	45	40	35	41	37	33	31				
7	63	50	42	36	60	48	41	35	45	38	33	41	36	32	38	33	30	27				
8	58	46	38	32	56	44	37	32	41	34	30	38	32	28	35	30	27	25				
9	55	42	34	29	52	40	33	28	37	31	27	35	29	26	32	27	24	22				
10	51	39	31	26	49	37	30	26	35	29	24	32	27	23	30	25	22	20				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9159	9159	9159
5°	9242	9170	9123
10°	9212	9148	9100
15°	9172	9114	9065
20°	9125	9067	8999
25°	9061	9000	8896
30°	8963	8900	8772
35°	8831	8754	8629
40°	8630	8537	8383
45°	8278	8133	7966
50°	7658	7474	7327
55°	6684	6533	6396
60°	5633	5585	5474
65°	4871	4890	4854
70°	4474	4498	4498
75°	4297	4297	4328
80°	4042	4088	4042
85°	3260	3620	3620



TEST NUMBER: P563891

CATALOG NUMBER: SQ4-PR1-025U-075D-935-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.8	2.8
10°-20°	402.9	8.1
20°-30°	607.7	12.2
30°-40°	724.0	14.5
40°-50°	713.8	14.3
50°-60°	545.6	10.9
60°-70°	337.6	6.8
70°-80°	191.7	3.8
80°-90°	59.4	1.2
90°-100°	94.7	1.9
100°-110°	248.9	5.0
110°-120°	258.1	5.2
120°-130°	207.0	4.2
130°-140°	162.4	3.3
140°-150°	124.6	2.5
150°-160°	89.8	1.8
160°-170°	54.9	1.1
170°-180°	18.6	0.4
0°-30°	1151.4	23.1
0°-40°	1875.4	37.6
0°-60°	3134.8	62.9
0°-90°	3723.5	74.7
90°-120°	601.6	12.1
90°-150°	1095.7	22.0
90°-180°	1259.0	25.3
0°-180°	4982.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1489	1489	1489	1489	1489	
5°	1497	1480	1485	1480	1478	142
15°	1440	1425	1431	1426	1424	406
25°	1335	1319	1326	1312	1311	614
35°	1176	1162	1166	1150	1149	734
45°	952	939	935	918	916	729
55°	623	613	609	599	596	559
65°	335	332	336	334	334	339
75°	181	181	181	182	182	191
85°	46	49	51	51	51	54
90°	1	4	10	5	5	3
95°	12	49	163	84	57	14
105°	45	68	275	418	390	48
115°	80	97	220	440	502	79
125°	111	124	200	339	400	98
135°	132	145	194	274	310	102
145°	153	163	192	233	252	96
155°	173	178	192	211	217	80
165°	187	189	192	199	202	53
175°	194	194	193	196	196	18
180°	194	194	194	194	194	

TEST NUMBER: P563891

CATALOG NUMBER: SQ4-PR1-025U-075D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1489.1	1489.1	1489.1	1489.1	1489.1
2.5°	1498.3	1485.2	1489.1	1485.8	1478.8
5°	1496.8	1480.4	1485.2	1480.0	1477.5
7.5°	1485.2	1469.2	1473.9	1468.8	1467.3
10°	1474.9	1459.9	1464.7	1459.5	1457.0
12.5°	1463.7	1447.6	1453.4	1447.2	1444.7
15°	1440.3	1425.3	1431.3	1426.2	1423.6
17.5°	1414.7	1398.6	1404.7	1398.7	1395.4
20°	1394.1	1379.1	1385.2	1376.2	1374.9
22.5°	1371.6	1356.5	1362.6	1350.5	1350.3
25°	1335.1	1318.8	1326.2	1312.0	1310.8
27.5°	1291.8	1276.7	1282.8	1268.4	1266.9
30°	1262.0	1247.0	1253.1	1237.6	1235.1
32.5°	1228.2	1214.1	1219.2	1203.8	1202.3
35°	1176.1	1162.3	1165.9	1150.4	1149.2
37.5°	1116.9	1104.3	1106.3	1089.4	1088.1
40°	1074.8	1062.2	1063.2	1045.3	1044.0
42.5°	1028.6	1016.1	1015.0	997.0	995.8
45°	951.7	939.1	935.0	918.3	915.8
47.5°	863.9	851.4	843.7	830.0	828.3
50°	800.3	787.8	781.1	769.5	765.7
52.5°	731.6	719.0	713.4	702.8	699.0
55°	623.3	613.3	609.2	598.9	596.4
57.5°	520.5	513.7	512.5	502.5	501.5
60°	457.9	454.1	454.0	445.0	445.0
62.5°	404.5	401.8	403.8	397.8	396.8
65°	334.7	332.2	336.0	333.5	333.5
67.5°	279.6	279.6	281.9	280.9	280.9
70°	248.8	248.8	250.1	250.1	250.1
72.5°	221.1	220.1	223.4	223.4	222.4
75°	180.8	180.8	180.8	182.1	182.1
77.5°	140.8	141.1	142.1	141.8	140.8
80°	114.1	115.4	115.4	114.1	114.1
82.5°	87.5	88.7	88.8	88.5	87.5
85°	46.2	48.7	51.3	51.3	51.3
87.5°	13.6	18.1	22.5	21.5	20.5
90°	1.2	3.7	10.0	5.0	5.0
92.5°	5.2	25.2	55.8	24.7	15.9
95°	12.5	49.0	163.1	84.1	57.3
97.5°	21.7	53.8	244.0	194.1	142.9
100°	28.6	57.9	268.9	272.5	211.7
102.5°	34.6	61.9	275.9	339.5	287.4
105°	44.8	68.0	275.2	417.7	389.7
107.5°	55.3	76.7	259.5	458.3	465.2
110°	62.3	81.7	246.5	468.8	498.0



TEST NUMBER: P563891

CATALOG NUMBER: SQ4-PR1-025U-075D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	69.2	87.7	234.6	462.2	507.0
115°	79.7	96.7	220.4	439.7	501.8
117.5°	89.9	105.5	210.7	408.5	477.4
120°	95.9	110.5	206.7	387.5	454.4
122.5°	101.8	116.5	203.7	366.6	432.5
125°	110.8	124.2	200.5	338.8	399.7
127.5°	118.0	131.7	197.7	316.4	367.8
130°	122.0	136.6	196.7	302.4	349.9
132.5°	126.0	140.6	195.7	290.3	332.9
135°	132.0	145.4	194.2	273.5	310.0
137.5°	138.2	151.3	194.0	260.9	290.8
140°	143.2	155.4	193.0	250.9	278.9
142.5°	147.2	158.4	193.0	243.8	267.9
145°	153.1	162.9	191.7	233.2	251.5
147.5°	159.1	168.6	191.7	224.5	239.6
150°	163.1	171.6	191.7	219.4	231.6
152.5°	167.1	173.7	191.7	215.4	224.6
155°	173.1	177.9	191.7	210.6	216.6
157.5°	177.5	182.2	191.7	206.3	210.7
160°	180.5	184.2	191.7	204.2	206.7
162.5°	183.5	186.2	191.7	202.3	204.7
165°	186.8	189.2	191.7	199.3	201.7
167.5°	189.7	191.0	193.0	198.0	199.0
170°	191.7	193.0	193.0	198.0	198.0
172.5°	192.7	193.0	193.0	196.9	196.0
175°	194.2	194.2	193.0	195.5	195.5
177.5°	194.2	194.2	193.2	195.2	194.2
180°	194.2	194.2	194.2	194.2	194.2

(END OF REPORT)