

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564155

Luminaire Tested: **SQ4-PR1-0U-050D-935-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P564155  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PR1-0U-050D-935-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2525.6 lumens  
Efficiency: N/A  
Efficacy: 94.6 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P564155  
CATALOG NUMBER: SQ4-PR1-0U-050D-935-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P564155

CATALOG NUMBER: SQ4-PR1-0U-050D-935-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	105	101	98	107	103	99	96	99	96	93	95	92	90	91	89	87	85				85
2	100	93	86	81	98	91	85	80	87	82	78	84	80	76	81	78	75	72				72
3	92	82	74	68	90	80	73	68	78	71	66	75	70	65	72	68	64	62				62
4	85	73	65	58	82	72	64	58	69	63	57	67	61	56	65	60	56	54				54
5	78	66	57	51	76	65	57	50	63	55	50	61	54	49	59	53	49	47				47
6	72	59	51	45	70	58	50	44	57	49	44	55	49	44	53	48	43	41				41
7	67	54	46	40	65	53	45	39	52	44	39	50	44	39	49	43	39	37				37
8	63	49	41	35	61	49	41	35	47	40	35	46	40	35	45	39	35	33				33
9	58	45	37	32	57	45	37	32	44	37	32	43	36	32	42	36	31	30				30
10	55	42	34	29	54	41	34	29	40	34	29	40	33	29	39	33	29	27				27

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6214	6214	6214
5°	6270	6222	6190
10°	6250	6207	6174
15°	6223	6184	6151
20°	6191	6152	6106
25°	6148	6107	6035
30°	6082	6038	5952
35°	5992	5939	5855
40°	5855	5792	5687
45°	5617	5518	5404
50°	5196	5071	4971
55°	4535	4432	4339
60°	3822	3789	3715
65°	3305	3318	3294
70°	3036	3052	3052
75°	2916	2916	2937
80°	2742	2773	2742
85°	2209	2456	2456



TEST NUMBER: P564155

CATALOG NUMBER: SQ4-PR1-0U-050D-935-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	95.5	3.8
10°-20°	273.3	10.8
20°-30°	412.3	16.3
30°-40°	491.2	19.5
40°-50°	484.3	19.2
50°-60°	370.1	14.7
60°-70°	229.1	9.1
70°-80°	130.1	5.2
80°-90°	39.6	1.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	781.2	30.9
0°-40°	1272.4	50.4
0°-60°	2126.9	84.2
0°-90°	2525.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2525.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1010	1010	1010	1010	1010	
5°	1016	1004	1008	1004	1002	96
15°	977	967	971	968	966	276
25°	906	895	900	890	889	417
35°	798	789	791	780	780	498
45°	646	637	634	623	621	495
55°	423	416	413	406	405	379
65°	227	225	228	226	226	230
75°	123	123	123	124	124	130
85°	31	33	35	35	35	38
90°	0	0	0	0	0	



TEST NUMBER: P564155

CATALOG NUMBER: SQ4-PR1-0U-050D-935-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1010.3	1010.3	1010.3	1010.3	1010.3
2.5°	1016.6	1007.7	1010.3	1008.1	1003.3
5°	1015.5	1004.5	1007.7	1004.2	1002.5
7.5°	1007.7	996.8	1000.0	996.5	995.5
10°	1000.7	990.5	993.8	990.2	988.5
12.5°	993.1	982.2	986.1	981.9	980.2
15°	977.2	967.0	971.1	967.6	965.9
17.5°	959.8	948.9	953.0	949.0	946.8
20°	945.9	935.7	939.8	933.7	932.8
22.5°	930.6	920.4	924.5	916.3	916.1
25°	905.9	894.8	899.8	890.2	889.3
27.5°	876.5	866.2	870.4	860.6	859.6
30°	856.3	846.1	850.2	839.7	838.0
32.5°	833.3	823.8	827.2	816.7	815.7
35°	798.0	788.6	791.0	780.5	779.7
37.5°	757.8	749.3	750.6	739.1	738.3
40°	729.2	720.7	721.4	709.2	708.3
42.5°	697.9	689.4	688.7	676.5	675.6
45°	645.7	637.2	634.4	623.0	621.3
47.5°	586.2	577.7	572.4	563.2	562.0
50°	543.0	534.5	529.9	522.1	519.5
52.5°	496.4	487.8	484.0	476.8	474.3
55°	422.9	416.1	413.3	406.3	404.6
57.5°	353.1	348.5	347.7	340.9	340.2
60°	310.7	308.1	308.0	302.0	302.0
62.5°	274.5	272.6	273.9	269.9	269.2
65°	227.1	225.4	228.0	226.3	226.3
67.5°	189.7	189.7	191.3	190.6	190.6
70°	168.8	168.8	169.7	169.7	169.7
72.5°	150.0	149.3	151.6	151.6	150.9
75°	122.7	122.7	122.7	123.6	123.6
77.5°	95.5	95.7	96.4	96.2	95.5
80°	77.4	78.3	78.3	77.4	77.4
82.5°	59.3	60.2	60.2	60.0	59.3
85°	31.3	33.0	34.8	34.8	34.8
87.5°	9.1	11.8	13.9	13.9	13.2
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)