

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564227

Luminaire Tested: **SQ4-PR1-0U-125D-935-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P564227  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PR1-0U-125D-935-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.  
DOWNLIGHT 1250 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6311.8 lumens  
Efficiency: N/A  
Efficacy: 90.6 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: Direct

Input Watts (W): 69.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P564227  
CATALOG NUMBER: SQ4-PR1-0U-125D-935-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P564227

CATALOG NUMBER: SQ4-PR1-0U-125D-935-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	110	105	101	98	107	103	99	96	99	96	93	95	92	90	91	89	87	85				
2	100	93	86	81	98	91	85	80	87	82	78	84	80	76	81	78	75	72				
3	92	82	74	68	90	80	73	68	78	71	66	75	70	65	72	68	64	62				
4	85	73	65	58	82	72	64	58	69	63	57	67	61	56	65	60	56	54				
5	78	66	57	51	76	65	57	50	63	55	50	61	54	49	59	53	49	47				
6	72	59	51	45	70	58	50	44	57	49	44	55	49	44	53	48	43	41				
7	67	54	46	40	65	53	45	39	52	44	39	50	44	39	49	43	39	37				
8	63	49	41	35	61	49	41	35	47	40	35	46	40	35	45	39	35	33				
9	58	45	37	32	57	45	37	32	44	37	32	43	36	32	42	36	31	30				
10	55	42	34	29	54	41	34	29	40	34	29	40	33	29	39	33	29	27				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15530	15530	15530
5°	15670	15549	15468
10°	15620	15511	15430
15°	15551	15455	15371
20°	15473	15374	15260
25°	15364	15261	15084
30°	15198	15090	14874
35°	14974	14843	14631
40°	14633	14475	14213
45°	14036	13791	13506
50°	12985	12673	12423
55°	11334	11077	10844
60°	9551	9471	9283
65°	8261	8293	8229
70°	7587	7627	7627
75°	7286	7286	7339
80°	6854	6932	6854
85°	5526	6140	6140



TEST NUMBER: P564227

CATALOG NUMBER: SQ4-PR1-0U-125D-935-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	238.8	3.8
10°-20°	683.1	10.8
20°-30°	1030.4	16.3
30°-40°	1227.7	19.5
40°-50°	1210.4	19.2
50°-60°	925.0	14.7
60°-70°	572.5	9.1
70°-80°	325.1	5.2
80°-90°	98.9	1.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1952.3	30.9
0°-40°	3179.9	50.4
0°-60°	5315.4	84.2
0°-90°	6311.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6311.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2525	2525	2525	2525	2525	
5°	2538	2510	2518	2510	2505	241
15°	2442	2417	2427	2418	2414	689
25°	2264	2236	2249	2225	2223	1042
35°	1994	1971	1977	1951	1948	1245
45°	1614	1592	1585	1557	1553	1236
55°	1057	1040	1033	1016	1011	947
65°	568	563	570	565	565	575
75°	307	307	307	309	309	324
85°	78	82	87	87	87	94
90°	0	0	0	0	0	



TEST NUMBER: P564227

CATALOG NUMBER: SQ4-PR1-0U-125D-935-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2524.8	2524.8	2524.8	2524.8	2524.8
2.5°	2540.5	2518.4	2524.8	2519.4	2507.5
5°	2537.9	2510.3	2518.3	2509.5	2505.3
7.5°	2518.3	2491.1	2499.2	2490.4	2487.9
10°	2500.9	2475.4	2483.5	2474.7	2470.5
12.5°	2481.8	2454.6	2464.4	2453.9	2449.6
15°	2442.2	2416.7	2427.0	2418.2	2413.9
17.5°	2398.7	2371.5	2381.8	2371.6	2366.1
20°	2363.9	2338.4	2348.7	2333.4	2331.3
22.5°	2325.6	2300.1	2310.4	2290.0	2289.5
25°	2263.9	2236.2	2248.7	2224.7	2222.6
27.5°	2190.4	2164.9	2175.2	2150.7	2148.2
30°	2139.9	2114.4	2124.7	2098.5	2094.3
32.5°	2082.5	2058.7	2067.3	2041.1	2038.6
35°	1994.2	1970.8	1976.8	1950.7	1948.5
37.5°	1893.7	1872.5	1875.9	1847.2	1845.0
40°	1822.4	1801.2	1802.8	1772.3	1770.2
42.5°	1744.1	1722.9	1721.1	1690.6	1688.5
45°	1613.6	1592.4	1585.4	1557.0	1552.7
47.5°	1464.9	1443.6	1430.5	1407.4	1404.4
50°	1357.0	1335.8	1324.4	1304.7	1298.3
52.5°	1240.5	1219.2	1209.6	1191.6	1185.2
55°	1056.9	1039.9	1033.0	1015.5	1011.2
57.5°	882.5	871.0	869.0	852.0	850.3
60°	776.4	770.0	769.9	754.6	754.6
62.5°	685.9	681.2	684.6	674.6	672.9
65°	567.6	563.3	569.8	565.4	565.4
67.5°	474.1	474.1	478.0	476.3	476.3
70°	421.9	421.9	424.1	424.1	424.1
72.5°	374.9	373.2	378.8	378.8	377.1
75°	306.6	306.6	306.6	308.8	308.8
77.5°	238.8	239.2	241.0	240.5	238.8
80°	193.5	195.7	195.7	193.5	193.5
82.5°	148.3	150.4	150.5	150.0	148.3
85°	78.3	82.5	87.0	87.0	87.0
87.5°	22.6	29.4	34.8	34.8	33.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)