

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564275

Luminaire Tested: **SQ4-PR1-100U-075D-935-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P564275  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2106-289-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PR1-100U-075D-935-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 1000 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8958.8 lumens  
Efficiency: N/A  
Efficacy: 114.9 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 78  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P564275  
CATALOG NUMBER: SQ4-PR1-100U-075D-935-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P564275

CATALOG NUMBER: SQ4-PR1-100U-075D-935-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	42
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	35
2	88	81	75	70	80	74	69	64	61	57	54	49	47	44	38	37	35	30
3	80	71	64	58	73	65	59	54	54	49	46	44	40	38	34	32	30	26
4	73	63	55	49	67	58	51	46	48	43	39	39	35	33	31	28	26	22
5	67	56	48	42	61	52	45	39	43	38	34	35	31	28	28	25	23	19
6	62	50	42	37	56	46	39	34	39	33	29	32	28	25	25	22	20	17
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	34	28	48	38	31	27	32	27	23	26	22	20	21	18	16	14
9	49	38	30	25	45	35	28	24	29	24	21	24	20	18	19	17	15	12
10	46	34	27	23	42	32	25	21	27	22	19	22	19	16	18	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9159	9159	9159
5°	9242	9170	9123
10°	9212	9148	9100
15°	9172	9114	9065
20°	9125	9067	8999
25°	9061	9000	8896
30°	8963	8900	8772
35°	8831	8754	8629
40°	8630	8537	8383
45°	8278	8133	7966
50°	7658	7474	7327
55°	6684	6533	6396
60°	5633	5585	5474
65°	4871	4890	4854
70°	4474	4498	4498
75°	4297	4297	4328
80°	4042	4088	4042
85°	3260	3620	3620



TEST NUMBER: P564275

CATALOG NUMBER: SQ4-PR1-100U-075D-935-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	140.8	1.6
10°-20°	402.9	4.5
20°-30°	607.7	6.8
30°-40°	724.0	8.1
40°-50°	713.8	8.0
50°-60°	545.6	6.1
60°-70°	337.6	3.8
70°-80°	191.7	2.1
80°-90°	60.0	0.7
90°-100°	377.3	4.2
100°-110°	1041.6	11.6
110°-120°	1074.2	12.0
120°-130°	863.2	9.6
130°-140°	678.4	7.6
140°-150°	520.3	5.8
150°-160°	373.9	4.2
160°-170°	228.7	2.6
170°-180°	77.1	0.9
0°-30°	1151.4	12.9
0°-40°	1875.4	20.9
0°-60°	3134.8	35.0
0°-90°	3724.1	41.6
90°-120°	2493.0	27.8
90°-150°	4554.9	50.8
90°-180°	5235.0	58.4
0°-180°	8958.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1489	1489	1489	1489	1489	
5°	1497	1480	1485	1480	1478	142
15°	1440	1425	1431	1426	1424	406
25°	1335	1319	1326	1312	1311	614
35°	1176	1162	1166	1150	1149	734
45°	952	939	935	918	916	729
55°	623	613	609	599	596	559
65°	335	332	336	334	334	339
75°	181	181	181	182	182	191
85°	46	49	51	51	51	54
90°	3	5	10	12	13	6
95°	55	204	684	281	183	59
105°	186	286	1146	1750	1647	197
115°	333	402	923	1827	2078	327
125°	456	519	837	1416	1662	406
135°	549	608	813	1147	1293	425
145°	637	681	803	976	1051	399
155°	718	742	797	876	904	331
165°	777	787	800	832	838	219
175°	806	807	802	813	811	77
180°	806	806	806	806	806	



TEST NUMBER: P564275

CATALOG NUMBER: SQ4-PR1-100U-075D-935-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1489.1	1489.1	1489.1	1489.1	1489.1
2.5°	1498.3	1485.2	1489.1	1485.8	1478.8
5°	1496.8	1480.4	1485.2	1480.0	1477.5
7.5°	1485.2	1469.2	1473.9	1468.8	1467.3
10°	1474.9	1459.9	1464.7	1459.5	1457.0
12.5°	1463.7	1447.6	1453.4	1447.2	1444.7
15°	1440.3	1425.3	1431.3	1426.2	1423.6
17.5°	1414.7	1398.6	1404.7	1398.7	1395.4
20°	1394.1	1379.1	1385.2	1376.2	1374.9
22.5°	1371.6	1356.5	1362.6	1350.5	1350.3
25°	1335.1	1318.8	1326.2	1312.0	1310.8
27.5°	1291.8	1276.7	1282.8	1268.4	1266.9
30°	1262.0	1247.0	1253.1	1237.6	1235.1
32.5°	1228.2	1214.1	1219.2	1203.8	1202.3
35°	1176.1	1162.3	1165.9	1150.4	1149.2
37.5°	1116.9	1104.3	1106.3	1089.4	1088.1
40°	1074.8	1062.2	1063.2	1045.3	1044.0
42.5°	1028.6	1016.1	1015.0	997.0	995.8
45°	951.7	939.1	935.0	918.3	915.8
47.5°	863.9	851.4	843.7	830.0	828.3
50°	800.3	787.8	781.1	769.5	765.7
52.5°	731.6	719.0	713.4	702.8	699.0
55°	623.3	613.3	609.2	598.9	596.4
57.5°	520.5	513.7	512.5	502.5	501.5
60°	457.9	454.1	454.0	445.0	445.0
62.5°	404.5	401.8	403.8	397.8	396.8
65°	334.7	332.2	336.0	333.5	333.5
67.5°	279.6	279.6	281.9	280.9	280.9
70°	248.8	248.8	250.1	250.1	250.1
72.5°	221.1	220.1	223.4	223.4	222.4
75°	180.8	180.8	180.8	182.1	182.1
77.5°	140.8	141.1	142.1	141.8	140.8
80°	114.1	115.4	115.4	114.1	114.1
82.5°	87.5	88.7	88.8	88.5	87.5
85°	46.2	48.7	51.3	51.3	51.3
87.5°	13.9	18.4	22.6	22.8	22.1
90°	2.6	5.1	10.3	11.6	12.9
92.5°	23.2	96.3	172.2	62.8	49.0
95°	55.4	204.2	684.5	281.4	183.0
97.5°	91.8	228.7	1013.9	780.6	565.4
100°	118.6	243.4	1135.6	1143.7	929.4
102.5°	144.4	260.1	1159.3	1413.1	1209.9
105°	185.6	286.4	1145.9	1749.5	1647.4
107.5°	229.4	319.2	1082.0	1911.7	1949.0
110°	260.4	341.0	1032.5	1946.6	2067.6



TEST NUMBER: P564275

CATALOG NUMBER: SQ4-PR1-100U-075D-935-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	288.2	365.9	986.1	1919.0	2097.5
115°	332.6	401.9	922.9	1827.1	2077.9
117.5°	371.2	440.3	881.4	1697.7	1983.0
120°	397.0	465.1	864.9	1610.1	1897.4
122.5°	421.8	486.8	851.5	1528.3	1800.5
125°	456.3	519.3	836.6	1415.8	1661.6
127.5°	485.7	548.7	827.8	1320.7	1532.6
130°	505.3	568.3	823.7	1262.5	1455.3
132.5°	523.9	583.9	819.6	1213.6	1388.3
135°	549.1	608.4	813.4	1146.7	1292.9
137.5°	577.5	631.4	810.3	1090.5	1215.3
140°	593.0	645.9	808.2	1053.0	1162.7
142.5°	610.5	659.4	806.2	1019.7	1116.3
145°	636.8	680.9	803.1	976.2	1050.6
147.5°	662.0	700.6	800.2	939.5	997.2
150°	680.6	712.1	799.2	917.6	964.2
152.5°	695.0	724.5	798.2	898.8	937.4
155°	718.0	741.9	796.6	875.9	903.6
157.5°	739.1	757.5	796.9	859.2	878.1
160°	751.5	767.9	797.9	849.8	863.6
162.5°	761.8	776.2	798.9	841.5	852.3
165°	777.3	787.4	800.5	831.6	837.9
167.5°	789.1	795.2	801.8	825.5	827.6
170°	795.3	800.4	801.8	822.4	822.4
172.5°	800.5	803.5	801.8	818.2	817.2
175°	805.6	806.9	801.8	813.3	810.8
177.5°	807.7	806.7	801.5	808.7	806.7
180°	805.6	805.6	805.6	805.6	805.6

(END OF REPORT)