

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564395

Luminaire Tested: **SQ4-PR1-125U-100D-935-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564395
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-125U-100D-935-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11464.3 lumens
Efficiency: N/A
Efficacy: 111.5 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 102.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564395
CATALOG NUMBER: SQ4-PR1-125U-100D-935-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P564395

CATALOG NUMBER: SQ4-PR1-125U-100D-935-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	
RCR																					
0	106	106	106	106	96	96	96	96	80	80	80	64	64	64	50	50	50	43			
1	96	92	89	85	88	85	81	78	70	68	66	57	55	54	44	43	43	37			
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	39	38	36	31			
3	80	71	64	59	73	65	59	54	55	50	46	44	41	39	35	33	31	27			
4	74	63	55	50	67	58	51	46	49	44	40	40	36	33	31	29	27	23			
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	28	26	24	20			
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18			
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	24	21	19	16			
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	22	19	17	14			
9	50	38	30	25	45	35	28	24	30	25	21	25	21	18	20	17	15	13			
10	46	35	27	23	42	32	26	21	27	22	19	23	19	16	19	16	14	12			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12169	12169	12169
5°	12279	12184	12121
10°	12240	12155	12091
15°	12187	12110	12045
20°	12125	12047	11957
25°	12040	11959	11820
30°	11910	11825	11656
35°	11734	11632	11465
40°	11467	11343	11138
45°	10999	10806	10584
50°	10176	9931	9735
55°	8881	8681	8497
60°	7484	7422	7274
65°	6474	6498	6449
70°	5945	5976	5976
75°	5711	5711	5751
80°	5373	5434	5373
85°	4326	4813	4813



TEST NUMBER: P564395

CATALOG NUMBER: SQ4-PR1-125U-100D-935-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.1	1.6
10°-20°	535.3	4.7
20°-30°	807.4	7.0
30°-40°	962.0	8.4
40°-50°	948.5	8.3
50°-60°	724.9	6.3
60°-70°	448.6	3.9
70°-80°	254.8	2.2
80°-90°	79.9	0.7
90°-100°	472.2	4.1
100°-110°	1271.9	11.1
110°-120°	1334.8	11.6
120°-130°	1083.2	9.4
130°-140°	849.5	7.4
140°-150°	652.2	5.7
150°-160°	468.9	4.1
160°-170°	286.5	2.5
170°-180°	96.6	0.8
0°-30°	1529.8	13.3
0°-40°	2491.9	21.7
0°-60°	4165.2	36.3
0°-90°	4948.5	43.2
90°-120°	3078.9	26.9
90°-150°	5663.8	49.4
90°-180°	6516.0	56.8
0°-180°	11464.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1978	1978	1978	1978	1978	
5°	1989	1967	1973	1966	1963	189
15°	1914	1894	1902	1895	1892	540
25°	1774	1752	1762	1743	1742	816
35°	1563	1544	1549	1529	1527	975
45°	1264	1248	1242	1220	1217	969
55°	828	815	810	796	792	742
65°	445	441	446	443	443	451
75°	240	240	240	242	242	254
85°	61	65	68	68	68	71
90°	3	8	15	17	17	8
95°	72	257	774	396	274	75
105°	235	366	1407	2104	1975	247
115°	415	508	1171	2263	2560	409
125°	567	651	1052	1778	2092	506
135°	683	762	1022	1434	1624	527
145°	790	851	1009	1226	1317	495
155°	896	929	1000	1100	1135	413
165°	972	983	1004	1044	1049	274
175°	1011	1009	1006	1020	1017	96
180°	1009	1009	1009	1009	1009	

TEST NUMBER: P564395

CATALOG NUMBER: SQ4-PR1-125U-100D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1978.5	1978.5	1978.5	1978.5	1978.5
2.5°	1990.8	1973.5	1978.5	1974.2	1964.9
5°	1988.7	1967.1	1973.4	1966.5	1963.2
7.5°	1973.4	1952.1	1958.4	1951.5	1949.5
10°	1959.8	1939.8	1946.1	1939.2	1935.9
12.5°	1944.8	1923.4	1931.1	1922.9	1919.6
15°	1913.8	1893.8	1901.8	1894.9	1891.6
17.5°	1879.7	1858.3	1866.4	1858.4	1854.1
20°	1852.4	1832.4	1840.5	1828.5	1826.8
22.5°	1822.4	1802.4	1810.5	1794.5	1794.1
25°	1774.0	1752.4	1762.1	1743.3	1741.6
27.5°	1716.4	1696.4	1704.5	1685.4	1683.4
30°	1676.9	1656.9	1665.0	1644.4	1641.1
32.5°	1631.9	1613.2	1620.0	1599.5	1597.5
35°	1562.7	1544.4	1549.1	1528.6	1526.9
37.5°	1484.0	1467.3	1470.0	1447.5	1445.8
40°	1428.1	1411.4	1412.7	1388.8	1387.2
42.5°	1366.7	1350.1	1348.7	1324.8	1323.1
45°	1264.5	1247.8	1242.3	1220.1	1216.8
47.5°	1147.9	1131.3	1121.0	1102.9	1100.5
50°	1063.4	1046.7	1037.8	1022.4	1017.4
52.5°	972.0	955.4	947.8	933.8	928.8
55°	828.2	814.9	809.5	795.8	792.4
57.5°	691.5	682.5	681.0	667.7	666.3
60°	608.4	603.4	603.3	591.3	591.3
62.5°	537.5	533.8	536.5	528.6	527.3
65°	444.8	441.4	446.5	443.1	443.1
67.5°	371.5	371.5	374.6	373.2	373.2
70°	330.6	330.6	332.3	332.3	332.3
72.5°	293.8	292.5	296.9	296.8	295.5
75°	240.3	240.3	240.3	242.0	242.0
77.5°	187.1	187.4	188.8	188.4	187.1
80°	151.7	153.3	153.4	151.7	151.7
82.5°	116.2	117.9	117.9	117.6	116.2
85°	61.3	64.7	68.2	68.2	68.2
87.5°	18.2	24.6	30.4	30.6	29.2
90°	2.6	7.6	15.4	16.7	16.7
92.5°	31.4	110.8	219.1	105.5	73.3
95°	72.0	256.8	774.0	395.8	273.9
97.5°	114.9	294.0	1214.0	1014.2	764.8
100°	147.9	308.8	1353.9	1416.6	1175.2
102.5°	179.8	329.6	1400.2	1717.9	1519.8
105°	235.3	366.0	1406.6	2104.4	1974.9
107.5°	287.8	404.4	1346.7	2303.1	2336.5
110°	322.7	433.4	1292.2	2364.7	2486.7



TEST NUMBER: P564395

CATALOG NUMBER: SQ4-PR1-125U-100D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	359.8	462.3	1239.7	2351.1	2551.5
115°	415.3	508.3	1171.3	2263.3	2560.0
117.5°	466.0	553.2	1118.4	2123.1	2453.5
120°	498.9	583.1	1091.6	2022.5	2362.0
122.5°	527.7	610.9	1072.1	1919.6	2258.1
125°	567.0	651.3	1051.8	1777.6	2091.9
127.5°	604.8	687.8	1038.9	1652.4	1933.0
130°	627.5	710.4	1033.8	1580.7	1827.1
132.5°	650.1	732.1	1028.6	1517.5	1743.8
135°	682.7	761.9	1022.2	1434.1	1623.9
137.5°	713.9	789.8	1018.8	1363.4	1519.3
140°	735.5	808.4	1015.8	1319.8	1460.6
142.5°	758.1	826.0	1013.7	1279.2	1397.9
145°	789.5	851.1	1009.3	1226.1	1316.6
147.5°	823.4	877.0	1005.0	1181.4	1252.6
150°	846.0	892.6	1002.9	1153.4	1212.5
152.5°	866.6	907.1	1001.9	1130.5	1178.5
155°	896.2	928.9	1000.3	1100.1	1135.3
157.5°	922.2	947.5	1000.6	1078.8	1102.4
160°	938.6	960.0	1001.6	1066.3	1083.9
162.5°	953.0	970.4	1002.6	1055.9	1068.5
165°	972.0	983.4	1004.2	1044.2	1049.2
167.5°	987.5	994.0	1005.5	1035.1	1037.1
170°	997.8	1000.3	1005.5	1029.9	1029.9
172.5°	1003.9	1004.4	1006.5	1024.8	1024.8
175°	1010.6	1009.4	1005.5	1019.6	1017.0
177.5°	1013.4	1011.4	1006.2	1014.4	1012.4
180°	1009.3	1009.3	1009.3	1009.3	1009.3

(END OF REPORT)