

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P564539

Luminaire Tested: **SQ4-PW1-025U-050D-935-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564539
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-025U-050D-935-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3772.9 lumens
Efficiency: N/A
Efficacy: 108.1 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 34.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564539
CATALOG NUMBER: SQ4-PW1-025U-050D-935-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P564539

CATALOG NUMBER: SQ4-PW1-025U-050D-935-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	71	71	71	67
1	102	97	93	90	96	92	88	85	82	79	77	72	70	68	63	62	61	56
2	93	85	79	74	87	80	75	70	72	67	64	63	60	57	56	53	51	47
3	85	75	67	61	79	71	64	59	63	58	54	56	52	49	50	46	44	40
4	78	66	58	52	73	63	56	50	56	50	46	50	45	42	44	41	38	35
5	71	59	51	45	67	56	49	43	50	44	40	45	40	36	40	36	33	30
6	66	53	45	39	62	51	43	38	46	39	35	41	36	32	36	32	29	26
7	61	48	40	34	57	46	38	33	41	35	31	37	32	28	33	29	26	23
8	57	44	36	30	53	42	35	29	38	32	27	34	29	25	31	26	23	21
9	53	40	32	27	50	38	31	26	35	29	25	31	26	23	28	24	21	19
10	49	37	30	25	47	35	28	24	32	26	22	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6075	6075	6075
5°	6114	6066	6039
10°	6065	6016	5984
15°	6001	5935	5912
20°	5930	5839	5827
25°	5847	5740	5723
30°	5723	5636	5599
35°	5560	5482	5449
40°	5387	5303	5282
45°	5177	5110	5087
50°	4962	4921	4888
55°	4731	4731	4656
60°	4442	4528	4367
65°	4065	4269	3965
70°	3584	3928	3491
75°	3061	3515	2978
80°	2373	2958	2405
85°	1538	2272	2025



TEST NUMBER: P564539

CATALOG NUMBER: SQ4-PW1-025U-050D-935-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.0	2.5
10°-20°	262.6	7.0
20°-30°	389.5	10.3
30°-40°	455.7	12.1
40°-50°	453.7	12.0
50°-60°	391.8	10.4
60°-70°	282.0	7.5
70°-80°	147.9	3.9
80°-90°	37.7	1.0
90°-100°	94.7	2.5
100°-110°	248.9	6.6
110°-120°	258.1	6.8
120°-130°	207.0	5.5
130°-140°	162.4	4.3
140°-150°	124.6	3.3
150°-160°	89.8	2.4
160°-170°	54.9	1.5
170°-180°	18.6	0.5
0°-30°	745.1	19.7
0°-40°	1200.8	31.8
0°-60°	2046.3	54.2
0°-90°	2513.9	66.6
90°-120°	601.6	15.9
90°-150°	1095.7	29.0
90°-180°	1259.0	33.4
0°-180°	3772.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	988	988	988	988	988	
5°	990	979	982	980	978	94
15°	942	930	932	930	928	266
25°	862	847	846	841	843	396
35°	740	730	730	723	726	463
45°	595	590	587	586	585	459
55°	441	440	441	435	434	394
65°	279	288	293	282	272	277
75°	129	141	148	138	125	138
85°	22	29	32	30	29	29
90°	1	4	10	5	5	2
95°	12	49	163	84	57	14
105°	45	68	275	418	390	48
115°	80	97	220	440	502	79
125°	111	124	200	339	400	98
135°	132	145	194	274	310	102
145°	153	163	192	233	252	96
155°	173	178	192	211	217	80
165°	187	189	192	199	202	53
175°	194	194	193	196	196	18
180°	194	194	194	194	194	

TEST NUMBER: P564539

CATALOG NUMBER: SQ4-PW1-025U-050D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	987.7	987.7	987.7	987.7	987.7
2.5°	993.2	985.1	987.7	985.5	980.7
5°	990.3	979.2	982.5	979.8	978.1
7.5°	980.2	970.0	972.4	969.5	968.5
10°	971.1	960.9	963.3	959.8	958.1
12.5°	960.7	949.8	952.2	948.7	947.6
15°	942.4	930.5	932.0	930.2	928.5
17.5°	921.2	909.1	909.4	906.6	906.2
20°	905.9	893.1	892.0	888.5	890.2
22.5°	889.2	875.7	874.5	869.7	872.1
25°	861.5	847.0	845.8	840.7	843.2
27.5°	829.5	815.2	815.2	808.0	810.7
30°	805.8	792.2	793.6	785.0	788.4
32.5°	780.7	768.5	769.3	760.6	764.0
35°	740.5	730.3	730.1	723.2	725.7
37.5°	699.5	690.4	689.0	685.0	685.7
40°	670.9	663.3	660.5	657.9	657.9
42.5°	641.0	634.0	631.2	629.3	628.6
45°	595.2	590.1	587.4	585.6	584.8
47.5°	550.0	545.2	542.8	541.6	540.7
50°	518.6	515.2	514.3	511.7	510.8
52.5°	487.3	485.3	484.4	481.0	480.2
55°	441.2	440.3	441.2	435.1	434.2
57.5°	393.2	394.5	397.3	389.1	387.1
60°	361.1	364.5	368.1	358.4	355.0
62.5°	328.4	333.9	338.9	327.8	323.0
65°	279.3	287.8	293.3	281.7	272.4
67.5°	232.0	242.5	249.1	236.6	226.1
70°	199.3	211.2	218.4	206.0	194.1
72.5°	170.7	184.0	189.9	178.1	166.2
75°	128.8	140.7	147.9	138.1	125.3
77.5°	91.4	102.6	108.6	100.0	89.5
80°	67.0	78.9	83.5	76.4	67.9
82.5°	47.5	57.4	60.6	56.3	50.5
85°	21.8	28.6	32.2	30.4	28.7
87.5°	5.8	11.1	15.2	14.2	14.9
90°	1.2	3.7	10.0	5.0	5.0
92.5°	5.2	25.2	55.8	24.7	15.9
95°	12.5	49.0	163.1	84.1	57.3
97.5°	21.7	53.8	244.0	194.1	142.9
100°	28.6	57.9	268.9	272.5	211.7
102.5°	34.6	61.9	275.9	339.5	287.4
105°	44.8	68.0	275.2	417.7	389.7
107.5°	55.3	76.7	259.5	458.3	465.2
110°	62.3	81.7	246.5	468.8	498.0

TEST NUMBER: P564539

CATALOG NUMBER: SQ4-PW1-025U-050D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	69.2	87.7	234.6	462.2	507.0
115°	79.7	96.7	220.4	439.7	501.8
117.5°	89.9	105.5	210.7	408.5	477.4
120°	95.9	110.5	206.7	387.5	454.4
122.5°	101.8	116.5	203.7	366.6	432.5
125°	110.8	124.2	200.5	338.8	399.7
127.5°	118.0	131.7	197.7	316.4	367.8
130°	122.0	136.6	196.7	302.4	349.9
132.5°	126.0	140.6	195.7	290.3	332.9
135°	132.0	145.4	194.2	273.5	310.0
137.5°	138.2	151.3	194.0	260.9	290.8
140°	143.2	155.4	193.0	250.9	278.9
142.5°	147.2	158.4	193.0	243.8	267.9
145°	153.1	162.9	191.7	233.2	251.5
147.5°	159.1	168.6	191.7	224.5	239.6
150°	163.1	171.6	191.7	219.4	231.6
152.5°	167.1	173.7	191.7	215.4	224.6
155°	173.1	177.9	191.7	210.6	216.6
157.5°	177.5	182.2	191.7	206.3	210.7
160°	180.5	184.2	191.7	204.2	206.7
162.5°	183.5	186.2	191.7	202.3	204.7
165°	186.8	189.2	191.7	199.3	201.7
167.5°	189.7	191.0	193.0	198.0	199.0
170°	191.7	193.0	193.0	198.0	198.0
172.5°	192.7	193.0	193.0	196.9	196.0
175°	194.2	194.2	193.0	195.5	195.5
177.5°	194.2	194.2	193.2	195.2	194.2
180°	194.2	194.2	194.2	194.2	194.2

(END OF REPORT)