

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563001

Luminaire Tested: **SQ4-PC3-125U-050D-935-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563001
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-125U-050D-935-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18166.2 lumens
Efficiency: N/A
Efficacy: 124.1 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 146.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563001
CATALOG NUMBER: SQ4-PC3-125U-050D-935-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P563001

CATALOG NUMBER: SQ4-PC3-125U-050D-935-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28
1	93	89	85	82	83	80	76	74	62	60	58	47	45	44	32	31	31	24
2	85	77	72	67	75	70	65	60	55	51	48	41	39	37	28	27	26	20
3	77	68	61	55	69	61	55	50	48	44	40	36	33	31	25	23	22	17
4	70	60	52	47	63	54	48	43	43	38	34	32	29	26	22	20	19	14
5	65	53	46	40	57	48	41	36	38	33	29	29	25	23	20	18	16	13
6	59	48	40	34	53	43	36	31	34	29	26	26	22	20	18	16	14	11
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	13	10
8	51	39	31	26	45	35	29	24	28	23	20	21	18	15	15	13	11	9
9	47	35	28	23	42	32	26	21	26	21	17	20	16	14	14	12	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5781	5781	5781
5°	5824	5787	5765
10°	5810	5783	5767
15°	5779	5779	5774
20°	5741	5758	5758
25°	5687	5729	5711
30°	5618	5686	5661
35°	5534	5619	5580
40°	5443	5520	5464
45°	5344	5382	5299
50°	5204	5204	5121
55°	5039	4974	4899
60°	4796	4699	4624
65°	4432	4344	4306
70°	3881	3912	3897
75°	3123	3453	3474
80°	2219	2928	2959
85°	1351	2456	2456



TEST NUMBER: P563001

CATALOG NUMBER: SQ4-PC3-125U-050D-935-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	177.9	1.0
10°-20°	510.5	2.8
20°-30°	773.1	4.3
30°-40°	926.8	5.1
40°-50°	945.0	5.2
50°-60°	824.9	4.5
60°-70°	590.6	3.3
70°-80°	304.2	1.7
80°-90°	81.6	0.4
90°-100°	944.3	5.2
100°-110°	2543.8	14.0
110°-120°	2669.6	14.7
120°-130°	2166.3	11.9
130°-140°	1699.0	9.4
140°-150°	1304.4	7.2
150°-160°	937.9	5.2
160°-170°	573.0	3.2
170°-180°	193.2	1.1
0°-30°	1461.4	8.0
0°-40°	2388.2	13.1
0°-60°	4158.2	22.9
0°-90°	5134.6	28.3
90°-120°	6157.8	33.9
90°-150°	11327.5	62.4
90°-180°	13032.0	71.7
0°-180°	18166.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1880	1880	1880	1880	1880	
5°	1887	1868	1874	1869	1867	179
15°	1815	1800	1815	1815	1814	512
25°	1676	1664	1688	1683	1683	771
35°	1474	1471	1497	1486	1486	922
45°	1229	1225	1237	1222	1218	946
55°	940	928	928	914	914	838
65°	609	596	597	592	592	602
75°	263	275	291	292	292	284
85°	38	59	70	71	70	52
90°	5	15	31	33	33	12
95°	144	514	1548	792	548	150
105°	471	732	2813	4209	3950	495
115°	831	1017	2343	4526	5120	817
125°	1134	1302	2104	3555	4184	1013
135°	1366	1524	2044	2868	3248	1054
145°	1579	1702	2019	2452	2633	990
155°	1792	1858	2001	2200	2271	825
165°	1944	1967	2008	2088	2098	548
175°	2021	2019	2011	2039	2034	192
180°	2019	2019	2019	2019	2019	

TEST NUMBER: P563001

CATALOG NUMBER: SQ4-PC3-125U-050D-935-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1879.6	1879.6	1879.6	1879.6	1879.6
2.5°	1890.8	1874.4	1879.6	1875.3	1868.5
5°	1886.6	1867.9	1874.4	1869.1	1867.4
7.5°	1873.0	1854.3	1862.9	1859.4	1857.7
10°	1860.5	1841.8	1851.8	1848.3	1846.6
12.5°	1843.8	1826.4	1837.9	1834.4	1834.0
15°	1815.2	1799.9	1815.2	1815.2	1813.5
17.5°	1779.4	1765.4	1781.8	1782.8	1781.8
20°	1754.3	1739.0	1759.5	1757.8	1759.5
22.5°	1723.7	1711.1	1733.1	1728.6	1730.3
25°	1676.0	1664.1	1688.2	1683.0	1683.0
27.5°	1619.6	1611.1	1637.4	1631.8	1631.8
30°	1582.0	1573.5	1601.2	1594.2	1594.2
32.5°	1540.2	1534.5	1560.8	1552.4	1552.4
35°	1474.1	1470.7	1496.7	1486.3	1486.3
37.5°	1405.9	1402.8	1426.4	1413.8	1409.7
40°	1355.8	1354.1	1374.9	1361.0	1361.0
42.5°	1305.6	1303.9	1322.0	1305.3	1305.3
45°	1228.7	1225.3	1237.4	1221.7	1218.3
47.5°	1144.8	1141.4	1149.0	1131.9	1130.2
50°	1087.7	1084.3	1087.7	1072.0	1070.3
52.5°	1029.3	1023.1	1023.7	1008.0	1007.7
55°	939.8	927.9	927.6	913.7	913.7
57.5°	845.1	829.5	830.9	819.0	817.3
60°	779.7	762.7	764.0	753.6	751.8
62.5°	715.6	695.9	700.0	688.1	687.8
65°	609.1	595.5	597.0	591.7	591.7
67.5°	506.8	494.2	503.3	499.1	498.8
70°	431.6	423.1	435.1	435.1	433.4
72.5°	362.0	361.7	376.6	376.6	377.7
75°	262.8	274.7	290.6	292.4	292.4
77.5°	175.4	196.5	214.1	214.8	214.4
80°	125.3	149.1	165.3	168.8	167.1
82.5°	84.9	110.1	123.6	127.0	125.3
85°	38.3	58.7	69.6	71.3	69.6
87.5°	12.2	26.4	34.0	34.5	31.7
90°	5.1	15.2	30.9	33.4	33.4
92.5°	62.7	221.7	438.2	210.9	146.6
95°	144.0	513.6	1548.1	791.6	547.7
97.5°	229.9	587.9	2428.0	2028.4	1529.6
100°	295.7	617.6	2707.8	2833.2	2350.4
102.5°	359.5	659.2	2800.4	3435.8	3039.6
105°	470.6	732.1	2813.3	4208.9	3949.9
107.5°	575.5	808.8	2693.4	4606.1	4673.0
110°	645.5	866.7	2584.4	4729.5	4973.4

TEST NUMBER: P563001

CATALOG NUMBER: SQ4-PC3-125U-050D-935-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	719.5	924.7	2479.5	4702.2	5103.0
115°	830.6	1016.7	2342.7	4526.5	5119.9
117.5°	931.9	1106.4	2236.7	4246.2	4907.0
120°	997.8	1166.2	2183.2	4045.0	4723.9
122.5°	1055.4	1221.8	2144.2	3839.3	4516.1
125°	1134.0	1302.5	2103.5	3555.3	4183.9
127.5°	1209.7	1375.6	2077.8	3304.8	3866.1
130°	1254.9	1420.9	2067.5	3161.3	3654.2
132.5°	1300.2	1464.1	2057.2	3034.9	3487.5
135°	1365.5	1523.9	2044.4	2868.2	3247.9
137.5°	1427.7	1579.6	2037.7	2726.7	3038.5
140°	1470.9	1616.8	2031.5	2639.7	2921.3
142.5°	1516.2	1652.0	2027.4	2558.4	2795.8
145°	1578.9	1702.1	2018.7	2452.2	2633.3
147.5°	1646.8	1753.9	2009.9	2362.9	2505.2
150°	1692.1	1785.1	2005.8	2306.8	2425.0
152.5°	1733.2	1814.2	2003.7	2261.0	2357.1
155°	1792.4	1857.7	2000.7	2200.3	2270.7
157.5°	1844.3	1895.1	2001.2	2157.6	2204.8
160°	1877.2	1920.0	2003.2	2132.6	2167.8
162.5°	1906.0	1940.7	2005.3	2111.8	2137.0
165°	1944.1	1966.7	2008.4	2088.3	2098.4
167.5°	1974.9	1988.0	2010.9	2070.2	2074.2
170°	1995.5	2000.5	2010.9	2059.8	2059.8
172.5°	2007.9	2008.9	2013.0	2049.5	2049.5
175°	2021.2	2018.7	2010.9	2039.1	2034.1
177.5°	2026.9	2022.9	2012.5	2028.9	2024.8
180°	2018.7	2018.7	2018.7	2018.7	2018.7

(END OF REPORT)