

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P563049

Luminaire Tested: **SQ4-PC3-125U-100D-935-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563049
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-125U-100D-935-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 23082.4 lumens
Efficiency: N/A
Efficacy: 114.7 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 201.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563049

CATALOG NUMBER: SQ4-PC3-125U-100D-935-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P563049

CATALOG NUMBER: SQ4-PC3-125U-100D-935-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44
1	96	92	88	85	88	84	81	78	70	68	66	57	55	54	44	43	42	37
2	88	80	74	69	80	74	69	64	61	58	54	50	47	45	39	37	36	31
3	80	71	63	58	73	65	59	54	54	49	46	44	41	38	35	32	30	26
4	73	62	55	49	67	57	51	45	48	43	39	39	35	32	31	28	26	22
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	28	25	23	19
6	62	50	42	36	56	46	39	34	39	33	29	32	28	24	25	22	20	17
7	57	45	37	31	52	41	34	29	35	29	25	29	25	22	23	20	18	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	27	22	18	22	18	15	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11321	11321	11321
5°	11406	11332	11290
10°	11378	11325	11293
15°	11318	11318	11307
20°	11244	11277	11277
25°	11138	11219	11184
30°	11002	11135	11087
35°	10838	11004	10928
40°	10659	10810	10700
45°	10466	10540	10376
50°	10192	10192	10029
55°	9868	9740	9594
60°	9392	9203	9056
65°	8681	8507	8433
70°	7601	7662	7631
75°	6116	6763	6804
80°	4346	5735	5795
85°	2646	4810	4810



TEST NUMBER: P563049

CATALOG NUMBER: SQ4-PC3-125U-100D-935-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	348.4	1.5
10°-20°	999.7	4.3
20°-30°	1513.9	6.6
30°-40°	1815.0	7.9
40°-50°	1850.7	8.0
50°-60°	1615.5	7.0
60°-70°	1156.6	5.0
70°-80°	595.7	2.6
80°-90°	155.4	0.7
90°-100°	944.3	4.1
100°-110°	2543.8	11.0
110°-120°	2669.6	11.6
120°-130°	2166.3	9.4
130°-140°	1699.0	7.4
140°-150°	1304.4	5.7
150°-160°	937.9	4.1
160°-170°	573.0	2.5
170°-180°	193.2	0.8
0°-30°	2862.0	12.4
0°-40°	4677.0	20.3
0°-60°	8143.2	35.3
0°-90°	10050.8	43.5
90°-120°	6157.8	26.7
90°-150°	11327.5	49.1
90°-180°	13032.0	56.5
0°-180°	23082.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3681	3681	3681	3681	3681	
5°	3695	3658	3671	3660	3657	351
15°	3555	3525	3555	3555	3551	1002
25°	3282	3259	3306	3296	3296	1511
35°	2887	2880	2931	2911	2911	1805
45°	2406	2400	2423	2392	2386	1852
55°	1840	1817	1817	1789	1789	1641
65°	1193	1166	1169	1159	1159	1180
75°	515	538	569	573	573	556
85°	75	115	136	140	136	102
90°	5	15	31	33	33	13
95°	144	514	1548	792	548	150
105°	471	732	2813	4209	3950	495
115°	831	1017	2343	4526	5120	817
125°	1134	1302	2104	3555	4184	1013
135°	1366	1524	2044	2868	3248	1054
145°	1579	1702	2019	2452	2633	990
155°	1792	1858	2001	2200	2271	825
165°	1944	1967	2008	2088	2098	548
175°	2021	2019	2011	2039	2034	192
180°	2019	2019	2019	2019	2019	

TEST NUMBER: P563049

CATALOG NUMBER: SQ4-PC3-125U-100D-935-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3681.0	3681.0	3681.0	3681.0	3681.0
2.5°	3702.8	3670.8	3681.0	3672.5	3659.2
5°	3694.6	3657.9	3670.7	3660.4	3657.1
7.5°	3668.0	3631.4	3648.2	3641.4	3638.0
10°	3643.5	3606.8	3626.4	3619.5	3616.2
12.5°	3610.8	3576.8	3599.2	3592.3	3591.7
15°	3554.9	3524.9	3554.9	3554.8	3551.4
17.5°	3484.6	3457.3	3489.4	3491.4	3489.4
20°	3435.6	3405.6	3445.8	3442.5	3445.8
22.5°	3375.6	3350.9	3394.0	3385.2	3388.5
25°	3282.2	3258.9	3306.1	3295.8	3295.8
27.5°	3171.8	3155.1	3206.5	3195.6	3195.6
30°	3098.1	3081.5	3135.6	3122.0	3122.0
32.5°	3016.3	3005.0	3056.6	3040.2	3040.2
35°	2886.8	2880.2	2931.1	2910.7	2910.7
37.5°	2753.2	2747.2	2793.4	2768.7	2760.7
40°	2655.1	2651.7	2692.6	2665.3	2665.3
42.5°	2556.9	2553.6	2588.9	2556.2	2556.2
45°	2406.3	2399.6	2423.3	2392.5	2385.8
47.5°	2242.0	2235.3	2250.2	2216.7	2213.3
50°	2130.2	2123.5	2130.2	2099.4	2096.1
52.5°	2015.7	2003.7	2004.8	1974.1	1973.4
55°	1840.5	1817.2	1816.6	1789.4	1789.4
57.5°	1655.1	1624.4	1627.1	1603.9	1600.5
60°	1526.9	1493.6	1496.2	1475.7	1472.4
62.5°	1401.5	1362.8	1370.8	1347.6	1347.0
65°	1192.9	1166.2	1169.0	1158.8	1158.8
67.5°	992.5	967.8	985.7	977.5	976.8
70°	845.3	828.6	852.1	852.0	848.7
72.5°	708.9	708.3	737.6	737.6	739.6
75°	514.7	538.0	569.2	572.6	572.6
77.5°	343.6	384.9	419.2	420.6	419.9
80°	245.4	292.1	323.8	330.5	327.2
82.5°	166.3	215.6	242.0	248.7	245.4
85°	75.0	115.0	136.3	139.7	136.3
87.5°	22.8	48.8	60.7	61.1	55.8
90°	5.1	15.2	30.9	33.4	33.4
92.5°	62.7	221.7	438.2	210.9	146.6
95°	144.0	513.6	1548.1	791.6	547.7
97.5°	229.9	587.9	2428.0	2028.4	1529.6
100°	295.7	617.6	2707.8	2833.2	2350.4
102.5°	359.5	659.2	2800.4	3435.8	3039.6
105°	470.6	732.1	2813.3	4208.9	3949.9
107.5°	575.5	808.8	2693.4	4606.1	4673.0
110°	645.5	866.7	2584.4	4729.5	4973.4



TEST NUMBER: P563049

CATALOG NUMBER: SQ4-PC3-125U-100D-935-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	719.5	924.7	2479.5	4702.2	5103.0
115°	830.6	1016.7	2342.7	4526.5	5119.9
117.5°	931.9	1106.4	2236.7	4246.2	4907.0
120°	997.8	1166.2	2183.2	4045.0	4723.9
122.5°	1055.4	1221.8	2144.2	3839.3	4516.1
125°	1134.0	1302.5	2103.5	3555.3	4183.9
127.5°	1209.7	1375.6	2077.8	3304.8	3866.1
130°	1254.9	1420.9	2067.5	3161.3	3654.2
132.5°	1300.2	1464.1	2057.2	3034.9	3487.5
135°	1365.5	1523.9	2044.4	2868.2	3247.9
137.5°	1427.7	1579.6	2037.7	2726.7	3038.5
140°	1470.9	1616.8	2031.5	2639.7	2921.3
142.5°	1516.2	1652.0	2027.4	2558.4	2795.8
145°	1578.9	1702.1	2018.7	2452.2	2633.3
147.5°	1646.8	1753.9	2009.9	2362.9	2505.2
150°	1692.1	1785.1	2005.8	2306.8	2425.0
152.5°	1733.2	1814.2	2003.7	2261.0	2357.1
155°	1792.4	1857.7	2000.7	2200.3	2270.7
157.5°	1844.3	1895.1	2001.2	2157.6	2204.8
160°	1877.2	1920.0	2003.2	2132.6	2167.8
162.5°	1906.0	1940.7	2005.3	2111.8	2137.0
165°	1944.1	1966.7	2008.4	2088.3	2098.4
167.5°	1974.9	1988.0	2010.9	2070.2	2074.2
170°	1995.5	2000.5	2010.9	2059.8	2059.8
172.5°	2007.9	2008.9	2013.0	2049.5	2049.5
175°	2021.2	2018.7	2010.9	2039.1	2034.1
177.5°	2026.9	2022.9	2012.5	2028.9	2024.8
180°	2018.7	2018.7	2018.7	2018.7	2018.7

(END OF REPORT)