

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P564971

Luminaire Tested: **SQ4-PW1-100U-100D-935-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564971
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-100U-100D-935-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10157.4 lumens
Efficiency: N/A
Efficacy: 109.3 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 92.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564971
CATALOG NUMBER: SQ4-PW1-100U-100D-935-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P564971

CATALOG NUMBER: SQ4-PW1-100U-100D-935-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20		
RC	80					70					50					0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55	48
1	98	93	89	86	90	86	83	80	72	70	68	60	58	57	49	47	46	41
2	89	82	75	70	82	75	70	66	64	60	56	53	50	48	43	41	39	35
3	81	72	64	59	74	66	60	55	56	51	47	47	43	40	38	36	33	29
4	74	63	56	50	68	59	52	47	50	45	40	42	38	35	34	31	29	25
5	68	57	48	43	62	52	45	40	45	39	35	37	33	30	31	28	25	22
6	63	51	43	37	58	47	40	35	40	35	30	34	30	26	28	25	22	19
7	58	46	38	32	53	43	35	30	36	31	27	31	26	23	25	22	20	17
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	30	25	46	35	29	24	30	25	21	26	22	19	21	18	16	14
10	47	35	28	23	43	32	26	22	28	23	19	24	20	17	20	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11897	11897	11897
5°	11974	11879	11827
10°	11878	11782	11719
15°	11752	11622	11579
20°	11612	11434	11411
25°	11450	11241	11207
30°	11207	11038	10966
35°	10889	10736	10672
40°	10550	10386	10344
45°	10139	10006	9962
50°	9719	9638	9572
55°	9265	9265	9119
60°	8700	8868	8553
65°	7961	8358	7763
70°	7019	7692	6834
75°	5994	6885	5832
80°	4647	5795	4707
85°	3006	4453	3966



TEST NUMBER: P564971

CATALOG NUMBER: SQ4-PW1-100U-100D-935-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.1	1.8
10°-20°	514.2	5.1
20°-30°	762.8	7.5
30°-40°	892.5	8.8
40°-50°	888.5	8.7
50°-60°	767.3	7.6
60°-70°	552.3	5.4
70°-80°	289.6	2.9
80°-90°	73.5	0.7
90°-100°	377.3	3.7
100°-110°	1041.6	10.3
110°-120°	1074.2	10.6
120°-130°	863.2	8.5
130°-140°	678.4	6.7
140°-150°	520.3	5.1
150°-160°	373.9	3.7
160°-170°	228.7	2.3
170°-180°	77.1	0.8
0°-30°	1459.1	14.4
0°-40°	2351.6	23.2
0°-60°	4007.4	39.5
0°-90°	4922.8	48.5
90°-120°	2493.0	24.5
90°-150°	4554.9	44.8
90°-180°	5235.0	51.5
0°-180°	10157.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1934	1934	1934	1934	1934	
5°	1939	1918	1924	1919	1916	184
15°	1846	1822	1825	1822	1818	520
25°	1687	1659	1656	1646	1651	776
35°	1450	1430	1430	1416	1421	907
45°	1166	1156	1150	1147	1145	899
55°	864	862	864	852	850	771
65°	547	564	574	552	533	542
75°	252	276	290	270	245	270
85°	43	56	63	60	56	56
90°	3	5	10	12	13	5
95°	55	204	684	281	183	59
105°	186	286	1146	1750	1647	197
115°	333	402	923	1827	2078	327
125°	456	519	837	1416	1662	406
135°	549	608	813	1147	1293	425
145°	637	681	803	976	1051	399
155°	718	742	797	876	904	331
165°	777	787	800	832	838	219
175°	806	807	802	813	811	77
180°	806	806	806	806	806	

TEST NUMBER: P564971

CATALOG NUMBER: SQ4-PW1-100U-100D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1934.2	1934.2	1934.2	1934.2	1934.2
2.5°	1945.1	1929.1	1934.2	1929.9	1920.6
5°	1939.3	1917.7	1924.0	1918.8	1915.5
7.5°	1919.6	1899.6	1904.2	1898.7	1896.7
10°	1901.8	1881.8	1886.5	1879.6	1876.3
12.5°	1881.4	1860.1	1864.7	1857.8	1855.8
15°	1845.6	1822.3	1825.1	1821.7	1818.3
17.5°	1804.0	1780.4	1780.8	1775.4	1774.7
20°	1774.0	1749.0	1746.8	1740.0	1743.3
22.5°	1741.3	1715.0	1712.7	1703.2	1707.9
25°	1687.1	1658.8	1656.4	1646.3	1651.3
27.5°	1624.4	1596.4	1596.4	1582.3	1587.6
30°	1578.0	1551.4	1554.2	1537.3	1544.0
32.5°	1529.0	1505.0	1506.5	1489.6	1496.2
35°	1450.2	1430.2	1429.8	1416.3	1421.3
37.5°	1369.8	1352.1	1349.3	1341.5	1342.9
40°	1313.9	1298.9	1293.5	1288.3	1288.3
42.5°	1255.3	1241.6	1236.2	1232.4	1231.1
45°	1165.6	1155.6	1150.3	1146.9	1145.2
47.5°	1077.0	1067.7	1063.0	1060.6	1059.0
50°	1015.7	1009.0	1007.2	1002.0	1000.3
52.5°	954.3	950.3	948.5	942.0	940.4
55°	864.0	862.3	864.0	852.0	850.4
57.5°	769.9	772.6	778.1	762.0	758.0
60°	707.2	713.9	720.9	702.0	695.3
62.5°	643.1	653.8	663.6	641.9	632.6
65°	547.0	563.7	574.3	551.7	533.4
67.5°	454.3	475.0	487.7	463.4	442.7
70°	390.3	413.6	427.7	403.4	380.0
72.5°	334.4	360.3	371.8	348.8	325.5
75°	252.2	275.5	289.7	270.4	245.4
77.5°	178.9	200.9	212.7	195.8	175.2
80°	131.2	154.5	163.6	149.6	132.9
82.5°	93.0	112.4	118.6	110.2	98.8
85°	42.6	55.9	63.1	59.6	56.2
87.5°	11.4	21.3	28.0	28.3	29.8
90°	2.6	5.1	10.3	11.6	12.9
92.5°	23.2	96.3	172.2	62.8	49.0
95°	55.4	204.2	684.5	281.4	183.0
97.5°	91.8	228.7	1013.9	780.6	565.4
100°	118.6	243.4	1135.6	1143.7	929.4
102.5°	144.4	260.1	1159.3	1413.1	1209.9
105°	185.6	286.4	1145.9	1749.5	1647.4
107.5°	229.4	319.2	1082.0	1911.7	1949.0
110°	260.4	341.0	1032.5	1946.6	2067.6

TEST NUMBER: P564971

CATALOG NUMBER: SQ4-PW1-100U-100D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	288.2	365.9	986.1	1919.0	2097.5
115°	332.6	401.9	922.9	1827.1	2077.9
117.5°	371.2	440.3	881.4	1697.7	1983.0
120°	397.0	465.1	864.9	1610.1	1897.4
122.5°	421.8	486.8	851.5	1528.3	1800.5
125°	456.3	519.3	836.6	1415.8	1661.6
127.5°	485.7	548.7	827.8	1320.7	1532.6
130°	505.3	568.3	823.7	1262.5	1455.3
132.5°	523.9	583.9	819.6	1213.6	1388.3
135°	549.1	608.4	813.4	1146.7	1292.9
137.5°	577.5	631.4	810.3	1090.5	1215.3
140°	593.0	645.9	808.2	1053.0	1162.7
142.5°	610.5	659.4	806.2	1019.7	1116.3
145°	636.8	680.9	803.1	976.2	1050.6
147.5°	662.0	700.6	800.2	939.5	997.2
150°	680.6	712.1	799.2	917.6	964.2
152.5°	695.0	724.5	798.2	898.8	937.4
155°	718.0	741.9	796.6	875.9	903.6
157.5°	739.1	757.5	796.9	859.2	878.1
160°	751.5	767.9	797.9	849.8	863.6
162.5°	761.8	776.2	798.9	841.5	852.3
165°	777.3	787.4	800.5	831.6	837.9
167.5°	789.1	795.2	801.8	825.5	827.6
170°	795.3	800.4	801.8	822.4	822.4
172.5°	800.5	803.5	801.8	818.2	817.2
175°	805.6	806.9	801.8	813.3	810.8
177.5°	807.7	806.7	801.5	808.7	806.7
180°	805.6	805.6	805.6	805.6	805.6

(END OF REPORT)