

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564995

Luminaire Tested: **SQ4-PW1-100U-125D-935-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564995
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-100U-125D-935-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11516.3 lumens
Efficiency: N/A
Efficacy: 107.3 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 107.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564995
CATALOG NUMBER: SQ4-PW1-100U-125D-935-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P564995

CATALOG NUMBER: SQ4-PW1-100U-125D-935-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60	55
1	99	95	91	87	92	88	85	82	76	73	71	64	62	61	53	52	51	46
2	90	83	77	71	83	77	72	67	66	62	59	56	53	51	47	45	43	39
3	82	73	65	60	76	68	61	56	59	54	49	50	46	43	42	39	37	33
4	75	64	57	50	70	60	53	48	52	47	42	44	40	37	37	34	32	28
5	69	57	49	43	64	54	46	41	47	41	36	40	36	32	34	30	28	25
6	64	52	43	38	59	48	41	36	42	36	32	36	32	28	31	27	24	22
7	59	47	39	33	55	44	36	31	38	32	28	33	28	25	28	24	22	19
8	55	42	35	29	51	40	33	28	35	29	25	30	26	22	26	22	19	17
9	51	39	31	26	47	36	30	25	32	26	22	28	23	20	24	20	18	15
10	48	36	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15182	15182	15182
5°	15280	15160	15092
10°	15158	15036	14955
15°	14997	14831	14776
20°	14818	14591	14562
25°	14612	14346	14302
30°	14303	14086	13994
35°	13896	13700	13619
40°	13463	13253	13201
45°	12939	12769	12712
50°	12402	12299	12216
55°	11824	11824	11637
60°	11102	11316	10915
65°	10160	10667	9907
70°	8956	9817	8722
75°	7650	8786	7443
80°	5933	7396	6007
85°	3839	5681	5067



TEST NUMBER: P564995

CATALOG NUMBER: SQ4-PW1-100U-125D-935-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	232.4	2.0
10°-20°	656.2	5.7
20°-30°	973.4	8.5
30°-40°	1139.0	9.9
40°-50°	1133.9	9.8
50°-60°	979.1	8.5
60°-70°	704.8	6.1
70°-80°	369.6	3.2
80°-90°	93.3	0.8
90°-100°	377.3	3.3
100°-110°	1041.6	9.0
110°-120°	1074.2	9.3
120°-130°	863.2	7.5
130°-140°	678.4	5.9
140°-150°	520.3	4.5
150°-160°	373.9	3.2
160°-170°	228.7	2.0
170°-180°	77.1	0.7
0°-30°	1862.0	16.2
0°-40°	3001.0	26.1
0°-60°	5114.0	44.4
0°-90°	6281.7	54.5
90°-120°	2493.0	21.6
90°-150°	4554.9	39.6
90°-180°	5235.0	45.5
0°-180°	11516.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2468	2468	2468	2468	2468	
5°	2475	2447	2455	2449	2444	234
15°	2355	2326	2329	2325	2320	664
25°	2153	2117	2114	2101	2107	990
35°	1851	1825	1825	1807	1814	1157
45°	1488	1475	1468	1464	1461	1148
55°	1103	1100	1103	1087	1085	984
65°	698	719	733	704	681	692
75°	322	352	370	345	313	345
85°	54	71	80	76	72	72
90°	3	5	10	12	13	6
95°	55	204	684	281	183	59
105°	186	286	1146	1750	1647	197
115°	333	402	923	1827	2078	327
125°	456	519	837	1416	1662	406
135°	549	608	813	1147	1293	425
145°	637	681	803	976	1051	399
155°	718	742	797	876	904	331
165°	777	787	800	832	838	219
175°	806	807	802	813	811	77
180°	806	806	806	806	806	

TEST NUMBER: P564995

CATALOG NUMBER: SQ4-PW1-100U-125D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2468.3	2468.3	2468.3	2468.3	2468.3
2.5°	2482.2	2461.8	2468.3	2462.8	2450.9
5°	2474.8	2447.2	2455.3	2448.6	2444.4
7.5°	2449.6	2424.1	2430.0	2423.0	2420.5
10°	2427.0	2401.5	2407.4	2398.6	2394.4
12.5°	2400.9	2373.7	2379.6	2370.8	2368.3
15°	2355.2	2325.5	2329.1	2324.7	2320.4
17.5°	2302.2	2272.0	2272.6	2265.6	2264.8
20°	2263.9	2232.0	2229.1	2220.5	2224.7
22.5°	2222.1	2188.5	2185.6	2173.6	2179.5
25°	2153.0	2116.8	2113.8	2100.9	2107.3
27.5°	2072.9	2037.2	2037.3	2019.2	2026.0
30°	2013.8	1979.8	1983.3	1961.8	1970.3
32.5°	1951.2	1920.5	1922.5	1900.9	1909.4
35°	1850.7	1825.2	1824.6	1807.3	1813.7
37.5°	1748.0	1725.5	1721.9	1712.0	1713.7
40°	1676.7	1657.6	1650.6	1644.1	1644.1
42.5°	1601.9	1584.5	1577.5	1572.7	1571.0
45°	1487.5	1474.8	1467.9	1463.5	1461.4
47.5°	1374.4	1362.5	1356.6	1353.5	1351.4
50°	1296.1	1287.6	1285.3	1278.7	1276.6
52.5°	1217.8	1212.7	1210.5	1202.1	1200.0
55°	1102.6	1100.5	1102.6	1087.3	1085.2
57.5°	982.5	985.9	993.0	972.4	967.3
60°	902.5	911.0	919.9	895.8	887.3
62.5°	820.7	834.4	846.8	819.2	807.3
65°	698.1	719.4	732.9	704.1	680.7
67.5°	579.8	606.1	622.4	591.4	565.0
70°	498.0	527.8	545.9	514.7	485.0
72.5°	426.7	459.9	474.5	445.1	415.4
75°	321.9	351.6	369.7	345.1	313.2
77.5°	228.3	256.4	271.4	249.9	223.6
80°	167.5	197.2	208.8	190.9	169.6
82.5°	118.7	143.4	151.4	140.6	126.1
85°	54.4	71.4	80.5	76.0	71.8
87.5°	14.4	26.8	35.1	35.4	37.4
90°	2.6	5.1	10.3	11.6	12.9
92.5°	23.2	96.3	172.2	62.8	49.0
95°	55.4	204.2	684.5	281.4	183.0
97.5°	91.8	228.7	1013.9	780.6	565.4
100°	118.6	243.4	1135.6	1143.7	929.4
102.5°	144.4	260.1	1159.3	1413.1	1209.9
105°	185.6	286.4	1145.9	1749.5	1647.4
107.5°	229.4	319.2	1082.0	1911.7	1949.0
110°	260.4	341.0	1032.5	1946.6	2067.6

TEST NUMBER: P564995

CATALOG NUMBER: SQ4-PW1-100U-125D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	288.2	365.9	986.1	1919.0	2097.5
115°	332.6	401.9	922.9	1827.1	2077.9
117.5°	371.2	440.3	881.4	1697.7	1983.0
120°	397.0	465.1	864.9	1610.1	1897.4
122.5°	421.8	486.8	851.5	1528.3	1800.5
125°	456.3	519.3	836.6	1415.8	1661.6
127.5°	485.7	548.7	827.8	1320.7	1532.6
130°	505.3	568.3	823.7	1262.5	1455.3
132.5°	523.9	583.9	819.6	1213.6	1388.3
135°	549.1	608.4	813.4	1146.7	1292.9
137.5°	577.5	631.4	810.3	1090.5	1215.3
140°	593.0	645.9	808.2	1053.0	1162.7
142.5°	610.5	659.4	806.2	1019.7	1116.3
145°	636.8	680.9	803.1	976.2	1050.6
147.5°	662.0	700.6	800.2	939.5	997.2
150°	680.6	712.1	799.2	917.6	964.2
152.5°	695.0	724.5	798.2	898.8	937.4
155°	718.0	741.9	796.6	875.9	903.6
157.5°	739.1	757.5	796.9	859.2	878.1
160°	751.5	767.9	797.9	849.8	863.6
162.5°	761.8	776.2	798.9	841.5	852.3
165°	777.3	787.4	800.5	831.6	837.9
167.5°	789.1	795.2	801.8	825.5	827.6
170°	795.3	800.4	801.8	822.4	822.4
172.5°	800.5	803.5	801.8	818.2	817.2
175°	805.6	806.9	801.8	813.3	810.8
177.5°	807.7	806.7	801.5	808.7	806.7
180°	805.6	805.6	805.6	805.6	805.6

(END OF REPORT)