

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519397

Luminaire Tested: **SQ4-WB-100U-075D-935-1D-UNV-STD-W-6**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519397
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-100U-075D-935-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8486.1 lumens
Efficiency: N/A
Efficacy: 108.8 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 78
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519397
CATALOG NUMBER: SQ4-WB-100U-075D-935-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P519397

CATALOG NUMBER: SQ4-WB-100U-075D-935-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38
1	96	92	89	85	87	84	81	78	69	67	65	54	53	52	41	41	40	34
2	88	81	76	71	80	74	70	66	61	58	55	49	47	45	38	36	35	30
3	81	72	66	60	74	66	61	56	55	51	47	44	41	39	34	32	31	26
4	75	65	57	52	68	59	53	48	49	45	41	40	37	34	31	29	27	24
5	69	58	51	45	62	53	47	42	45	40	36	36	33	30	29	26	25	21
6	64	52	45	40	58	48	42	37	40	36	32	33	30	27	26	24	22	19
7	59	48	40	35	54	44	37	33	37	32	29	30	27	24	24	22	20	17
8	55	43	36	31	50	40	34	29	34	29	26	28	24	22	23	20	18	16
9	51	40	33	28	47	37	31	26	31	26	23	26	22	20	21	19	17	15
10	48	37	30	25	44	34	28	24	29	24	21	24	21	18	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13718	13718	13718
5°	13546	13498	13576
10°	12798	12914	13214
15°	11815	12089	12631
20°	10729	11133	11869
25°	9623	10148	11058
30°	8604	9167	10217
35°	7525	8068	9221
40°	6333	6836	7983
45°	5226	5678	6665
50°	4363	4757	5553
55°	3704	4082	4585
60°	3166	3539	3660
65°	2521	2976	2364
70°	2235	2323	1442
75°	2070	1885	884
80°	1906	1732	762
85°	1729	1588	621



TEST NUMBER: P519397

CATALOG NUMBER: SQ4-WB-100U-075D-935-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	204.6	2.4
10°-20°	532.1	6.3
20°-30°	689.2	8.1
30°-40°	674.9	8.0
40°-50°	516.6	6.1
50°-60°	344.2	4.1
60°-70°	187.8	2.2
70°-80°	78.3	0.9
80°-90°	23.8	0.3
90°-100°	377.3	4.4
100°-110°	1041.6	12.3
110°-120°	1074.2	12.7
120°-130°	863.2	10.2
130°-140°	678.4	8.0
140°-150°	520.3	6.1
150°-160°	373.9	4.4
160°-170°	228.7	2.7
170°-180°	77.1	0.9
0°-30°	1425.8	16.8
0°-40°	2100.7	24.8
0°-60°	2961.5	34.9
0°-90°	3251.4	38.3
90°-120°	2493.0	29.4
90°-150°	4554.9	53.7
90°-180°	5235.0	61.7
0°-180°	8486.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2230	2230	2230	2230	2230	
5°	2194	2172	2186	2191	2199	204
15°	1855	1849	1898	1950	1984	518
25°	1418	1422	1495	1560	1629	652
35°	1002	1007	1074	1147	1228	623
45°	601	612	653	702	766	469
55°	345	360	381	395	428	313
65°	173	188	204	179	162	180
75°	87	87	79	54	37	93
85°	24	24	22	14	9	27
90°	3	5	10	12	13	5
95°	55	204	684	281	183	59
105°	186	286	1146	1750	1647	197
115°	333	402	923	1827	2078	327
125°	456	519	837	1416	1662	406
135°	549	608	813	1147	1293	425
145°	637	681	803	976	1051	399
155°	718	742	797	876	904	331
165°	777	787	800	832	838	219
175°	806	807	802	813	811	77
180°	806	806	806	806	806	

TEST NUMBER: P519397

CATALOG NUMBER: SQ4-WB-100U-075D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2230.2	2230.2	2230.2	2230.2	2230.2
2.5°	2235.6	2215.7	2220.8	2220.6	2214.5
5°	2194.0	2171.9	2186.1	2191.2	2198.8
7.5°	2112.5	2095.9	2121.7	2140.9	2156.4
10°	2049.1	2034.8	2067.7	2095.6	2115.7
12.5°	1975.5	1963.5	2004.3	2041.7	2067.9
15°	1855.4	1848.7	1898.4	1950.1	1983.6
17.5°	1726.8	1723.5	1780.6	1840.9	1883.7
20°	1639.1	1638.1	1700.8	1763.5	1813.3
22.5°	1550.6	1552.7	1618.6	1683.8	1740.5
25°	1417.9	1421.8	1495.3	1560.4	1629.3
27.5°	1295.2	1297.0	1372.9	1441.7	1515.2
30°	1211.5	1216.3	1290.7	1362.0	1438.5
32.5°	1127.7	1133.3	1206.2	1279.8	1357.9
35°	1002.1	1006.8	1074.5	1146.8	1228.1
37.5°	872.5	879.0	939.0	1007.4	1087.4
40°	788.7	798.3	851.4	915.8	994.2
42.5°	708.1	720.0	769.2	830.3	901.1
45°	600.8	612.3	652.7	702.1	766.2
47.5°	508.5	521.7	552.7	595.2	650.0
50°	456.0	468.5	497.1	528.6	580.3
52.5°	409.8	422.3	447.8	472.1	516.1
55°	345.4	359.8	380.7	395.1	427.6
57.5°	292.6	306.4	322.9	329.4	349.2
60°	257.4	272.7	287.7	287.0	297.5
62.5°	225.3	238.3	253.3	242.9	243.5
65°	173.2	187.6	204.5	178.7	162.4
67.5°	139.9	143.0	160.5	124.6	105.3
70°	124.3	124.3	129.2	96.5	80.2
72.5°	109.4	109.4	104.9	78.5	61.5
75°	87.1	87.1	79.3	54.4	37.2
77.5°	67.1	66.4	60.7	40.6	27.0
80°	53.8	53.8	48.9	32.1	21.5
82.5°	42.1	42.1	38.0	25.0	16.0
85°	24.5	24.5	22.5	14.5	8.8
87.5°	9.1	9.6	9.9	7.0	6.5
90°	2.6	5.1	10.3	11.6	12.9
92.5°	23.2	96.3	172.2	62.8	49.0
95°	55.4	204.2	684.5	281.4	183.0
97.5°	91.8	228.7	1013.9	780.6	565.4
100°	118.6	243.4	1135.6	1143.7	929.4
102.5°	144.4	260.1	1159.3	1413.1	1209.9
105°	185.6	286.4	1145.9	1749.5	1647.4
107.5°	229.4	319.2	1082.0	1911.7	1949.0
110°	260.4	341.0	1032.5	1946.6	2067.6

TEST NUMBER: P519397

CATALOG NUMBER: SQ4-WB-100U-075D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	288.2	365.9	986.1	1919.0	2097.5
115°	332.6	401.9	922.9	1827.1	2077.9
117.5°	371.2	440.3	881.4	1697.7	1983.0
120°	397.0	465.1	864.9	1610.1	1897.4
122.5°	421.8	486.8	851.5	1528.3	1800.5
125°	456.3	519.3	836.6	1415.8	1661.6
127.5°	485.7	548.7	827.8	1320.7	1532.6
130°	505.3	568.3	823.7	1262.5	1455.3
132.5°	523.9	583.9	819.6	1213.6	1388.3
135°	549.1	608.4	813.4	1146.7	1292.9
137.5°	577.5	631.4	810.3	1090.5	1215.3
140°	593.0	645.9	808.2	1053.0	1162.7
142.5°	610.5	659.4	806.2	1019.7	1116.3
145°	636.8	680.9	803.1	976.2	1050.6
147.5°	662.0	700.6	800.2	939.5	997.2
150°	680.6	712.1	799.2	917.6	964.2
152.5°	695.0	724.5	798.2	898.8	937.4
155°	718.0	741.9	796.6	875.9	903.6
157.5°	739.1	757.5	796.9	859.2	878.1
160°	751.5	767.9	797.9	849.8	863.6
162.5°	761.8	776.2	798.9	841.5	852.3
165°	777.3	787.4	800.5	831.6	837.9
167.5°	789.1	795.2	801.8	825.5	827.6
170°	795.3	800.4	801.8	822.4	822.4
172.5°	800.5	803.5	801.8	818.2	817.2
175°	805.6	806.9	801.8	813.3	810.8
177.5°	807.7	806.7	801.5	808.7	806.7
180°	805.6	805.6	805.6	805.6	805.6

(END OF REPORT)