

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519445

Luminaire Tested: **SQ4-WB-100U-125D-935-1D-UNV-STD-W-6**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519445
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-100U-125D-935-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10586.5 lumens
Efficiency: N/A
Efficacy: 98.7 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 107.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519445
CATALOG NUMBER: SQ4-WB-100U-125D-935-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P519445

CATALOG NUMBER: SQ4-WB-100U-125D-935-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51	51	51
1	99	95	92	89	91	88	85	83	75	73	71	63	62	60	52	51	50	45	45	45
2	91	84	79	74	84	78	74	70	67	64	61	57	54	52	47	45	44	40	40	40
3	84	75	69	63	78	70	64	60	60	56	53	51	48	46	43	41	39	35	35	35
4	77	68	60	55	72	63	57	52	54	50	46	47	43	40	39	37	35	31	31	31
5	72	61	53	48	66	57	50	45	49	44	40	42	39	36	36	33	31	28	28	28
6	66	55	48	42	61	52	45	40	45	40	36	39	35	32	33	30	28	25	25	25
7	62	50	43	38	57	47	41	36	41	36	32	36	32	29	31	28	25	23	23	23
8	58	46	39	34	53	43	37	32	38	33	29	33	29	26	28	25	23	21	21	21
9	54	42	35	30	50	40	33	29	35	30	27	31	27	24	27	24	21	19	19	19
10	50	39	32	28	47	37	31	27	33	28	24	29	25	22	25	22	20	18	18	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22583	22583	22583
5°	22302	22222	22351
10°	21070	21261	21754
15°	19450	19902	20795
20°	17663	18328	19540
25°	15843	16707	18205
30°	14166	15092	16820
35°	12387	13282	15182
40°	10426	11254	13142
45°	8605	9347	10972
50°	7183	7831	9141
55°	6099	6720	7549
60°	5212	5826	6025
65°	4151	4900	3892
70°	3679	3825	2376
75°	3408	3101	1454
80°	3138	2855	1254
85°	2844	2618	1023



TEST NUMBER: P519445

CATALOG NUMBER: SQ4-WB-100U-125D-935-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	336.8	3.2
10°-20°	876.0	8.3
20°-30°	1134.6	10.7
30°-40°	1111.1	10.5
40°-50°	850.5	8.0
50°-60°	566.7	5.4
60°-70°	309.2	2.9
70°-80°	128.9	1.2
80°-90°	38.2	0.4
90°-100°	377.3	3.6
100°-110°	1041.6	9.8
110°-120°	1074.2	10.1
120°-130°	863.2	8.2
130°-140°	678.4	6.4
140°-150°	520.3	4.9
150°-160°	373.9	3.5
160°-170°	228.7	2.2
170°-180°	77.1	0.7
0°-30°	2347.3	22.2
0°-40°	3458.4	32.7
0°-60°	4875.6	46.1
0°-90°	5351.8	50.6
90°-120°	2493.0	23.5
90°-150°	4554.9	43.0
90°-180°	5235.0	49.4
0°-180°	10586.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3672	3672	3672	3672	3672	
5°	3612	3576	3599	3607	3620	336
15°	3054	3044	3125	3210	3266	853
25°	2334	2341	2462	2569	2682	1074
35°	1650	1658	1769	1888	2022	1026
45°	989	1008	1075	1156	1261	771
55°	569	592	627	650	704	516
65°	285	309	337	294	267	296
75°	143	143	130	90	61	153
85°	40	40	37	24	14	44
90°	3	5	10	12	13	6
95°	55	204	684	281	183	59
105°	186	286	1146	1750	1647	197
115°	333	402	923	1827	2078	327
125°	456	519	837	1416	1662	406
135°	549	608	813	1147	1293	425
145°	637	681	803	976	1051	399
155°	718	742	797	876	904	331
165°	777	787	800	832	838	219
175°	806	807	802	813	811	77
180°	806	806	806	806	806	

TEST NUMBER: P519445

CATALOG NUMBER: SQ4-WB-100U-125D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3671.6	3671.6	3671.6	3671.6	3671.6
2.5°	3680.6	3647.8	3656.1	3655.9	3645.8
5°	3612.0	3575.7	3599.1	3607.4	3620.0
7.5°	3477.9	3450.5	3493.1	3524.6	3550.1
10°	3373.5	3349.9	3404.1	3450.0	3483.1
12.5°	3252.4	3232.5	3299.7	3361.3	3404.5
15°	3054.5	3043.5	3125.4	3210.5	3265.6
17.5°	2842.8	2837.5	2931.5	3030.7	3101.3
20°	2698.5	2696.9	2800.0	2903.4	2985.3
22.5°	2552.9	2556.3	2664.7	2772.1	2865.4
25°	2334.4	2340.7	2461.7	2569.0	2682.4
27.5°	2132.4	2135.2	2260.3	2373.6	2494.5
30°	1994.5	2002.3	2125.0	2242.2	2368.2
32.5°	1856.6	1865.7	1985.8	2106.9	2235.5
35°	1649.7	1657.6	1768.9	1888.0	2021.9
37.5°	1436.4	1447.1	1546.0	1658.5	1790.2
40°	1298.5	1314.3	1401.6	1507.6	1636.8
42.5°	1165.8	1185.3	1266.3	1366.9	1483.4
45°	989.2	1008.1	1074.6	1155.9	1261.4
47.5°	837.1	858.8	909.9	980.0	1070.1
50°	750.7	771.2	818.4	870.3	955.3
52.5°	674.7	695.2	737.2	777.2	849.7
55°	568.7	592.3	626.7	650.5	704.0
57.5°	481.7	504.4	531.6	542.4	574.8
60°	423.7	448.9	473.6	472.4	489.8
62.5°	370.9	392.3	416.9	399.9	400.8
65°	285.2	308.8	336.7	294.2	267.4
67.5°	230.4	235.4	264.2	205.2	173.3
70°	204.6	204.6	212.7	158.9	132.1
72.5°	180.1	180.1	172.7	129.2	101.2
75°	143.4	143.4	130.5	89.6	61.2
77.5°	110.5	109.3	99.9	66.8	44.5
80°	88.6	88.6	80.6	52.8	35.4
82.5°	69.3	69.3	62.5	41.2	26.4
85°	40.3	40.3	37.1	24.0	14.5
87.5°	14.7	15.2	15.0	10.0	9.0
90°	2.6	5.1	10.3	11.6	12.9
92.5°	23.2	96.3	172.2	62.8	49.0
95°	55.4	204.2	684.5	281.4	183.0
97.5°	91.8	228.7	1013.9	780.6	565.4
100°	118.6	243.4	1135.6	1143.7	929.4
102.5°	144.4	260.1	1159.3	1413.1	1209.9
105°	185.6	286.4	1145.9	1749.5	1647.4
107.5°	229.4	319.2	1082.0	1911.7	1949.0
110°	260.4	341.0	1032.5	1946.6	2067.6



TEST NUMBER: P519445

CATALOG NUMBER: SQ4-WB-100U-125D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	288.2	365.9	986.1	1919.0	2097.5
115°	332.6	401.9	922.9	1827.1	2077.9
117.5°	371.2	440.3	881.4	1697.7	1983.0
120°	397.0	465.1	864.9	1610.1	1897.4
122.5°	421.8	486.8	851.5	1528.3	1800.5
125°	456.3	519.3	836.6	1415.8	1661.6
127.5°	485.7	548.7	827.8	1320.7	1532.6
130°	505.3	568.3	823.7	1262.5	1455.3
132.5°	523.9	583.9	819.6	1213.6	1388.3
135°	549.1	608.4	813.4	1146.7	1292.9
137.5°	577.5	631.4	810.3	1090.5	1215.3
140°	593.0	645.9	808.2	1053.0	1162.7
142.5°	610.5	659.4	806.2	1019.7	1116.3
145°	636.8	680.9	803.1	976.2	1050.6
147.5°	662.0	700.6	800.2	939.5	997.2
150°	680.6	712.1	799.2	917.6	964.2
152.5°	695.0	724.5	798.2	898.8	937.4
155°	718.0	741.9	796.6	875.9	903.6
157.5°	739.1	757.5	796.9	859.2	878.1
160°	751.5	767.9	797.9	849.8	863.6
162.5°	761.8	776.2	798.9	841.5	852.3
165°	777.3	787.4	800.5	831.6	837.9
167.5°	789.1	795.2	801.8	825.5	827.6
170°	795.3	800.4	801.8	822.4	822.4
172.5°	800.5	803.5	801.8	818.2	817.2
175°	805.6	806.9	801.8	813.3	810.8
177.5°	807.7	806.7	801.5	808.7	806.7
180°	805.6	805.6	805.6	805.6	805.6

(END OF REPORT)