

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519517

Luminaire Tested: **SQ4-WB-125U-100D-935-1D-UNV-STD-W-6**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519517
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-125U-100D-935-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10806.7 lumens
Efficiency: N/A
Efficacy: 105.1 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 102.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519517
CATALOG NUMBER: SQ4-WB-125U-100D-935-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P519517

CATALOG NUMBER: SQ4-WB-125U-100D-935-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47	40
1	96	92	89	86	88	84	81	79	69	67	65	55	54	53	43	42	41	35
2	88	82	76	72	80	75	70	66	62	59	56	50	48	46	39	37	36	31
3	81	73	66	61	74	67	61	56	55	51	48	45	42	40	35	33	32	27
4	75	65	58	52	68	60	54	49	50	45	42	41	37	35	32	30	28	24
5	69	58	51	45	63	54	47	42	45	40	37	37	34	31	29	27	25	22
6	64	53	45	40	58	49	42	37	41	36	32	34	30	28	27	25	23	20
7	59	48	40	35	54	44	38	33	37	33	29	31	27	25	25	23	21	18
8	55	44	36	32	50	40	34	30	34	29	26	29	25	22	23	21	19	16
9	52	40	33	28	47	37	31	27	32	27	24	26	23	20	22	19	17	15
10	48	37	30	26	44	34	28	24	29	25	21	25	21	19	20	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18102	18102	18102
5°	17876	17812	17916
10°	16889	17042	17437
15°	15591	15953	16668
20°	14158	14691	15663
25°	12699	13391	14592
30°	11355	12097	13482
35°	9929	10647	12169
40°	8357	9021	10534
45°	6897	7492	8795
50°	5759	6277	7328
55°	4888	5386	6051
60°	4178	4671	4830
65°	3327	3928	3120
70°	2949	3066	1904
75°	2731	2486	1167
80°	2515	2288	1006
85°	2279	2096	819



TEST NUMBER: P519517

CATALOG NUMBER: SQ4-WB-125U-100D-935-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	269.9	2.5
10°-20°	702.1	6.5
20°-30°	909.5	8.4
30°-40°	890.6	8.2
40°-50°	681.7	6.3
50°-60°	454.2	4.2
60°-70°	247.9	2.3
70°-80°	103.3	1.0
80°-90°	31.6	0.3
90°-100°	472.2	4.4
100°-110°	1271.9	11.8
110°-120°	1334.8	12.4
120°-130°	1083.2	10.0
130°-140°	849.5	7.9
140°-150°	652.2	6.0
150°-160°	468.9	4.3
160°-170°	286.5	2.7
170°-180°	96.6	0.9
0°-30°	1881.5	17.4
0°-40°	2772.1	25.7
0°-60°	3908.1	36.2
0°-90°	4290.9	39.7
90°-120°	3078.9	28.5
90°-150°	5663.8	52.4
90°-180°	6516.0	60.3
0°-180°	10806.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2943	2943	2943	2943	2943	
5°	2895	2866	2885	2892	2902	269
15°	2448	2440	2505	2573	2618	684
25°	1871	1876	1973	2059	2150	861
35°	1322	1329	1418	1513	1621	822
45°	793	808	861	926	1011	618
55°	456	475	502	521	564	413
65°	229	248	270	236	214	238
75°	115	115	105	72	49	123
85°	32	32	30	19	12	35
90°	3	8	15	17	17	7
95°	72	257	774	396	274	75
105°	235	366	1407	2104	1975	247
115°	415	508	1171	2263	2560	409
125°	567	651	1052	1778	2092	506
135°	683	762	1022	1434	1624	527
145°	790	851	1009	1226	1317	495
155°	896	929	1000	1100	1135	413
165°	972	983	1004	1044	1049	274
175°	1011	1009	1006	1020	1017	96
180°	1009	1009	1009	1009	1009	

TEST NUMBER: P519517

CATALOG NUMBER: SQ4-WB-125U-100D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2943.0	2943.0	2943.0	2943.0	2943.0
2.5°	2950.2	2924.0	2930.6	2930.4	2922.3
5°	2895.2	2866.2	2884.9	2891.6	2901.7
7.5°	2787.8	2765.8	2799.9	2825.2	2845.6
10°	2704.1	2685.2	2728.6	2765.4	2791.9
12.5°	2607.0	2591.1	2645.0	2694.3	2728.9
15°	2448.4	2439.6	2505.2	2573.4	2617.6
17.5°	2278.7	2274.4	2349.8	2429.3	2485.9
20°	2163.0	2161.8	2244.4	2327.2	2392.9
22.5°	2046.3	2049.1	2135.9	2222.1	2296.8
25°	1871.2	1876.2	1973.2	2059.2	2150.1
27.5°	1709.2	1711.5	1811.8	1902.6	1999.5
30°	1598.7	1605.0	1703.3	1797.3	1898.3
32.5°	1488.2	1495.5	1591.7	1688.9	1791.9
35°	1322.3	1328.7	1417.9	1513.3	1620.7
37.5°	1151.4	1160.0	1239.2	1329.4	1435.0
40°	1040.8	1053.5	1123.5	1208.5	1312.0
42.5°	934.4	950.1	1015.0	1095.6	1189.1
45°	792.9	808.0	861.3	926.5	1011.1
47.5°	671.0	688.4	729.4	785.5	857.7
50°	601.8	618.2	656.0	697.6	765.8
52.5°	540.8	557.2	590.9	623.0	681.1
55°	455.8	474.8	502.3	521.4	564.3
57.5°	386.1	404.3	426.1	434.7	460.8
60°	339.6	359.8	379.7	378.7	392.6
62.5°	297.3	314.4	334.2	320.5	321.3
65°	228.6	247.5	269.9	235.8	214.4
67.5°	184.7	188.7	211.8	164.5	139.0
70°	164.0	164.0	170.5	127.4	105.9
72.5°	144.4	144.4	138.4	103.6	81.1
75°	114.9	114.9	104.6	71.8	49.1
77.5°	88.6	87.6	80.1	53.6	35.6
80°	71.0	71.0	64.6	42.3	28.4
82.5°	55.5	55.5	50.1	33.0	21.2
85°	32.3	32.3	29.7	19.2	11.6
87.5°	11.9	12.9	13.4	9.5	8.5
90°	2.6	7.6	15.4	16.7	16.7
92.5°	31.4	110.8	219.1	105.5	73.3
95°	72.0	256.8	774.0	395.8	273.9
97.5°	114.9	294.0	1214.0	1014.2	764.8
100°	147.9	308.8	1353.9	1416.6	1175.2
102.5°	179.8	329.6	1400.2	1717.9	1519.8
105°	235.3	366.0	1406.6	2104.4	1974.9
107.5°	287.8	404.4	1346.7	2303.1	2336.5
110°	322.7	433.4	1292.2	2364.7	2486.7

TEST NUMBER: P519517

CATALOG NUMBER: SQ4-WB-125U-100D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	359.8	462.3	1239.7	2351.1	2551.5
115°	415.3	508.3	1171.3	2263.3	2560.0
117.5°	466.0	553.2	1118.4	2123.1	2453.5
120°	498.9	583.1	1091.6	2022.5	2362.0
122.5°	527.7	610.9	1072.1	1919.6	2258.1
125°	567.0	651.3	1051.8	1777.6	2091.9
127.5°	604.8	687.8	1038.9	1652.4	1933.0
130°	627.5	710.4	1033.8	1580.7	1827.1
132.5°	650.1	732.1	1028.6	1517.5	1743.8
135°	682.7	761.9	1022.2	1434.1	1623.9
137.5°	713.9	789.8	1018.8	1363.4	1519.3
140°	735.5	808.4	1015.8	1319.8	1460.6
142.5°	758.1	826.0	1013.7	1279.2	1397.9
145°	789.5	851.1	1009.3	1226.1	1316.6
147.5°	823.4	877.0	1005.0	1181.4	1252.6
150°	846.0	892.6	1002.9	1153.4	1212.5
152.5°	866.6	907.1	1001.9	1130.5	1178.5
155°	896.2	928.9	1000.3	1100.1	1135.3
157.5°	922.2	947.5	1000.6	1078.8	1102.4
160°	938.6	960.0	1001.6	1066.3	1083.9
162.5°	953.0	970.4	1002.6	1055.9	1068.5
165°	972.0	983.4	1004.2	1044.2	1049.2
167.5°	987.5	994.0	1005.5	1035.1	1037.1
170°	997.8	1000.3	1005.5	1029.9	1029.9
172.5°	1003.9	1004.4	1006.5	1024.8	1024.8
175°	1010.6	1009.4	1005.5	1019.6	1017.0
177.5°	1013.4	1011.4	1006.2	1014.4	1012.4
180°	1009.3	1009.3	1009.3	1009.3	1009.3

(END OF REPORT)