

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564489

Luminaire Tested: **SQ4-PR1-150U-100D-935-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P564489  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PR1-150U-100D-935-1D-UNV-STD-W-12  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 25599.7 lumens  
Efficiency: N/A  
Efficacy: 114.4 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35  
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 223.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P564489  
CATALOG NUMBER: SQ4-PR1-150U-100D-935-1D-UNV-STD-W-12

### Luminous Intensity Polar Plot





TEST NUMBER: P564489

CATALOG NUMBER: SQ4-PR1-150U-100D-935-1D-UNV-STD-W-12

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46	39				
1	95	91	88	84	87	83	80	77	68	66	64	54	52	51	41	40	39	33				
2	87	80	74	69	79	73	68	64	60	56	53	47	45	43	36	35	33	28				
3	80	70	63	58	72	64	58	53	53	48	45	42	39	36	32	30	28	24				
4	73	62	55	49	66	57	50	45	47	42	38	38	34	31	29	27	25	21				
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	24	22	18				
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	21	19	16				
7	57	45	37	32	52	41	34	30	34	29	25	28	24	21	22	19	17	14				
8	53	41	33	28	48	37	31	26	31	26	22	25	22	19	20	17	15	13				
9	49	37	30	25	45	34	28	23	29	24	20	23	20	17	18	16	14	11				
10	46	34	27	22	42	31	25	21	26	21	18	21	18	15	17	14	12	10				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	12169	12169	12169
5°	12279	12184	12121
10°	12240	12155	12091
15°	12186	12111	12045
20°	12125	12047	11958
25°	12040	11959	11820
30°	11910	11825	11656
35°	11734	11631	11465
40°	11466	11343	11138
45°	10999	10806	10584
50°	10176	9931	9735
55°	8881	8680	8498
60°	7484	7421	7275
65°	6474	6498	6449
70°	5945	5976	5976
75°	5711	5711	5751
80°	5372	5432	5372
85°	4330	4810	4810



TEST NUMBER: P564489

CATALOG NUMBER: SQ4-PR1-150U-100D-935-1D-UNV-STD-W-12

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	374.2	1.5
10°-20°	1070.6	4.2
20°-30°	1614.8	6.3
30°-40°	1924.1	7.5
40°-50°	1897.0	7.4
50°-60°	1449.7	5.7
60°-70°	897.2	3.5
70°-80°	509.6	2.0
80°-90°	160.1	0.6
90°-100°	1131.9	4.4
100°-110°	3060.3	12.0
110°-120°	3217.5	12.6
120°-130°	2613.5	10.2
130°-140°	2050.0	8.0
140°-150°	1573.4	6.1
150°-160°	1131.6	4.4
160°-170°	691.3	2.7
170°-180°	233.1	0.9
0°-30°	3059.6	12.0
0°-40°	4983.7	19.5
0°-60°	8330.4	32.5
0°-90°	9897.2	38.7
90°-120°	7409.7	28.9
90°-150°	13646.6	53.3
90°-180°	15703.0	61.3
0°-180°	25599.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3957	3957	3957	3957	3957	
5°	3978	3934	3947	3933	3926	377
15°	3828	3788	3804	3790	3783	1080
25°	3548	3505	3524	3487	3483	1633
35°	3125	3089	3098	3057	3054	1951
45°	2529	2496	2485	2440	2434	1937
55°	1656	1630	1619	1592	1585	1484
65°	890	883	893	886	886	901
75°	481	481	481	484	484	508
85°	123	129	136	136	136	143
90°	5	16	34	37	34	17
95°	176	616	1882	974	579	184
105°	569	879	3395	5008	4803	599
115°	1002	1224	2816	5451	6153	989
125°	1371	1571	2538	4282	5031	1222
135°	1644	1839	2470	3458	3914	1270
145°	1911	2055	2436	2960	3185	1196
155°	2158	2242	2414	2655	2742	995
165°	2349	2372	2425	2520	2532	662
175°	2438	2436	2428	2459	2454	231
180°	2436	2436	2436	2436	2436	

TEST NUMBER: P564489

CATALOG NUMBER: SQ4-PR1-150U-100D-935-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3957.0	3957.0	3957.0	3957.0	3957.0
2.5°	3981.6	3946.9	3957.0	3948.4	3929.8
5°	3977.5	3934.2	3946.8	3933.0	3926.4
7.5°	3946.8	3904.1	3916.8	3903.1	3899.1
10°	3919.5	3879.5	3892.3	3878.5	3871.8
12.5°	3889.5	3846.9	3862.3	3845.8	3839.1
15°	3827.5	3787.5	3803.7	3789.9	3783.2
17.5°	3759.3	3716.7	3732.8	3716.9	3708.2
20°	3704.8	3664.8	3681.0	3657.0	3653.7
22.5°	3644.8	3604.8	3621.0	3588.9	3588.2
25°	3548.0	3504.7	3524.2	3486.6	3483.3
27.5°	3432.8	3392.8	3409.0	3370.7	3366.7
30°	3353.8	3313.8	3329.9	3288.9	3282.2
32.5°	3263.8	3226.5	3239.9	3198.9	3194.9
35°	3125.4	3088.7	3098.1	3057.2	3053.8
37.5°	2967.9	2934.6	2940.0	2894.9	2891.6
40°	2856.1	2822.8	2825.5	2777.7	2774.3
42.5°	2733.5	2700.1	2697.3	2649.5	2646.2
45°	2529.0	2495.6	2484.6	2440.2	2433.5
47.5°	2295.8	2262.5	2242.0	2205.7	2201.1
50°	2126.8	2093.4	2075.6	2044.7	2034.8
52.5°	1944.1	1910.8	1895.7	1867.5	1857.5
55°	1656.4	1629.8	1618.9	1591.5	1584.9
57.5°	1383.1	1365.1	1362.0	1335.3	1332.6
60°	1216.8	1206.8	1206.5	1182.7	1182.7
62.5°	1075.0	1067.6	1072.9	1057.2	1054.5
65°	889.6	882.9	893.0	886.2	886.2
67.5°	743.0	743.0	749.1	746.4	746.4
70°	661.2	661.2	664.6	664.6	664.6
72.5°	587.6	584.9	593.7	593.7	591.0
75°	480.6	480.6	480.6	484.0	484.0
77.5°	374.2	374.9	377.6	376.9	374.2
80°	303.3	306.7	306.7	303.3	303.3
82.5°	232.4	235.8	235.9	235.1	232.4
85°	122.7	129.4	136.3	136.3	136.3
87.5°	36.5	49.2	61.3	61.8	58.6
90°	5.2	15.5	34.1	36.6	34.1
92.5°	74.5	271.3	535.3	232.4	168.3
95°	175.6	616.5	1882.3	974.1	579.4
97.5°	282.1	707.1	2934.1	2428.2	1783.2
100°	361.8	743.7	3261.3	3401.2	2750.1
102.5°	435.2	794.6	3376.7	4139.0	3651.9
105°	568.9	879.1	3395.0	5007.9	4802.8
107.5°	692.6	975.6	3246.6	5550.0	5618.1
110°	789.1	1045.4	3114.5	5695.5	5985.2



TEST NUMBER: P564489

CATALOG NUMBER: SQ4-PR1-150U-100D-935-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	875.1	1115.0	2992.8	5666.4	6153.0
115°	1001.5	1224.5	2815.6	5450.6	6153.0
117.5°	1125.2	1334.4	2698.7	5120.8	5917.0
120°	1200.7	1405.8	2629.5	4884.2	5696.8
122.5°	1272.0	1473.0	2587.5	4630.6	5449.3
125°	1371.1	1571.1	2537.7	4282.4	5030.9
127.5°	1462.3	1658.7	2508.4	3998.3	4656.5
130°	1512.7	1715.2	2495.8	3822.7	4417.4
132.5°	1565.1	1765.6	2483.2	3664.4	4211.9
135°	1643.8	1838.6	2469.6	3457.8	3914.1
137.5°	1722.9	1907.0	2458.0	3290.2	3661.9
140°	1777.5	1949.2	2453.8	3182.3	3513.0
142.5°	1829.9	1991.4	2445.5	3084.9	3374.6
145°	1911.2	2054.7	2435.5	2959.7	3185.3
147.5°	1985.1	2112.2	2424.0	2846.3	3019.6
150°	2039.6	2152.4	2419.8	2784.7	2923.1
152.5°	2090.0	2188.4	2417.7	2727.5	2841.3
155°	2157.6	2242.2	2414.5	2655.1	2742.2
157.5°	2227.9	2286.8	2415.0	2604.6	2662.0
160°	2267.7	2316.4	2417.1	2572.7	2613.8
162.5°	2299.2	2339.7	2419.2	2547.3	2578.1
165°	2349.0	2372.0	2425.0	2519.7	2532.5
167.5°	2383.1	2399.0	2425.5	2495.9	2502.1
170°	2404.0	2411.7	2427.6	2485.3	2485.3
172.5°	2420.8	2422.3	2427.6	2472.7	2470.6
175°	2438.1	2435.5	2427.6	2459.0	2453.8
177.5°	2443.9	2437.7	2427.1	2447.9	2441.8
180°	2435.5	2435.5	2435.5	2435.5	2435.5

(END OF REPORT)