

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519589

Luminaire Tested: **SQ4-WB-150U-075D-935-1D-UNV-STD-W-6**

Issue Date: 4/29/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P519589  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2009-966-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 4/29/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-WB-150U-075D-935-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 11103.6 lumens  
Efficiency: N/A  
Efficacy: 113.5 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 97.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P519589  
CATALOG NUMBER: SQ4-WB-150U-075D-935-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P519589

CATALOG NUMBER: SQ4-WB-150U-075D-935-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	29
1	94	90	86	83	84	81	78	75	64	62	60	48	47	46	34	33	33	26
2	86	79	74	69	77	71	67	63	57	54	51	43	41	39	31	29	28	23
3	79	70	64	58	71	63	58	53	51	47	44	39	36	34	28	26	25	20
4	72	63	55	50	65	57	50	46	45	41	38	35	32	30	25	24	22	18
5	67	56	49	43	60	51	44	40	41	36	33	32	29	26	23	21	20	16
6	62	50	43	38	55	46	39	35	37	32	29	29	26	23	21	19	18	15
7	57	46	38	33	51	42	35	31	34	29	26	26	23	21	20	18	16	13
8	53	41	34	29	48	38	32	27	31	26	23	24	21	19	18	16	15	12
9	49	38	31	26	44	35	29	24	28	24	21	22	19	17	17	15	13	11
10	46	35	28	24	42	32	26	22	26	22	19	21	18	15	16	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13718	13718	13718
5°	13546	13498	13576
10°	12798	12914	13214
15°	11815	12089	12631
20°	10729	11133	11869
25°	9623	10148	11058
30°	8604	9167	10217
35°	7525	8068	9221
40°	6333	6836	7983
45°	5226	5678	6665
50°	4363	4757	5553
55°	3704	4082	4585
60°	3166	3539	3660
65°	2521	2976	2364
70°	2235	2323	1442
75°	2070	1885	884
80°	1906	1732	762
85°	1729	1588	621



TEST NUMBER: P519589

CATALOG NUMBER: SQ4-WB-150U-075D-935-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	204.6	1.8
10°-20°	532.1	4.8
20°-30°	689.2	6.2
30°-40°	674.9	6.1
40°-50°	516.6	4.7
50°-60°	344.2	3.1
60°-70°	187.8	1.7
70°-80°	78.3	0.7
80°-90°	24.7	0.2
90°-100°	565.9	5.1
100°-110°	1530.2	13.8
110°-120°	1608.7	14.5
120°-130°	1306.7	11.8
130°-140°	1025.0	9.2
140°-150°	786.7	7.1
150°-160°	565.8	5.1
160°-170°	345.6	3.1
170°-180°	116.5	1.0
0°-30°	1425.8	12.8
0°-40°	2100.7	18.9
0°-60°	2961.5	26.7
0°-90°	3252.3	29.3
90°-120°	3704.8	33.4
90°-150°	6823.3	61.5
90°-180°	7851.0	70.7
0°-180°	11103.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2230	2230	2230	2230	2230	
5°	2194	2172	2186	2191	2199	204
15°	1855	1849	1898	1950	1984	518
25°	1418	1422	1495	1560	1629	652
35°	1002	1007	1074	1147	1228	623
45°	601	612	653	702	766	469
55°	345	360	381	395	428	313
65°	173	188	204	179	162	180
75°	87	87	79	54	37	93
85°	24	24	22	14	9	27
90°	3	8	17	18	17	7
95°	88	308	941	487	290	92
105°	284	440	1698	2504	2401	300
115°	501	612	1408	2725	3076	494
125°	686	786	1269	2141	2515	611
135°	822	919	1235	1729	1957	635
145°	956	1027	1218	1480	1593	598
155°	1079	1121	1207	1328	1371	498
165°	1174	1186	1212	1260	1266	331
175°	1219	1218	1214	1230	1227	116
180°	1218	1218	1218	1218	1218	

TEST NUMBER: P519589

CATALOG NUMBER: SQ4-WB-150U-075D-935-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2230.2	2230.2	2230.2	2230.2	2230.2
2.5°	2235.6	2215.7	2220.8	2220.6	2214.5
5°	2194.0	2171.9	2186.1	2191.2	2198.8
7.5°	2112.5	2095.9	2121.7	2140.9	2156.4
10°	2049.1	2034.8	2067.7	2095.6	2115.7
12.5°	1975.5	1963.5	2004.3	2041.7	2067.9
15°	1855.4	1848.7	1898.4	1950.1	1983.6
17.5°	1726.8	1723.5	1780.6	1840.9	1883.7
20°	1639.1	1638.1	1700.8	1763.5	1813.3
22.5°	1550.6	1552.7	1618.6	1683.8	1740.5
25°	1417.9	1421.8	1495.3	1560.4	1629.3
27.5°	1295.2	1297.0	1372.9	1441.7	1515.2
30°	1211.5	1216.3	1290.7	1362.0	1438.5
32.5°	1127.7	1133.3	1206.2	1279.8	1357.9
35°	1002.1	1006.8	1074.5	1146.8	1228.1
37.5°	872.5	879.0	939.0	1007.4	1087.4
40°	788.7	798.3	851.4	915.8	994.2
42.5°	708.1	720.0	769.2	830.3	901.1
45°	600.8	612.3	652.7	702.1	766.2
47.5°	508.5	521.7	552.7	595.2	650.0
50°	456.0	468.5	497.1	528.6	580.3
52.5°	409.8	422.3	447.8	472.1	516.1
55°	345.4	359.8	380.7	395.1	427.6
57.5°	292.6	306.4	322.9	329.4	349.2
60°	257.4	272.7	287.7	287.0	297.5
62.5°	225.3	238.3	253.3	242.9	243.5
65°	173.2	187.6	204.5	178.7	162.4
67.5°	139.9	143.0	160.5	124.6	105.3
70°	124.3	124.3	129.2	96.5	80.2
72.5°	109.4	109.4	104.9	78.5	61.5
75°	87.1	87.1	79.3	54.4	37.2
77.5°	67.1	66.4	60.7	40.6	27.0
80°	53.8	53.8	48.9	32.1	21.5
82.5°	42.1	42.1	38.0	25.0	16.0
85°	24.5	24.5	22.5	14.5	8.8
87.5°	9.1	10.2	11.2	8.3	7.3
90°	2.6	7.7	17.0	18.3	17.0
92.5°	37.2	135.7	267.7	116.2	84.2
95°	87.8	308.3	941.2	487.1	289.7
97.5°	141.0	353.5	1467.1	1214.1	891.6
100°	180.9	371.9	1630.7	1700.6	1375.0
102.5°	217.6	397.3	1688.3	2069.5	1826.0
105°	284.4	439.5	1697.5	2503.9	2401.4
107.5°	346.3	487.8	1623.3	2775.0	2809.1
110°	394.6	522.7	1557.2	2847.8	2992.6



TEST NUMBER: P519589

CATALOG NUMBER: SQ4-WB-150U-075D-935-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	437.5	557.5	1496.4	2833.2	3076.5
115°	500.7	612.2	1407.8	2725.3	3076.5
117.5°	562.6	667.2	1349.4	2560.4	2958.5
120°	600.4	702.9	1314.7	2442.1	2848.4
122.5°	636.0	736.5	1293.8	2315.3	2724.7
125°	685.6	785.5	1268.9	2141.2	2515.4
127.5°	731.2	829.3	1254.2	1999.1	2328.3
130°	756.3	857.6	1247.9	1911.4	2208.7
132.5°	782.6	882.8	1241.6	1832.2	2106.0
135°	821.9	919.3	1234.8	1728.9	1957.0
137.5°	861.5	953.5	1229.0	1645.1	1830.9
140°	888.7	974.6	1226.9	1591.2	1756.5
142.5°	914.9	995.7	1222.7	1542.4	1687.3
145°	955.6	1027.4	1217.7	1479.8	1592.6
147.5°	992.5	1056.1	1212.0	1423.2	1509.8
150°	1019.8	1076.2	1209.9	1392.3	1461.6
152.5°	1045.0	1094.2	1208.8	1363.8	1420.7
155°	1078.8	1121.1	1207.3	1327.5	1371.1
157.5°	1113.9	1143.4	1207.5	1302.3	1331.0
160°	1133.9	1158.2	1208.6	1286.4	1306.9
162.5°	1149.6	1169.8	1209.6	1273.7	1289.1
165°	1174.5	1186.0	1212.5	1259.8	1266.2
167.5°	1191.5	1199.5	1212.8	1248.0	1251.0
170°	1202.0	1205.9	1213.8	1242.7	1242.7
172.5°	1210.4	1211.2	1213.8	1236.3	1235.3
175°	1219.1	1217.8	1213.8	1229.5	1226.9
177.5°	1221.9	1218.9	1213.6	1224.0	1220.9
180°	1217.7	1217.7	1217.7	1217.7	1217.7

(END OF REPORT)