

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P565089

Luminaire Tested: **SQ4-PW1-125U-125D-935-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P565089
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-125U-125D-935-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 25596.4 lumens
Efficiency: N/A
Efficacy: 109.5 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 233.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P565089

CATALOG NUMBER: SQ4-PW1-125U-125D-935-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P565089

CATALOG NUMBER: SQ4-PW1-125U-125D-935-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55	49
1	98	93	90	86	90	86	83	80	73	70	68	60	59	57	49	48	47	42
2	89	82	76	70	82	75	70	66	64	60	57	53	50	48	43	41	40	35
3	81	72	65	59	75	66	60	55	56	52	48	47	44	41	38	36	34	30
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29	25
5	68	57	49	43	63	53	45	40	45	39	35	38	33	30	31	28	25	22
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22	19
7	58	46	38	32	53	43	36	31	37	31	27	31	27	23	26	22	20	17
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18	15
9	50	38	31	25	46	35	29	24	31	25	21	26	22	19	22	18	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15182	15182	15182
5°	15280	15159	15092
10°	15158	15036	14954
15°	14998	14832	14776
20°	14818	14591	14562
25°	14612	14346	14302
30°	14303	14086	13994
35°	13896	13700	13619
40°	13463	13253	13201
45°	12939	12769	12712
50°	12403	12298	12215
55°	11824	11824	11637
60°	11102	11316	10915
65°	10160	10667	9907
70°	8956	9816	8721
75°	7649	8786	7442
80°	5931	7394	6009
85°	3836	5678	5064



TEST NUMBER: P565089

CATALOG NUMBER: SQ4-PW1-125U-125D-935-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	464.9	1.8
10°-20°	1312.4	5.1
20°-30°	1946.8	7.6
30°-40°	2277.9	8.9
40°-50°	2267.7	8.9
50°-60°	1958.3	7.7
60°-70°	1409.6	5.5
70°-80°	739.2	2.9
80°-90°	188.0	0.7
90°-100°	944.3	3.7
100°-110°	2543.8	9.9
110°-120°	2669.6	10.4
120°-130°	2166.3	8.5
130°-140°	1699.0	6.6
140°-150°	1304.4	5.1
150°-160°	937.9	3.7
160°-170°	573.0	2.2
170°-180°	193.2	0.8
0°-30°	3724.1	14.5
0°-40°	6002.0	23.4
0°-60°	10228.0	40.0
0°-90°	12564.8	49.1
90°-120°	6157.8	24.1
90°-150°	11327.5	44.3
90°-180°	13032.0	50.9
0°-180°	25596.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4937	4937	4937	4937	4937	
5°	4950	4894	4910	4897	4889	469
15°	4710	4651	4658	4649	4641	1328
25°	4306	4234	4228	4202	4215	1980
35°	3701	3650	3649	3615	3627	2314
45°	2975	2950	2936	2927	2923	2295
55°	2205	2201	2205	2175	2170	1968
65°	1396	1439	1466	1408	1361	1384
75°	644	703	739	690	626	690
85°	109	143	161	152	144	144
90°	5	15	31	33	33	14
95°	144	514	1548	792	548	150
105°	471	732	2813	4209	3950	495
115°	831	1017	2343	4526	5120	817
125°	1134	1302	2104	3555	4184	1013
135°	1366	1524	2044	2868	3248	1054
145°	1579	1702	2019	2452	2633	990
155°	1792	1858	2001	2200	2271	825
165°	1944	1967	2008	2088	2098	548
175°	2021	2019	2011	2039	2034	192
180°	2019	2019	2019	2019	2019	

TEST NUMBER: P565089

CATALOG NUMBER: SQ4-PW1-125U-125D-935-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4936.6	4936.6	4936.6	4936.6	4936.6
2.5°	4964.5	4923.6	4936.6	4925.6	4901.8
5°	4949.7	4894.4	4910.5	4897.3	4888.8
7.5°	4899.2	4848.2	4860.1	4846.0	4840.9
10°	4854.0	4803.0	4814.8	4797.3	4788.7
12.5°	4801.8	4747.4	4759.2	4741.7	4736.6
15°	4710.5	4650.9	4658.3	4649.4	4640.9
17.5°	4604.3	4543.9	4545.2	4531.2	4529.5
20°	4527.8	4464.0	4458.2	4441.0	4449.5
22.5°	4444.3	4377.1	4371.2	4347.1	4359.0
25°	4306.0	4233.7	4227.7	4201.9	4214.6
27.5°	4145.9	4074.4	4074.6	4038.3	4051.9
30°	4027.6	3959.5	3966.7	3923.6	3940.6
32.5°	3902.3	3841.1	3844.9	3801.8	3818.8
35°	3701.4	3650.3	3649.2	3614.7	3627.4
37.5°	3496.1	3451.0	3443.9	3424.0	3427.4
40°	3353.4	3315.2	3301.2	3288.2	3288.2
42.5°	3203.8	3168.9	3155.1	3145.4	3142.0
45°	2975.0	2949.5	2935.9	2927.1	2922.8
47.5°	2748.9	2725.0	2713.2	2707.0	2702.7
50°	2592.3	2575.3	2570.5	2557.4	2553.1
52.5°	2435.7	2425.5	2420.9	2404.3	2400.0
55°	2205.2	2200.9	2205.2	2174.6	2170.4
57.5°	1965.1	1971.9	1986.0	1944.8	1934.6
60°	1805.0	1822.0	1839.8	1791.6	1774.6
62.5°	1641.5	1668.7	1693.7	1638.3	1614.5
65°	1396.2	1438.7	1465.8	1408.2	1361.4
67.5°	1159.6	1212.3	1244.8	1182.7	1130.0
70°	996.0	1055.6	1091.7	1029.5	969.9
72.5°	853.4	919.7	949.0	890.3	830.7
75°	643.7	703.3	739.4	690.1	626.3
77.5°	456.7	512.8	542.8	499.9	447.1
80°	334.9	394.4	417.5	381.8	339.3
82.5°	237.5	286.8	302.7	281.2	252.3
85°	108.7	142.8	160.9	152.0	143.5
87.5°	28.9	54.7	72.3	72.9	76.3
90°	5.1	15.2	30.9	33.4	33.4
92.5°	62.7	221.7	438.2	210.9	146.6
95°	144.0	513.6	1548.1	791.6	547.7
97.5°	229.9	587.9	2428.0	2028.4	1529.6
100°	295.7	617.6	2707.8	2833.2	2350.4
102.5°	359.5	659.2	2800.4	3435.8	3039.6
105°	470.6	732.1	2813.3	4208.9	3949.9
107.5°	575.5	808.8	2693.4	4606.1	4673.0
110°	645.5	866.7	2584.4	4729.5	4973.4



TEST NUMBER: P565089

CATALOG NUMBER: SQ4-PW1-125U-125D-935-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	719.5	924.7	2479.5	4702.2	5103.0
115°	830.6	1016.7	2342.7	4526.5	5119.9
117.5°	931.9	1106.4	2236.7	4246.2	4907.0
120°	997.8	1166.2	2183.2	4045.0	4723.9
122.5°	1055.4	1221.8	2144.2	3839.3	4516.1
125°	1134.0	1302.5	2103.5	3555.3	4183.9
127.5°	1209.7	1375.6	2077.8	3304.8	3866.1
130°	1254.9	1420.9	2067.5	3161.3	3654.2
132.5°	1300.2	1464.1	2057.2	3034.9	3487.5
135°	1365.5	1523.9	2044.4	2868.2	3247.9
137.5°	1427.7	1579.6	2037.7	2726.7	3038.5
140°	1470.9	1616.8	2031.5	2639.7	2921.3
142.5°	1516.2	1652.0	2027.4	2558.4	2795.8
145°	1578.9	1702.1	2018.7	2452.2	2633.3
147.5°	1646.8	1753.9	2009.9	2362.9	2505.2
150°	1692.1	1785.1	2005.8	2306.8	2425.0
152.5°	1733.2	1814.2	2003.7	2261.0	2357.1
155°	1792.4	1857.7	2000.7	2200.3	2270.7
157.5°	1844.3	1895.1	2001.2	2157.6	2204.8
160°	1877.2	1920.0	2003.2	2132.6	2167.8
162.5°	1906.0	1940.7	2005.3	2111.8	2137.0
165°	1944.1	1966.7	2008.4	2088.3	2098.4
167.5°	1974.9	1988.0	2010.9	2070.2	2074.2
170°	1995.5	2000.5	2010.9	2059.8	2059.8
172.5°	2007.9	2008.9	2013.0	2049.5	2049.5
175°	2021.2	2018.7	2010.9	2039.1	2034.1
177.5°	2026.9	2022.9	2012.5	2028.9	2024.8
180°	2018.7	2018.7	2018.7	2018.7	2018.7

(END OF REPORT)