

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519710

Luminaire Tested: **SQ4-075U-0D-935-1D-UNV-STD-W-8**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519710
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-075U-0D-935-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5202.6 lumens
Efficiency: N/A
Efficacy: 142.1 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Indirect


Input Watts (W): 36.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519710

CATALOG NUMBER: SQ4-075U-0D-935-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P519710

CATALOG NUMBER: SQ4-075U-0D-935-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20
RC	80								50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	2969	35256	9623
100°	3114	29926	24645
105°	3301	20351	28922
110°	3461	13865	27777
115°	3579	9996	22591
120°	3653	7917	17433
125°	3635	6683	13242
130°	3585	5853	10390
135°	3558	5265	8392
140°	3551	4830	6958
145°	3550	4478	5875
150°	3584	4218	5096
155°	3632	4022	4558
160°	3662	3879	4204
165°	3684	3790	3968
170°	3693	3725	3820
175°	3698	3682	3722



TEST NUMBER: P519710

CATALOG NUMBER: SQ4-075U-0D-935-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	376.7	7.2
100°-110°	1036.3	19.9
110°-120°	1069.6	20.6
120°-130°	857.0	16.5
130°-140°	673.1	12.9
140°-150°	515.8	9.9
150°-160°	370.9	7.1
160°-170°	226.8	4.4
170°-180°	76.4	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	2482.6	47.7
90°-150°	4528.5	87.0
90°-180°	5203.0	100.0
0°-180°	5202.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	2	7	12	15	15	
95°	56	206	666	285	182	63
105°	185	285	1142	1739	1623	195
115°	328	399	916	1824	2070	324
125°	452	515	831	1406	1646	403
135°	545	605	807	1137	1286	421
145°	630	674	795	968	1043	395
155°	714	737	790	870	896	328
165°	771	781	794	826	831	217
175°	799	800	795	805	804	76
180°	799	799	799	799	799	



TEST NUMBER: P519710

CATALOG NUMBER: SQ4-075U-0D-935-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	1.7	6.7	11.9	15.3	15.3
92.5°	23.4	100.2	173.7	66.7	54.7
95°	56.1	205.6	666.1	284.8	181.8
97.5°	91.4	228.0	1016.4	783.2	552.6
100°	117.2	241.8	1126.5	1137.1	927.7
102.5°	141.7	258.3	1155.1	1410.7	1218.6
105°	185.2	284.9	1141.8	1739.0	1622.7
107.5°	226.7	317.7	1076.9	1899.8	1934.3
110°	256.6	339.6	1028.0	1939.7	2059.4
112.5°	283.8	364.2	979.0	1914.0	2096.1
115°	327.9	399.4	915.8	1823.7	2069.6
117.5°	370.1	435.9	875.7	1697.0	1975.1
120°	395.9	459.0	858.1	1602.0	1889.5
122.5°	419.0	482.1	845.8	1518.8	1791.6
125°	452.0	515.1	830.9	1405.6	1646.5
127.5°	483.2	543.4	821.0	1311.1	1522.4
130°	499.5	561.0	815.6	1255.0	1447.7
132.5°	518.6	580.1	811.5	1205.6	1379.7
135°	545.4	605.2	807.1	1136.7	1286.3
137.5°	570.6	626.1	803.4	1081.1	1204.4
140°	589.6	641.1	802.0	1044.1	1155.4
142.5°	605.9	653.4	799.3	1011.1	1106.5
145°	630.4	673.6	795.2	968.5	1043.3
147.5°	656.6	693.8	793.2	930.8	990.6
150°	672.9	706.1	791.8	910.1	956.6
152.5°	687.8	718.4	790.4	892.2	930.8
155°	713.6	736.9	790.1	870.5	895.5
157.5°	732.3	751.3	790.1	852.7	870.0
160°	745.9	760.9	790.1	843.1	856.4
162.5°	756.8	769.1	791.5	834.9	845.5
165°	771.4	781.4	793.5	825.9	830.9
167.5°	781.6	789.2	795.2	818.3	819.7
170°	788.4	793.4	795.2	815.6	815.6
172.5°	793.8	796.2	795.2	811.5	810.2
175°	798.6	800.3	795.2	805.4	803.7
177.5°	800.0	800.0	794.5	802.6	800.0
180°	798.6	798.6	798.6	798.6	798.6

(END OF REPORT)