

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519782

Luminaire Tested: **SQ4-150U-0D-935-1D-UNV-STD-W-8**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519782
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-150U-0D-935-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10468.3 lumens
Efficiency: N/A
Efficacy: 136.5 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Indirect

Input Watts (W): 76.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519782
CATALOG NUMBER: SQ4-150U-0D-935-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P519782

CATALOG NUMBER: SQ4-150U-0D-935-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20	
RC	80								50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	6198	66421	20447
100°	6408	57759	48706
105°	6761	40340	57070
110°	7096	28005	53818
115°	7287	20490	44775
120°	7386	16174	35040
125°	7352	13607	26974
130°	7238	11941	21135
135°	7149	10741	17023
140°	7136	9851	14103
145°	7175	9144	11959
150°	7243	8593	10380
155°	7321	8193	9305
160°	7422	7911	8554
165°	7479	7721	8063
170°	7507	7581	7761
175°	7527	7494	7575



TEST NUMBER: P519782

CATALOG NUMBER: SQ4-150U-0D-935-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	754.6	7.2
100°-110°	2040.2	19.5
110°-120°	2145.0	20.5
120°-130°	1742.3	16.6
130°-140°	1366.7	13.1
140°-150°	1049.0	10.0
150°-160°	754.4	7.2
160°-170°	460.8	4.4
170°-180°	155.4	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	4939.8	47.2
90°-150°	9097.7	86.9
90°-180°	10468.0	100.0
0°-180°	10468.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	4	10	23	24	23	
95°	117	411	1255	649	386	130
105°	379	586	2263	3339	3202	399
115°	668	816	1877	3634	4102	659
125°	914	1047	1692	2855	3354	815
135°	1096	1226	1646	2305	2609	847
145°	1274	1370	1624	1973	2124	797
155°	1438	1495	1610	1770	1828	663
165°	1566	1581	1617	1680	1688	441
175°	1625	1624	1618	1639	1636	154
180°	1624	1624	1624	1624	1624	



TEST NUMBER: P519782

CATALOG NUMBER: SQ4-150U-OD-935-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	3.5	10.3	22.7	24.4	22.7
92.5°	49.6	180.9	356.9	154.9	112.2
95°	117.1	411.0	1254.9	649.4	386.3
97.5°	188.1	471.4	1956.1	1618.8	1188.8
100°	241.2	495.8	2174.2	2267.5	1833.4
102.5°	290.1	529.7	2251.1	2759.3	2434.6
105°	379.3	586.0	2263.3	3338.6	3201.9
107.5°	461.8	650.4	2164.4	3700.0	3745.4
110°	526.1	697.0	2076.3	3797.0	3990.1
112.5°	583.4	743.4	1995.2	3777.6	4102.0
115°	667.6	816.3	1877.1	3633.7	4102.0
117.5°	750.1	889.6	1799.1	3413.9	3944.7
120°	800.5	937.2	1753.0	3256.1	3797.9
122.5°	848.0	982.0	1725.0	3087.0	3632.9
125°	914.1	1047.4	1691.8	2854.9	3353.9
127.5°	974.9	1105.8	1672.2	2665.5	3104.4
130°	1008.5	1143.5	1663.9	2548.5	2945.0
132.5°	1043.4	1177.0	1655.5	2442.9	2807.9
135°	1095.8	1225.7	1646.4	2305.2	2609.4
137.5°	1148.6	1271.3	1638.7	2193.5	2441.3
140°	1185.0	1299.5	1635.9	2121.5	2342.0
142.5°	1219.9	1327.6	1630.3	2056.6	2249.7
145°	1274.1	1369.8	1623.7	1973.1	2123.5
147.5°	1323.4	1408.2	1616.0	1897.5	2013.1
150°	1359.7	1434.9	1613.2	1856.5	1948.7
152.5°	1393.3	1458.9	1611.8	1818.3	1894.2
155°	1438.4	1494.8	1609.7	1770.0	1828.1
157.5°	1485.2	1524.5	1610.0	1736.4	1774.7
160°	1511.8	1544.3	1611.4	1715.2	1742.5
162.5°	1532.8	1559.8	1612.8	1698.2	1718.7
165°	1566.0	1581.4	1616.7	1679.8	1688.3
167.5°	1588.7	1599.3	1617.0	1664.0	1668.1
170°	1602.7	1607.8	1618.4	1656.9	1656.9
172.5°	1613.9	1614.9	1618.4	1648.4	1647.1
175°	1625.4	1623.7	1618.4	1639.3	1635.9
177.5°	1629.3	1625.2	1618.1	1632.0	1627.9
180°	1623.7	1623.7	1623.7	1623.7	1623.7

(END OF REPORT)