

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519652

Luminaire Tested: **SQ4-025U-0D-840-1D-UNV-STD-W-4**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519652
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-025U-0D-840-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 250 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 975.6 lumens
Efficiency: N/A
Efficacy: 165.4 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 5.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519652
CATALOG NUMBER: SQ4-025U-0D-840-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P519652

CATALOG NUMBER: SQ4-025U-0D-840-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20	
RC	80								50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	1016	13381	4700
100°	1180	11073	8714
105°	1237	7600	10765
110°	1300	5155	10413
115°	1349	3729	8490
120°	1371	2956	6499
125°	1382	2498	4982
130°	1358	2189	3891
135°	1335	1964	3135
140°	1337	1802	2603
145°	1337	1674	2195
150°	1347	1583	1912
155°	1365	1513	1709
160°	1374	1459	1573
165°	1382	1419	1493
170°	1392	1402	1437
175°	1394	1386	1403



TEST NUMBER: P519652

CATALOG NUMBER: SQ4-025U-0D-840-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	73.4	7.5
100°-110°	192.9	19.8
110°-120°	200.0	20.5
120°-130°	160.4	16.4
130°-140°	125.9	12.9
140°-150°	96.6	9.9
150°-160°	69.6	7.1
160°-170°	42.6	4.4
170°-180°	14.4	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	466.2	47.8
90°-150°	849.1	87.0
90°-180°	976.0	100.0
0°-180°	975.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	1	3	8	4	4	
95°	10	38	126	65	44	11
105°	35	53	213	324	302	37
115°	62	75	171	341	389	61
125°	86	96	155	263	310	76
135°	102	113	150	212	240	79
145°	119	126	149	181	195	74
155°	134	138	149	163	168	62
165°	145	147	149	154	156	41
175°	150	150	150	152	152	14
180°	150	150	150	150	150	



TEST NUMBER: P519652

CATALOG NUMBER: SQ4-025U-0D-840-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	1.0	2.9	7.7	3.9	3.9
92.5°	4.1	19.5	43.2	19.1	12.4
95°	9.6	38.0	126.4	65.1	44.4
97.5°	16.8	41.7	189.1	150.4	110.8
100°	22.2	44.8	208.4	211.2	164.0
102.5°	26.8	48.0	213.8	263.1	222.7
105°	34.7	52.7	213.2	323.7	302.0
107.5°	42.8	59.4	201.1	355.2	360.5
110°	48.2	63.3	191.1	363.3	386.0
112.5°	53.6	68.0	181.8	358.2	392.9
115°	61.8	75.0	170.8	340.7	388.9
117.5°	69.7	81.7	163.3	316.5	369.9
120°	74.3	85.6	160.2	300.3	352.2
122.5°	78.9	90.3	157.9	284.1	335.2
125°	85.9	96.3	155.3	262.6	309.7
127.5°	91.5	102.0	153.2	245.2	285.0
130°	94.6	105.9	152.5	234.3	271.1
132.5°	97.6	109.0	151.7	225.0	258.0
135°	102.3	112.7	150.5	212.0	240.3
137.5°	107.1	117.3	150.3	202.2	225.4
140°	111.0	120.4	149.6	194.4	216.1
142.5°	114.1	122.7	149.6	189.0	207.6
145°	118.7	126.2	148.6	180.8	194.9
147.5°	123.3	130.7	148.6	173.9	185.6
150°	126.4	133.0	148.6	170.0	179.5
152.5°	129.5	134.6	148.6	166.9	174.1
155°	134.1	137.9	148.6	163.2	167.9
157.5°	137.6	141.2	148.6	159.9	163.3
160°	139.9	142.7	148.6	158.3	160.2
162.5°	142.2	144.3	148.6	156.7	158.6
165°	144.7	146.6	148.6	154.4	156.3
167.5°	147.1	148.0	149.6	153.4	154.2
170°	148.6	149.5	149.6	153.4	153.4
172.5°	149.4	149.6	149.6	152.6	151.9
175°	150.5	150.5	149.6	151.5	151.5
177.5°	150.5	150.5	149.8	151.3	150.5
180°	150.5	150.5	150.5	150.5	150.5

(END OF REPORT)