

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937118

Luminaire Tested: SQ4-FB-075U-075D-840-1D-UNV-STD-W-4

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937118
REPORT IS A COMBINATION OF REPORTS P933502 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-075U-075D-840-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5337.1 lumens
Efficiency: N/A
Efficacy: 125.9 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 42.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937118
CATALOG NUMBER: SQ4-FB-075U-075D-840-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P937118

CATALOG NUMBER: SQ4-FB-075U-075D-840-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45	45	45	45
1	96	92	88	84	88	84	80	77	70	67	65	57	55	53	44	43	42	37	37	37	37
2	87	79	73	68	79	73	67	63	60	56	53	49	46	44	38	36	35	30	30	30	30
3	79	69	62	56	72	64	57	52	53	48	44	43	39	36	34	31	29	25	25	25	25
4	72	61	53	47	65	56	49	43	46	41	37	38	34	31	30	27	24	21	21	21	21
5	66	54	46	39	60	50	42	37	41	36	31	34	29	26	26	23	21	17	17	17	17
6	60	48	40	34	55	44	37	31	37	31	27	30	26	22	24	21	18	15	15	15	15
7	56	43	35	29	51	40	32	27	33	28	23	27	23	20	21	18	16	13	13	13	13
8	51	39	31	26	47	36	29	24	30	24	21	25	20	17	20	16	14	11	11	11	11
9	48	35	28	23	44	33	26	21	27	22	18	22	18	15	18	15	12	10	10	10	10
10	44	32	25	20	41	30	23	19	25	20	16	21	17	14	16	13	11	9	9	9	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2852	2852	2852
5°	2783	3293	3833
10°	2521	4796	6354
15°	2140	6262	7672
20°	1740	7251	7819
25°	1450	7583	7660
30°	1221	7625	7645
35°	1078	7492	7844
40°	937	7321	8048
45°	848	7194	8079
50°	775	7079	7946
55°	740	6913	7593
60°	756	6600	7036
65°	781	6129	6273
70°	828	5335	5300
75°	908	4338	4136
80°	969	2998	2786
85°	820	1583	1426

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 8079 cd/sqm



TEST NUMBER: P937118

CATALOG NUMBER: SQ4-FB-075U-075D-840-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.7	0.7
10°-20°	176.2	3.3
20°-30°	308.1	5.8
30°-40°	396.6	7.4
40°-50°	443.0	8.3
50°-60°	424.3	8.0
60°-70°	336.3	6.3
70°-80°	197.7	3.7
80°-90°	56.7	1.1
90°-100°	222.5	4.2
100°-110°	584.8	11.0
110°-120°	606.4	11.4
120°-130°	486.4	9.1
130°-140°	381.7	7.2
140°-150°	292.9	5.5
150°-160°	211.0	4.0
160°-170°	129.1	2.4
170°-180°	43.6	0.8
0°-30°	524.0	9.8
0°-40°	920.7	17.3
0°-60°	1788.1	33.5
0°-90°	2378.8	44.6
90°-120°	1413.7	26.5
90°-150°	2574.7	48.2
90°-180°	2958.0	55.4
0°-180°	5337.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	307	307	307	307	307	
5°	299	321	362	409	424	28
15°	224	414	698	846	872	62
25°	143	469	831	868	868	66
35°	97	449	782	827	860	60
45°	66	358	692	792	828	51
55°	47	227	587	682	700	43
65°	38	120	436	490	497	37
75°	28	74	239	263	264	29
85°	10	23	59	65	66	10
90°	3	9	23	12	12	3
95°	29	115	383	198	134	33
105°	105	160	646	982	916	112
115°	187	227	518	1033	1179	185
125°	260	292	471	796	939	231
135°	310	342	456	643	729	240
145°	360	383	450	548	591	225
155°	407	418	450	495	509	187
165°	439	445	450	468	474	124
175°	456	456	454	459	459	43
180°	456	456	456	456	456	



TEST NUMBER: P937118
 CATALOG NUMBER: SQ4-FB-075U-075D-840-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	307.3	307.3	307.3	307.3	307.3	307.3	307.3	307.3	307.3	307.3	307.3
2.5°	307.3	307.3	309.2	310.2	312.2	313.2	315.2	317.1	323.1	324.1	326.0
5°	299.4	303.3	316.2	321.1	334.9	353.7	361.6	374.5	401.1	409.0	414.0
7.5°	287.5	296.4	328.0	335.9	370.5	419.9	440.6	468.3	510.8	531.5	548.3
10°	268.7	287.5	343.8	362.6	418.9	494.0	532.5	571.1	635.3	663.9	674.8
12.5°	248.0	278.6	360.6	386.3	467.3	577.0	623.4	665.9	739.0	777.6	783.5
15°	224.3	265.8	376.4	414.0	518.7	646.2	697.5	749.9	818.1	845.7	852.6
17.5°	203.5	255.9	391.2	430.8	558.2	708.4	760.8	804.2	859.6	878.3	883.3
20°	177.8	240.1	401.1	452.5	599.7	753.8	804.2	837.8	875.4	887.2	889.2
22.5°	159.1	223.3	407.1	460.4	627.4	781.5	824.0	850.7	876.4	880.3	881.3
25°	143.3	204.5	406.1	469.3	651.1	798.3	830.9	850.7	865.5	867.5	867.5
27.5°	128.4	183.8	402.1	471.3	668.9	802.3	827.9	841.8	848.7	852.6	852.6
30°	115.6	164.0	392.2	467.3	676.8	798.3	819.1	826.0	832.9	838.8	841.8
32.5°	105.7	145.2	377.4	459.4	677.8	788.4	803.2	807.2	817.1	830.9	835.8
35°	96.8	126.5	360.6	448.6	671.8	772.6	782.5	786.4	806.2	827.0	833.9
37.5°	87.9	112.6	338.9	429.8	662.9	753.8	760.8	767.7	798.3	823.0	830.9
40°	79.0	100.8	313.2	409.0	649.1	731.1	737.0	747.9	788.4	817.1	825.0
42.5°	72.1	90.9	285.5	387.3	631.3	705.4	714.3	730.1	776.6	807.2	816.1
45°	66.2	81.0	255.9	357.7	608.6	678.8	691.6	713.3	762.7	792.4	800.3
47.5°	60.3	74.1	225.3	327.0	583.9	652.1	668.9	693.6	744.0	772.6	779.5
50°	55.3	67.2	194.6	294.4	557.2	623.4	643.2	668.9	720.3	746.9	755.8
52.5°	51.4	61.3	166.0	261.8	526.6	593.8	616.5	643.2	691.6	717.3	723.2
55°	47.4	56.3	141.3	227.2	495.0	562.2	586.9	612.6	660.0	681.7	685.7
57.5°	45.4	52.4	120.5	194.6	461.4	526.6	554.3	578.0	622.4	639.2	643.2
60°	42.5	49.4	104.7	167.0	424.8	493.0	516.7	540.4	578.0	591.8	594.8
62.5°	39.5	47.4	92.9	140.3	387.3	453.5	477.2	498.9	530.6	540.4	544.4
65°	37.5	45.4	84.0	120.5	348.8	412.0	435.7	454.5	480.2	490.0	492.0
67.5°	35.6	43.5	77.1	103.7	310.2	370.5	388.3	406.1	425.8	435.7	436.7
70°	32.6	41.5	71.1	91.9	270.7	323.1	337.9	356.7	372.5	377.4	380.4
72.5°	30.6	38.5	67.2	83.0	230.2	277.6	291.5	302.3	316.2	321.1	321.1
75°	27.7	34.6	63.2	74.1	188.7	227.2	239.1	250.0	260.8	262.8	259.8
77.5°	24.7	30.6	54.3	62.2	147.2	179.8	189.7	195.6	204.5	206.5	207.5
80°	20.7	26.7	42.5	48.4	106.7	132.4	139.3	144.2	152.2	152.2	154.1
82.5°	15.8	20.7	30.6	34.6	72.1	90.9	96.8	99.8	104.7	104.7	104.7
85°	9.9	12.8	19.8	22.7	43.5	55.3	59.3	60.3	64.2	65.2	65.2
87.5°	4.9	6.9	12.8	13.8	22.7	28.7	28.7	30.6	30.6	29.6	28.7
90°	3.1	5.5	8.0	8.6	13.5	20.1	23.3	20.7	15.5	11.7	11.7
92.5°	12.3	33.1	53.8	59.1	83.1	115.1	131.1	114.9	82.5	58.2	55.9
95°	29.4	67.6	105.7	115.2	204.5	323.6	383.1	341.8	259.4	197.5	190.5
97.5°	50.9	84.5	118.1	126.5	275.5	474.0	573.3	547.3	495.2	456.1	442.7
100°	67.4	97.8	128.3	135.9	301.2	521.7	631.8	633.7	637.6	640.4	624.5
102.5°	81.5	110.0	138.3	145.4	313.1	536.7	648.4	681.6	748.0	797.8	784.2
105°	105.3	129.4	153.5	159.6	321.9	538.4	646.5	721.0	869.9	981.6	974.3
107.5°	129.8	152.3	174.8	180.4	323.6	514.4	609.8	713.6	921.3	1077.1	1078.9
110°	146.4	166.7	187.0	192.1	321.1	493.1	579.2	695.3	927.4	1101.6	1109.2



TEST NUMBER: P937118

CATALOG NUMBER: SQ4-FB-075U-075D-840-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	162.6	182.0	201.3	206.1	321.2	474.6	551.3	670.2	907.8	1086.0	1097.8
115°	187.1	204.9	222.8	227.2	324.2	453.3	517.9	632.4	861.3	1033.1	1049.3
117.5°	211.3	227.5	243.7	247.8	330.2	440.0	494.9	598.2	804.8	959.8	977.8
120°	225.5	240.7	255.9	259.7	335.0	435.5	485.7	580.2	769.0	910.5	928.0
122.5°	239.2	254.6	269.9	273.8	342.0	433.1	478.7	563.7	733.7	861.2	878.5
125°	260.3	274.4	288.4	291.9	351.6	431.3	471.1	543.3	687.7	796.0	811.9
127.5°	277.5	291.7	305.8	309.3	361.1	430.2	464.7	526.7	650.7	743.7	757.1
130°	286.7	301.9	317.1	321.0	368.0	430.8	462.2	517.4	627.8	710.6	722.9
132.5°	296.2	311.4	326.6	330.5	373.7	431.3	460.0	509.4	608.3	682.4	693.5
135°	310.2	324.1	338.0	341.5	379.8	430.9	456.4	497.8	580.5	642.6	652.2
137.5°	324.7	338.4	352.1	355.6	389.0	433.5	455.8	490.7	560.7	613.2	621.0
140°	336.6	349.3	361.9	365.1	394.6	433.9	453.6	483.8	544.2	589.5	596.9
142.5°	345.8	357.5	369.1	372.1	399.3	435.5	453.6	480.2	533.2	573.0	579.4
145°	359.8	370.1	380.3	382.8	405.4	435.5	450.5	472.3	515.6	548.2	553.0
147.5°	374.0	383.8	393.8	396.3	414.4	438.5	450.5	467.6	501.8	527.4	531.3
150°	383.1	392.1	401.1	403.4	419.1	440.1	450.5	465.0	493.8	515.4	518.6
152.5°	392.6	399.4	406.3	407.9	422.2	441.0	450.5	462.9	487.5	506.0	508.3
155°	406.8	411.8	416.7	418.0	428.9	443.3	450.5	460.3	479.9	494.6	496.2
157.5°	417.1	422.1	427.0	428.2	435.6	445.6	450.5	458.1	473.4	484.8	485.9
160°	424.1	428.0	431.8	432.7	438.7	446.6	450.5	457.0	470.2	480.0	480.6
162.5°	431.3	434.1	437.0	437.7	441.9	447.7	450.5	456.1	467.0	475.3	475.9
165°	438.9	441.4	444.0	444.7	446.7	449.2	450.5	454.5	462.4	468.3	469.0
167.5°	445.9	447.1	448.4	448.7	450.3	452.5	453.6	456.2	461.4	465.2	465.5
170°	450.5	451.7	453.0	453.3	453.4	453.5	453.6	456.2	461.4	465.2	465.2
172.5°	453.0	453.3	453.5	453.6	453.6	453.6	453.6	455.7	459.7	462.8	462.6
175°	456.4	456.4	456.4	456.4	455.5	454.2	453.6	454.9	457.4	459.4	459.4
177.5°	456.4	456.4	456.4	456.4	455.7	454.7	454.2	455.2	457.2	458.8	458.5
180°	456.4	456.4	456.4	456.4	456.4	456.4	456.4	456.4	456.4	456.4	456.4



TEST NUMBER: P937118

CATALOG NUMBER: SQ4-FB-075U-075D-840-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	307.3	307.3
2.5°	328.0	326.0
5°	421.9	423.9
7.5°	568.1	567.1
10°	706.4	715.3
12.5°	807.2	809.2
15°	868.5	872.4
17.5°	892.2	893.2
20°	893.2	891.2
22.5°	882.3	880.3
25°	869.4	868.5
27.5°	857.6	858.6
30°	852.6	855.6
32.5°	852.6	857.6
35°	854.6	859.6
37.5°	853.6	859.6
40°	849.7	856.6
42.5°	838.8	843.8
45°	822.0	827.9
47.5°	800.3	804.2
50°	772.6	776.6
52.5°	738.0	739.0
55°	696.5	700.5
57.5°	652.1	653.1
60°	602.7	605.6
62.5°	550.3	550.3
65°	495.0	497.0
67.5°	437.7	442.6
70°	379.4	380.4
72.5°	322.1	322.1
75°	262.8	263.8
77.5°	206.5	206.5
80°	153.1	154.1
82.5°	105.7	107.7
85°	66.2	66.2
87.5°	30.6	27.7
90°	11.7	11.7
92.5°	46.6	37.3
95°	162.5	134.5
97.5°	389.4	336.0
100°	561.0	497.4
102.5°	729.7	675.3
105°	945.0	915.8
107.5°	1086.0	1093.1
110°	1139.8	1170.3



TEST NUMBER: P937118

CATALOG NUMBER: SQ4-FB-075U-075D-840-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	1144.6	1191.4
115°	1114.3	1179.2
117.5°	1049.8	1121.9
120°	998.0	1067.9
122.5°	947.5	1016.6
125°	875.5	939.0
127.5°	810.7	864.3
130°	772.5	822.0
132.5°	737.8	782.2
135°	690.4	728.6
137.5°	652.3	683.6
140°	626.2	655.4
142.5°	604.5	629.7
145°	572.1	591.1
147.5°	547.2	563.0
150°	531.4	544.3
152.5°	518.0	527.7
155°	502.6	509.0
157.5°	490.4	494.9
160°	483.1	485.7
162.5°	478.4	480.9
165°	471.6	474.1
167.5°	466.6	467.7
170°	465.2	465.2
172.5°	461.6	460.6
175°	459.4	459.4
177.5°	457.4	456.4
180°	456.4	456.4



TEST NUMBER: P937118
 CATALOG NUMBER: SQ4-FB-075U-075D-840-1D-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.11	4.96	5.11	5.97	7.32	17.25	18.10	18.25	19.11	20.46
	3H	4.82	5.58	5.82	6.60	7.96	19.08	19.84	20.08	20.86	22.22
	4H	5.12	5.84	6.14	6.86	8.23	19.71	20.43	20.73	21.46	22.83
	6H	5.37	6.03	6.40	7.06	8.45	20.13	20.79	21.16	21.82	23.21
	8H	5.43	6.07	6.47	7.11	8.49	20.24	20.88	21.28	21.92	23.30
	12H	5.45	6.06	6.49	7.09	8.50	20.30	20.91	21.34	21.94	23.35
4H	2H	11.30	12.03	12.33	13.05	14.42	17.53	18.25	18.55	19.27	20.64
	3H	12.87	13.48	13.91	14.53	15.91	19.56	20.16	20.59	21.21	22.60
	4H	12.97	13.52	14.01	14.56	15.97	20.31	20.87	21.35	21.91	23.32
	6H	12.98	13.45	14.03	14.52	15.92	20.84	21.32	21.89	22.38	23.79
	8H	12.95	13.40	14.01	14.46	15.88	20.99	21.44	22.05	22.50	23.92
	12H	12.91	13.31	13.98	14.39	15.81	21.08	21.48	22.15	22.56	23.98
8H	4H	14.40	14.85	15.45	15.91	17.32	20.37	20.82	21.42	21.88	23.30
	6H	14.64	15.01	15.72	16.11	17.53	20.99	21.36	22.06	22.46	23.88
	8H	14.66	14.98	15.74	16.07	17.50	21.20	21.53	22.28	22.61	24.05
	12H	14.63	14.91	15.72	15.99	17.47	21.34	21.62	22.42	22.70	24.18
12H	4H	14.54	14.94	15.61	16.02	17.44	20.32	20.73	21.40	21.80	23.23
	6H	14.90	15.22	15.98	16.31	17.74	20.97	21.30	22.05	22.38	23.82
	8H	14.96	15.25	16.05	16.33	17.81	21.19	21.48	22.28	22.56	24.04