

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563748

Luminaire Tested: **SQ4-PP3-125U-125D-935-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563748
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-125U-125D-935-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17156.8 lumens
Efficiency: N/A
Efficacy: 112.4 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 152.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563748
CATALOG NUMBER: SQ4-PP3-125U-125D-935-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P563748

CATALOG NUMBER: SQ4-PP3-125U-125D-935-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	49
1	98	94	90	86	90	86	83	80	73	71	69	61	59	58	49	48	47	42
2	89	82	76	71	82	76	71	66	64	60	57	54	51	48	44	42	40	35
3	81	72	65	59	75	67	60	55	57	52	48	47	44	41	39	36	34	30
4	75	64	56	50	69	59	52	47	50	45	41	42	38	35	35	32	30	26
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	31	28	26	23
6	63	51	43	37	58	48	40	35	41	35	31	34	30	27	28	25	23	20
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15259	15259	15259
5°	15371	15277	15223
10°	15345	15236	15168
15°	15243	15160	15077
20°	15142	15057	14943
25°	14962	14859	14711
30°	14685	14608	14423
35°	14301	14203	14024
40°	13844	13757	13599
45°	13465	13371	13239
50°	12982	12899	12775
55°	12310	12148	12054
60°	11207	10886	10832
65°	9873	9462	9430
70°	8524	8172	8172
75°	7338	7235	7131
80°	6469	6546	6392
85°	5065	5526	5526



TEST NUMBER: P563748

CATALOG NUMBER: SQ4-PP3-125U-125D-935-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	312.8	1.8
10°-20°	893.1	5.2
20°-30°	1337.7	7.8
30°-40°	1569.1	9.1
40°-50°	1574.0	9.2
50°-60°	1342.7	7.8
60°-70°	875.7	5.1
70°-80°	439.3	2.6
80°-90°	124.7	0.7
90°-100°	629.6	3.7
100°-110°	1695.9	9.9
110°-120°	1779.8	10.4
120°-130°	1444.2	8.4
130°-140°	1132.7	6.6
140°-150°	869.6	5.1
150°-160°	625.2	3.6
160°-170°	382.0	2.2
170°-180°	128.8	0.8
0°-30°	2543.5	14.8
0°-40°	4112.6	24.0
0°-60°	7029.3	41.0
0°-90°	8469.1	49.4
90°-120°	4105.2	23.9
90°-150°	7551.7	44.0
90°-180°	8688.0	50.6
0°-180°	17156.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3308	3308	3308	3308	3308	
5°	3319	3288	3299	3287	3287	315
15°	3192	3161	3174	3163	3157	900
25°	2940	2906	2919	2893	2890	1352
35°	2540	2514	2522	2493	2490	1586
45°	2064	2050	2050	2029	2029	1589
55°	1531	1525	1510	1502	1499	1360
65°	904	888	867	861	864	903
75°	412	412	406	403	400	447
85°	96	104	104	104	104	112
90°	3	10	21	22	22	10
95°	96	342	1032	528	365	100
105°	314	488	1876	2806	2633	330
115°	554	678	1562	3018	3413	545
125°	756	868	1402	2370	2789	675
135°	910	1016	1363	1912	2165	703
145°	1053	1135	1346	1635	1756	660
155°	1195	1238	1334	1467	1514	550
165°	1296	1311	1339	1392	1399	365
175°	1348	1346	1341	1359	1356	128
180°	1346	1346	1346	1346	1346	



TEST NUMBER: P563748

CATALOG NUMBER: SQ4-PP3-125U-125D-935-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3307.7	3307.7	3307.7	3307.7	3307.7
2.5°	3328.6	3301.4	3307.7	3302.7	3289.1
5°	3319.3	3288.1	3299.0	3287.4	3287.4
7.5°	3296.7	3262.7	3273.5	3261.9	3261.3
10°	3275.8	3241.8	3252.6	3241.0	3238.1
12.5°	3245.7	3211.6	3224.8	3210.9	3210.3
15°	3191.7	3160.6	3174.3	3162.6	3157.0
17.5°	3130.9	3096.8	3113.5	3097.2	3094.9
20°	3084.5	3050.5	3067.1	3043.9	3043.9
22.5°	3028.8	2994.8	3013.7	2983.6	2983.6
25°	2939.5	2905.5	2919.2	2893.1	2890.2
27.5°	2833.4	2800.0	2814.3	2784.7	2784.1
30°	2756.9	2725.7	2742.4	2710.4	2707.6
32.5°	2673.4	2644.5	2656.6	2624.6	2621.8
35°	2539.5	2514.0	2522.1	2493.0	2490.2
37.5°	2398.6	2372.5	2381.8	2356.8	2355.7
40°	2298.9	2281.9	2284.4	2263.9	2258.3
42.5°	2206.1	2186.8	2189.3	2169.0	2167.8
45°	2064.0	2049.9	2049.6	2029.3	2029.3
47.5°	1913.3	1902.5	1899.4	1882.6	1882.0
50°	1808.9	1800.4	1797.3	1782.8	1780.0
52.5°	1699.9	1696.0	1686.0	1673.8	1673.3
55°	1530.6	1525.0	1510.4	1501.6	1498.8
57.5°	1346.8	1335.5	1319.0	1306.3	1308.6
60°	1214.7	1203.3	1179.9	1174.1	1174.1
62.5°	1087.1	1073.5	1050.0	1042.0	1046.5
65°	904.5	887.5	866.8	861.1	863.9
67.5°	738.7	723.3	701.0	700.9	698.6
70°	632.0	623.5	605.9	605.9	605.9
72.5°	536.9	532.9	520.1	520.0	517.8
75°	411.7	411.7	405.9	402.9	400.1
77.5°	308.4	309.6	306.7	303.7	298.6
80°	243.5	249.2	246.4	243.4	240.6
82.5°	183.2	188.9	188.4	183.2	182.6
85°	95.7	104.2	104.4	104.4	104.4
87.5°	26.2	36.6	41.2	41.6	43.9
90°	3.4	10.1	20.6	22.3	22.3
92.5°	41.8	147.8	292.1	140.6	97.7
95°	96.0	342.4	1032.0	527.8	365.2
97.5°	153.3	392.0	1618.7	1352.3	1019.7
100°	197.2	411.7	1805.2	1888.8	1566.9
102.5°	239.7	439.5	1866.9	2290.6	2026.4
105°	313.7	488.1	1875.5	2805.9	2633.3
107.5°	383.7	539.2	1795.6	3070.7	3115.3
110°	430.3	577.8	1722.9	3153.0	3315.6

TEST NUMBER: P563748

CATALOG NUMBER: SQ4-PP3-125U-125D-935-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	479.7	616.5	1653.0	3134.8	3402.0
115°	553.7	677.8	1561.8	3017.7	3413.3
117.5°	621.3	737.6	1491.2	2830.8	3271.3
120°	665.2	777.5	1455.5	2696.7	3149.3
122.5°	703.6	814.5	1429.4	2559.5	3010.8
125°	756.0	868.3	1402.3	2370.2	2789.3
127.5°	806.4	917.1	1385.2	2203.2	2577.4
130°	836.6	947.2	1378.3	2107.6	2436.1
132.5°	866.8	976.1	1371.5	2023.3	2325.0
135°	910.3	1015.9	1362.9	1912.1	2165.2
137.5°	951.8	1053.1	1358.5	1817.8	2025.7
140°	980.6	1077.8	1354.3	1759.8	1947.5
142.5°	1010.8	1101.3	1351.6	1705.6	1863.9
145°	1052.6	1134.8	1345.8	1634.8	1755.5
147.5°	1097.9	1169.3	1339.9	1575.3	1670.1
150°	1128.0	1190.1	1337.2	1537.9	1616.6
152.5°	1155.5	1209.5	1335.8	1507.3	1571.4
155°	1194.9	1238.5	1333.8	1466.8	1513.8
157.5°	1229.5	1263.4	1334.1	1438.4	1469.9
160°	1251.5	1280.0	1335.5	1421.7	1445.2
162.5°	1270.7	1293.8	1336.9	1407.9	1424.6
165°	1296.1	1311.1	1338.9	1392.2	1398.9
167.5°	1316.6	1325.3	1340.6	1380.1	1382.8
170°	1330.3	1333.7	1340.6	1373.2	1373.2
172.5°	1338.6	1339.2	1342.0	1366.3	1366.3
175°	1347.5	1345.8	1340.6	1359.4	1356.1
177.5°	1351.3	1348.6	1341.7	1352.6	1349.9
180°	1345.8	1345.8	1345.8	1345.8	1345.8

(END OF REPORT)