

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562706

Luminaire Tested: **SQ4-PC3-075U-050D-840-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562706  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-075U-050D-840-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 750 LUMENS PER FOOT  
Light Source: 4000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5012.8 lumens  
Efficiency: N/A  
Efficacy: 144.5 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 34.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562706  
CATALOG NUMBER: SQ4-PC3-075U-050D-840-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P562706

CATALOG NUMBER: SQ4-PC3-075U-050D-840-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47	40				
1	96	91	87	84	87	83	80	77	68	66	64	54	53	51	41	40	39	34				
2	87	80	74	69	79	73	68	63	60	56	53	48	45	43	36	35	33	28				
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	32	30	28	24				
4	72	62	54	48	66	57	50	45	47	42	38	37	34	31	29	26	24	20				
5	66	55	47	41	60	50	43	38	42	36	32	33	30	27	26	23	21	18				
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	21	19	15				
7	56	44	37	31	51	41	34	29	34	29	25	27	23	21	21	19	16	14				
8	52	40	33	27	47	37	30	25	31	26	22	25	21	18	20	17	15	12				
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11				
10	45	33	26	22	41	31	25	20	26	21	17	21	17	15	17	14	12	10				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6719	6719	6719
5°	6770	6727	6702
10°	6754	6722	6703
15°	6719	6719	6712
20°	6674	6694	6694
25°	6611	6660	6638
30°	6531	6609	6581
35°	6433	6533	6486
40°	6327	6417	6352
45°	6212	6256	6160
50°	6050	6050	5952
55°	5858	5781	5696
60°	5574	5464	5375
65°	5152	5050	5006
70°	4510	4548	4529
75°	3629	4014	4039
80°	2582	3406	3438
85°	1567	2858	2858



TEST NUMBER: P562706

CATALOG NUMBER: SQ4-PC3-075U-050D-840-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	68.9	1.4
10°-20°	197.8	3.9
20°-30°	299.6	6.0
30°-40°	359.1	7.2
40°-50°	366.2	7.3
50°-60°	319.7	6.4
60°-70°	228.8	4.6
70°-80°	117.9	2.4
80°-90°	31.0	0.6
90°-100°	218.9	4.4
100°-110°	602.3	12.0
110°-120°	621.7	12.4
120°-130°	498.1	9.9
130°-140°	391.2	7.8
140°-150°	299.8	6.0
150°-160°	215.6	4.3
160°-170°	131.8	2.6
170°-180°	44.4	0.9
0°-30°	566.3	11.3
0°-40°	925.4	18.5
0°-60°	1611.3	32.1
0°-90°	1988.9	39.7
90°-120°	1442.9	28.8
90°-150°	2632.1	52.5
90°-180°	3024.0	60.3
0°-180°	5012.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	728	728	728	728	728	
5°	731	724	726	724	724	69
15°	703	697	703	703	703	198
25°	649	645	654	652	652	299
35°	571	570	580	576	576	357
45°	476	475	480	473	472	366
55°	364	360	359	354	354	325
65°	236	231	231	229	229	233
75°	102	106	113	113	113	110
85°	15	23	27	28	27	20
90°	1	4	7	9	9	3
95°	33	120	387	166	106	34
105°	108	166	664	1011	943	113
115°	191	232	532	1060	1203	188
125°	263	299	483	817	957	234
135°	317	352	469	661	748	245
145°	366	392	462	563	606	230
155°	415	428	459	506	520	191
165°	448	454	461	480	483	126
175°	464	465	462	468	467	44
180°	464	464	464	464	464	

TEST NUMBER: P562706

CATALOG NUMBER: SQ4-PC3-075U-050D-840-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	728.3	728.3	728.3	728.3	728.3
2.5°	732.7	726.3	728.3	726.7	724.0
5°	731.0	723.8	726.3	724.3	723.6
7.5°	725.8	718.5	721.9	720.5	719.8
10°	720.9	713.7	717.5	716.2	715.5
12.5°	714.4	707.7	712.1	710.8	710.7
15°	703.4	697.4	703.4	703.4	702.7
17.5°	689.5	684.1	690.4	690.8	690.4
20°	679.8	673.8	681.8	681.1	681.8
22.5°	667.9	663.0	671.6	669.8	670.5
25°	649.4	644.8	654.2	652.1	652.1
27.5°	627.6	624.3	634.5	632.3	632.3
30°	613.0	609.7	620.4	617.7	617.7
32.5°	596.8	594.6	604.8	601.6	601.6
35°	571.2	569.9	580.0	575.9	575.9
37.5°	544.8	543.6	552.7	547.8	546.3
40°	525.3	524.7	532.8	527.4	527.4
42.5°	505.9	505.3	512.3	505.8	505.8
45°	476.1	474.8	479.5	473.4	472.1
47.5°	443.6	442.3	445.2	438.6	437.9
50°	421.5	420.2	421.5	415.4	414.7
52.5°	398.8	396.5	396.7	390.6	390.5
55°	364.2	359.6	359.4	354.1	354.1
57.5°	327.5	321.4	322.0	317.4	316.7
60°	302.1	295.5	296.1	292.0	291.3
62.5°	277.3	269.7	271.2	266.6	266.5
65°	236.0	230.8	231.3	229.3	229.3
67.5°	196.4	191.5	195.0	193.4	193.3
70°	167.2	164.0	168.6	168.6	167.9
72.5°	140.3	140.1	145.9	145.9	146.3
75°	101.8	106.4	112.6	113.3	113.3
77.5°	68.0	76.2	82.9	83.2	83.1
80°	48.6	57.8	64.1	65.4	64.7
82.5°	32.9	42.7	47.9	49.2	48.6
85°	14.8	22.7	27.0	27.6	27.0
87.5°	4.5	9.8	12.2	12.5	11.5
90°	1.0	3.9	6.9	8.9	8.9
92.5°	13.6	58.2	100.9	38.8	31.8
95°	32.6	119.5	387.1	165.5	105.7
97.5°	53.1	132.5	590.8	455.2	321.2
100°	68.1	140.6	654.8	660.9	539.2
102.5°	82.4	150.2	671.4	819.9	708.3
105°	107.6	165.6	663.7	1010.8	943.2
107.5°	131.7	184.7	625.9	1104.2	1124.3
110°	149.1	197.4	597.5	1127.4	1197.0



TEST NUMBER: P562706

CATALOG NUMBER: SQ4-PC3-075U-050D-840-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	164.9	211.7	569.1	1112.5	1218.3
115°	190.6	232.1	532.3	1060.0	1202.9
117.5°	215.1	253.3	509.0	986.3	1148.0
120°	230.1	266.8	498.7	931.2	1098.2
122.5°	243.5	280.2	491.6	882.8	1041.3
125°	262.7	299.4	482.9	817.0	957.0
127.5°	280.9	315.8	477.2	762.1	884.9
130°	290.4	326.1	474.1	729.4	841.4
132.5°	301.4	337.1	471.7	700.7	801.9
135°	317.0	351.8	469.1	660.7	747.6
137.5°	331.6	363.9	466.9	628.4	700.0
140°	342.7	372.6	466.1	606.9	671.6
142.5°	352.2	379.8	464.6	587.7	643.1
145°	366.4	391.5	462.2	562.9	606.4
147.5°	381.6	403.2	461.0	541.0	575.8
150°	391.1	410.4	460.2	529.0	556.0
152.5°	399.8	417.6	459.4	518.6	541.0
155°	414.8	428.3	459.2	506.0	520.5
157.5°	425.7	436.7	459.2	495.6	505.7
160°	433.6	442.2	459.2	490.0	497.8
162.5°	439.9	447.0	460.0	485.3	491.4
165°	448.4	454.2	461.2	480.0	482.9
167.5°	454.3	458.7	462.2	475.6	476.4
170°	458.2	461.1	462.2	474.1	474.1
172.5°	461.4	462.8	462.2	471.7	470.9
175°	464.2	465.1	462.2	468.1	467.1
177.5°	465.0	465.0	461.8	466.5	465.0
180°	464.2	464.2	464.2	464.2	464.2

(END OF REPORT)