

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562778

Luminaire Tested: **SQ4-PC3-075U-125D-840-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562778
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-075U-125D-840-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7992.7 lumens
Efficiency: N/A
Efficacy: 128.7 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 62.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562778
CATALOG NUMBER: SQ4-PC3-075U-125D-840-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P562778

CATALOG NUMBER: SQ4-PC3-075U-125D-840-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	60	58	57	53
2	92	84	78	73	86	79	73	69	69	65	62	61	57	55	52	50	48	44
3	84	74	66	60	78	70	63	57	61	56	52	54	50	46	46	43	41	37
4	76	65	57	51	71	62	54	49	54	49	44	48	43	40	42	38	35	32
5	70	58	50	44	66	55	47	42	49	43	38	43	38	34	37	34	31	28
6	65	52	44	38	60	49	42	36	44	38	33	39	34	30	34	30	27	24
7	60	47	39	33	56	45	37	32	40	34	29	35	30	27	31	27	24	21
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23	30	25	21	26	22	19	17
10	48	36	29	24	45	34	27	23	31	25	21	27	23	19	24	20	17	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16794	16794	16794
5°	16920	16810	16748
10°	16879	16800	16753
15°	16790	16790	16775
20°	16680	16729	16729
25°	16522	16642	16591
30°	16321	16518	16447
35°	16078	16325	16211
40°	15813	16035	15874
45°	15526	15635	15394
50°	15120	15120	14877
55°	14639	14450	14232
60°	13932	13653	13435
65°	12878	12621	12509
70°	11276	11365	11322
75°	9072	10035	10092
80°	6445	8506	8597
85°	3927	7135	7135



TEST NUMBER: P562778

CATALOG NUMBER: SQ4-PC3-075U-125D-840-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.3	2.2
10°-20°	494.3	6.2
20°-30°	748.6	9.4
30°-40°	897.5	11.2
40°-50°	915.1	11.4
50°-60°	798.9	10.0
60°-70°	571.9	7.2
70°-80°	294.6	3.7
80°-90°	75.7	0.9
90°-100°	218.9	2.7
100°-110°	602.3	7.5
110°-120°	621.7	7.8
120°-130°	498.1	6.2
130°-140°	391.2	4.9
140°-150°	299.8	3.8
150°-160°	215.6	2.7
160°-170°	131.8	1.6
170°-180°	44.4	0.6
0°-30°	1415.2	17.7
0°-40°	2312.7	28.9
0°-60°	4026.7	50.4
0°-90°	4968.8	62.2
90°-120°	1442.9	18.1
90°-150°	2632.1	32.9
90°-180°	3024.0	37.8
0°-180°	7992.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1820	1820	1820	1820	1820	
5°	1827	1809	1815	1810	1808	173
15°	1758	1743	1758	1758	1756	496
25°	1623	1612	1635	1630	1630	747
35°	1428	1424	1449	1439	1439	893
45°	1190	1187	1198	1183	1180	916
55°	910	899	898	885	885	811
65°	590	577	578	573	573	583
75°	254	266	282	283	283	275
85°	37	57	67	69	67	50
90°	1	4	7	9	9	4
95°	33	120	387	166	106	34
105°	108	166	664	1011	943	113
115°	191	232	532	1060	1203	188
125°	263	299	483	817	957	234
135°	317	352	469	661	748	245
145°	366	392	462	563	606	230
155°	415	428	459	506	520	191
165°	448	454	461	480	483	126
175°	464	465	462	468	467	44
180°	464	464	464	464	464	

TEST NUMBER: P562778

CATALOG NUMBER: SQ4-PC3-075U-125D-840-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1820.2	1820.2	1820.2	1820.2	1820.2
2.5°	1831.0	1815.2	1820.2	1816.0	1809.4
5°	1826.9	1808.8	1815.1	1810.0	1808.4
7.5°	1813.8	1795.7	1804.0	1800.6	1799.0
10°	1801.7	1783.5	1793.2	1789.8	1788.2
12.5°	1785.5	1768.7	1779.7	1776.4	1776.0
15°	1757.8	1743.0	1757.8	1757.8	1756.2
17.5°	1723.1	1709.6	1725.5	1726.5	1725.5
20°	1698.9	1684.0	1703.9	1702.3	1703.9
22.5°	1669.2	1657.0	1678.3	1673.9	1675.6
25°	1623.0	1611.5	1634.8	1629.8	1629.8
27.5°	1568.4	1560.2	1585.6	1580.2	1580.2
30°	1532.0	1523.8	1550.5	1543.8	1543.8
32.5°	1491.6	1485.9	1511.4	1503.3	1503.3
35°	1427.5	1424.2	1449.4	1439.3	1439.3
37.5°	1361.4	1358.5	1381.3	1369.1	1365.1
40°	1312.9	1311.3	1331.4	1318.0	1318.0
42.5°	1264.4	1262.7	1280.2	1264.0	1264.0
45°	1189.9	1186.6	1198.3	1183.1	1179.8
47.5°	1108.6	1105.3	1112.7	1096.1	1094.5
50°	1053.4	1050.1	1053.4	1038.1	1036.5
52.5°	996.7	990.8	991.3	976.2	975.8
55°	910.1	898.6	898.3	884.8	884.8
57.5°	818.4	803.3	804.6	793.1	791.4
60°	755.0	738.6	739.9	729.7	728.1
62.5°	693.0	673.9	677.9	666.4	666.1
65°	589.9	576.7	578.1	573.0	573.0
67.5°	490.8	478.6	487.4	483.4	483.0
70°	418.0	409.7	421.3	421.3	419.7
72.5°	350.6	350.2	364.7	364.7	365.7
75°	254.5	266.0	281.5	283.1	283.1
77.5°	169.9	190.3	207.3	208.0	207.6
80°	121.3	144.4	160.1	163.4	161.8
82.5°	82.2	106.6	119.7	123.0	121.3
85°	37.1	56.9	67.4	69.1	67.4
87.5°	11.0	23.4	28.3	28.7	26.0
90°	1.0	3.9	6.9	8.9	8.9
92.5°	13.6	58.2	100.9	38.8	31.8
95°	32.6	119.5	387.1	165.5	105.7
97.5°	53.1	132.5	590.8	455.2	321.2
100°	68.1	140.6	654.8	660.9	539.2
102.5°	82.4	150.2	671.4	819.9	708.3
105°	107.6	165.6	663.7	1010.8	943.2
107.5°	131.7	184.7	625.9	1104.2	1124.3
110°	149.1	197.4	597.5	1127.4	1197.0

TEST NUMBER: P562778

CATALOG NUMBER: SQ4-PC3-075U-125D-840-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	164.9	211.7	569.1	1112.5	1218.3
115°	190.6	232.1	532.3	1060.0	1202.9
117.5°	215.1	253.3	509.0	986.3	1148.0
120°	230.1	266.8	498.7	931.2	1098.2
122.5°	243.5	280.2	491.6	882.8	1041.3
125°	262.7	299.4	482.9	817.0	957.0
127.5°	280.9	315.8	477.2	762.1	884.9
130°	290.4	326.1	474.1	729.4	841.4
132.5°	301.4	337.1	471.7	700.7	801.9
135°	317.0	351.8	469.1	660.7	747.6
137.5°	331.6	363.9	466.9	628.4	700.0
140°	342.7	372.6	466.1	606.9	671.6
142.5°	352.2	379.8	464.6	587.7	643.1
145°	366.4	391.5	462.2	562.9	606.4
147.5°	381.6	403.2	461.0	541.0	575.8
150°	391.1	410.4	460.2	529.0	556.0
152.5°	399.8	417.6	459.4	518.6	541.0
155°	414.8	428.3	459.2	506.0	520.5
157.5°	425.7	436.7	459.2	495.6	505.7
160°	433.6	442.2	459.2	490.0	497.8
162.5°	439.9	447.0	460.0	485.3	491.4
165°	448.4	454.2	461.2	480.0	482.9
167.5°	454.3	458.7	462.2	475.6	476.4
170°	458.2	461.1	462.2	474.1	474.1
172.5°	461.4	462.8	462.2	471.7	470.9
175°	464.2	465.1	462.2	468.1	467.1
177.5°	465.0	465.0	461.8	466.5	465.0
180°	464.2	464.2	464.2	464.2	464.2

(END OF REPORT)