

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563940

Luminaire Tested: **SQ4-PR1-025U-125D-935-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2106-289-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PR1-025U-125D-935-1D-UNV-STD-W-8  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 10095.8 lumens  
Efficiency: N/A  
Efficacy: 99.4 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35  
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 101.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563940  
CATALOG NUMBER: SQ4-PR1-025U-125D-935-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P563940

CATALOG NUMBER: SQ4-PR1-025U-125D-935-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	115	115	115	115	110	110	110	110	102	102	102	94	94	94	87	87	87	83				
1	106	101	97	94	101	97	94	91	90	87	85	84	81	79	77	76	74	71				
2	97	89	83	78	93	86	80	75	80	75	71	74	70	67	69	66	63	60				
3	89	79	71	65	85	76	69	64	71	65	60	66	61	57	61	58	54	52				
4	81	70	62	56	78	68	60	55	63	57	52	59	54	50	55	51	47	45				
5	75	63	55	48	72	61	53	47	57	50	45	53	48	43	50	45	41	39				
6	69	57	48	42	66	55	47	42	52	45	40	48	43	38	45	41	37	34				
7	64	52	43	37	62	50	42	37	47	40	35	44	38	34	42	37	33	31				
8	60	47	39	33	57	46	38	33	43	36	32	41	35	31	38	33	29	27				
9	56	43	35	30	54	42	35	30	40	33	29	37	32	28	35	30	27	25				
10	52	40	32	27	50	39	32	27	37	30	26	35	29	25	33	28	24	22				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15530	15530	15530
5°	15670	15549	15468
10°	15620	15511	15430
15°	15552	15455	15371
20°	15473	15374	15260
25°	15364	15261	15084
30°	15198	15090	14874
35°	14974	14844	14631
40°	14633	14476	14214
45°	14036	13790	13506
50°	12986	12673	12424
55°	11334	11077	10844
60°	9551	9471	9283
65°	8261	8293	8229
70°	7587	7626	7626
75°	7286	7286	7338
80°	6857	6934	6857
85°	5526	6140	6140



TEST NUMBER: P563940

CATALOG NUMBER: SQ4-PR1-025U-125D-935-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	318.4	3.2
10°-20°	910.8	9.0
20°-30°	1373.8	13.6
30°-40°	1636.9	16.2
40°-50°	1613.8	16.0
50°-60°	1233.4	12.2
60°-70°	763.3	7.6
70°-80°	433.5	4.3
80°-90°	133.3	1.3
90°-100°	126.2	1.3
100°-110°	331.8	3.3
110°-120°	344.1	3.4
120°-130°	276.0	2.7
130°-140°	216.6	2.1
140°-150°	166.2	1.6
150°-160°	119.7	1.2
160°-170°	73.2	0.7
170°-180°	24.7	0.2
0°-30°	2603.0	25.8
0°-40°	4239.9	42.0
0°-60°	7087.1	70.2
0°-90°	8417.2	83.4
90°-120°	802.1	7.9
90°-150°	1460.9	14.5
90°-180°	1679.0	16.6
0°-180°	10095.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3366	3366	3366	3366	3366	
5°	3384	3347	3358	3346	3340	321
15°	3256	3222	3236	3224	3219	919
25°	3018	2982	2998	2966	2963	1389
35°	2659	2628	2636	2601	2598	1660
45°	2152	2123	2114	2076	2070	1648
55°	1409	1386	1377	1354	1348	1263
65°	757	751	760	754	754	767
75°	409	409	409	412	412	432
85°	104	110	116	116	116	121
90°	2	5	13	7	7	6
95°	17	65	218	112	76	19
105°	60	91	367	557	520	63
115°	106	129	294	586	669	105
125°	148	166	267	452	533	131
135°	176	194	259	365	413	136
145°	204	217	256	311	335	128
155°	231	237	256	281	289	106
165°	249	252	256	266	269	70
175°	259	259	257	261	261	25
180°	259	259	259	259	259	

TEST NUMBER: P563940

CATALOG NUMBER: SQ4-PR1-025U-125D-935-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3366.5	3366.5	3366.5	3366.5	3366.5
2.5°	3387.3	3357.9	3366.5	3359.1	3343.3
5°	3383.9	3347.0	3357.8	3346.0	3340.4
7.5°	3357.8	3321.5	3332.2	3320.6	3317.2
10°	3334.6	3300.5	3311.4	3299.6	3294.0
12.5°	3309.1	3272.8	3285.9	3271.8	3266.1
15°	3256.3	3222.3	3236.0	3224.3	3218.6
17.5°	3198.3	3162.0	3175.7	3162.2	3154.8
20°	3151.9	3117.9	3131.6	3111.2	3108.4
22.5°	3100.9	3066.8	3080.6	3053.3	3052.7
25°	3018.5	2981.7	2998.2	2966.3	2963.4
27.5°	2920.5	2886.5	2900.2	2867.7	2864.2
30°	2853.2	2819.2	2832.9	2798.0	2792.3
32.5°	2776.7	2744.9	2756.4	2721.5	2718.1
35°	2659.0	2627.8	2635.8	2600.9	2598.1
37.5°	2525.0	2496.6	2501.2	2462.9	2460.0
40°	2429.9	2401.5	2403.8	2363.1	2360.3
42.5°	2325.5	2297.1	2294.8	2254.1	2251.3
45°	2151.5	2123.2	2113.8	2076.0	2070.3
47.5°	1953.2	1924.8	1907.4	1876.5	1872.6
50°	1809.4	1781.0	1765.9	1739.6	1731.1
52.5°	1653.9	1625.6	1612.8	1588.8	1580.3
55°	1409.2	1386.5	1377.3	1354.0	1348.3
57.5°	1176.7	1161.4	1158.7	1136.0	1133.8
60°	1035.2	1026.7	1026.5	1006.2	1006.2
62.5°	914.5	908.3	912.8	899.4	897.1
65°	756.8	751.1	759.7	753.9	753.9
67.5°	632.1	632.1	637.3	635.0	635.0
70°	562.5	562.5	565.4	565.4	565.4
72.5°	499.9	497.6	505.1	505.1	502.8
75°	408.8	408.8	408.8	411.7	411.7
77.5°	318.4	318.9	321.3	320.6	318.4
80°	258.1	260.9	261.0	258.1	258.1
82.5°	197.8	200.6	200.7	200.0	197.8
85°	104.4	110.1	116.0	116.0	116.0
87.5°	30.5	40.2	49.1	47.7	45.4
90°	1.7	4.9	13.3	6.6	6.6
92.5°	7.0	33.6	74.4	32.9	21.2
95°	16.6	65.3	217.5	112.1	76.4
97.5°	28.9	71.7	325.4	258.8	190.6
100°	38.2	77.1	358.6	363.4	282.2
102.5°	46.2	82.5	367.9	452.6	383.1
105°	59.8	90.6	366.9	556.9	519.6
107.5°	73.7	102.3	346.0	611.1	620.2
110°	83.0	109.0	328.7	625.1	664.0



TEST NUMBER: P563940

CATALOG NUMBER: SQ4-PR1-025U-125D-935-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	92.3	117.0	312.8	616.3	676.0
115°	106.2	129.0	293.8	586.2	669.0
117.5°	119.9	140.6	280.9	544.6	636.5
120°	127.8	147.3	275.6	516.7	605.9
122.5°	135.8	155.3	271.6	488.7	576.7
125°	147.7	165.6	267.3	451.7	532.9
127.5°	157.4	175.6	263.6	421.9	490.4
130°	162.7	182.2	262.3	403.2	466.5
132.5°	168.0	187.5	261.0	387.1	443.9
135°	176.0	193.8	259.0	364.7	413.4
137.5°	184.3	201.8	258.6	347.9	387.8
140°	190.9	207.1	257.3	334.5	371.9
142.5°	196.2	211.2	257.3	325.1	357.3
145°	204.2	217.2	255.7	311.0	335.3
147.5°	212.2	224.8	255.7	299.3	319.4
150°	217.5	228.8	255.7	292.5	308.8
152.5°	222.8	231.5	255.7	287.1	299.5
155°	230.8	237.2	255.7	280.7	288.9
157.5°	236.7	242.9	255.7	275.0	280.9
160°	240.7	245.6	255.7	272.3	275.6
162.5°	244.7	248.3	255.7	269.7	272.9
165°	249.0	252.3	255.7	265.7	268.9
167.5°	253.0	254.6	257.3	264.0	265.3
170°	255.7	257.3	257.3	264.0	264.0
172.5°	257.0	257.3	257.3	262.6	261.3
175°	259.0	259.0	257.3	260.6	260.6
177.5°	259.0	259.0	257.6	260.3	259.0
180°	259.0	259.0	259.0	259.0	259.0

(END OF REPORT)