

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564108

Luminaire Tested: **SQ4-PR1-075U-100D-935-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564108
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-075U-100D-935-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11799.4 lumens
Efficiency: N/A
Efficacy: 109.0 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 108.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564108
CATALOG NUMBER: SQ4-PR1-075U-100D-935-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P564108

CATALOG NUMBER: SQ4-PR1-075U-100D-935-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56
1	99	95	91	88	92	89	85	82	76	74	72	65	64	62	55	54	53	48
2	91	84	77	72	84	78	73	68	67	63	60	58	55	52	49	47	45	41
3	83	74	66	61	77	69	62	57	60	55	51	51	48	45	43	41	38	35
4	76	65	58	52	71	61	54	49	53	48	44	46	42	38	39	36	33	30
5	70	58	50	44	65	55	48	42	48	42	38	41	37	33	35	32	29	26
6	65	53	44	39	60	49	42	37	43	37	33	37	33	29	32	29	26	23
7	60	47	40	34	55	45	37	32	39	33	29	34	30	26	29	26	23	21
8	55	43	35	30	52	41	34	29	36	30	26	31	27	23	27	23	21	18
9	52	39	32	27	48	37	30	26	33	27	23	29	24	21	25	21	19	17
10	48	36	29	24	45	34	28	23	30	25	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12169	12169	12169
5°	12279	12184	12121
10°	12240	12155	12091
15°	12186	12111	12045
20°	12125	12047	11958
25°	12040	11958	11820
30°	11910	11825	11655
35°	11734	11631	11465
40°	11466	11343	11138
45°	10999	10806	10584
50°	10175	9931	9735
55°	8882	8680	8498
60°	7484	7422	7275
65°	6473	6498	6449
70°	5945	5976	5976
75°	5711	5711	5752
80°	5372	5433	5372
85°	4330	4811	4811



TEST NUMBER: P564108

CATALOG NUMBER: SQ4-PR1-075U-100D-935-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	249.5	2.1
10°-20°	713.7	6.0
20°-30°	1076.5	9.1
30°-40°	1282.7	10.9
40°-50°	1264.6	10.7
50°-60°	966.5	8.2
60°-70°	598.1	5.1
70°-80°	339.7	2.9
80°-90°	105.4	0.9
90°-100°	376.7	3.2
100°-110°	1036.3	8.8
110°-120°	1069.6	9.1
120°-130°	857.0	7.3
130°-140°	673.1	5.7
140°-150°	515.8	4.4
150°-160°	370.9	3.1
160°-170°	226.8	1.9
170°-180°	76.4	0.6
0°-30°	2039.8	17.3
0°-40°	3322.5	28.2
0°-60°	5553.6	47.1
0°-90°	6596.8	55.9
90°-120°	2482.6	21.0
90°-150°	4528.5	38.4
90°-180°	5203.0	44.1
0°-180°	11799.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2638	2638	2638	2638	2638	
5°	2652	2623	2631	2622	2618	252
15°	2552	2525	2536	2527	2522	720
25°	2365	2336	2349	2324	2322	1089
35°	2084	2059	2065	2038	2036	1300
45°	1686	1664	1656	1627	1622	1292
55°	1104	1086	1079	1061	1057	989
65°	593	589	595	591	591	601
75°	320	320	320	323	323	338
85°	82	86	91	91	91	95
90°	2	7	12	15	15	7
95°	56	206	666	285	182	59
105°	185	285	1142	1739	1623	195
115°	328	399	916	1824	2070	324
125°	452	515	831	1406	1646	403
135°	545	605	807	1137	1286	421
145°	630	674	795	968	1043	395
155°	714	737	790	870	896	328
165°	771	781	794	826	831	217
175°	799	800	795	805	804	76
180°	799	799	799	799	799	

TEST NUMBER: P564108

CATALOG NUMBER: SQ4-PR1-075U-100D-935-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2638.0	2638.0	2638.0	2638.0	2638.0
2.5°	2654.4	2631.3	2638.0	2632.3	2619.8
5°	2651.7	2622.8	2631.2	2622.0	2617.6
7.5°	2631.2	2602.8	2611.2	2602.1	2599.4
10°	2613.0	2586.4	2594.8	2585.7	2581.2
12.5°	2593.0	2564.6	2574.9	2563.8	2559.4
15°	2551.7	2525.0	2535.8	2526.6	2522.1
17.5°	2506.2	2477.8	2488.5	2477.9	2472.1
20°	2469.9	2443.2	2454.0	2438.0	2435.8
22.5°	2429.9	2403.2	2414.0	2392.6	2392.2
25°	2365.4	2336.5	2349.4	2324.4	2322.2
27.5°	2288.6	2261.9	2272.6	2247.1	2244.5
30°	2235.8	2209.2	2219.9	2192.6	2188.1
32.5°	2175.9	2151.0	2159.9	2132.6	2130.0
35°	2083.6	2059.2	2065.4	2038.1	2035.9
37.5°	1978.6	1956.4	1960.0	1930.0	1927.7
40°	1904.1	1881.9	1883.6	1851.8	1849.6
42.5°	1822.3	1800.1	1798.2	1766.4	1764.1
45°	1686.0	1663.8	1656.4	1626.8	1622.3
47.5°	1530.6	1508.3	1494.6	1470.5	1467.4
50°	1417.8	1395.6	1383.8	1363.2	1356.5
52.5°	1296.1	1273.8	1263.8	1245.0	1238.3
55°	1104.3	1086.5	1079.3	1061.0	1056.6
57.5°	922.1	910.1	908.0	890.2	888.4
60°	811.2	804.5	804.4	788.5	788.5
62.5°	716.7	711.8	715.3	704.8	703.0
65°	593.0	588.6	595.3	590.8	590.8
67.5°	495.3	495.3	499.4	497.6	497.6
70°	440.8	440.8	443.1	443.1	443.1
72.5°	391.7	389.9	395.8	395.8	394.0
75°	320.4	320.4	320.4	322.7	322.7
77.5°	249.5	249.9	251.8	251.3	249.5
80°	202.2	204.4	204.5	202.2	202.2
82.5°	155.0	157.2	157.2	156.7	155.0
85°	81.8	86.2	90.9	90.9	90.9
87.5°	24.0	32.1	38.7	39.4	37.6
90°	1.7	6.7	11.9	15.3	15.3
92.5°	23.4	100.2	173.7	66.7	54.7
95°	56.1	205.6	666.1	284.8	181.8
97.5°	91.4	228.0	1016.4	783.2	552.6
100°	117.2	241.8	1126.5	1137.1	927.7
102.5°	141.7	258.3	1155.1	1410.7	1218.6
105°	185.2	284.9	1141.8	1739.0	1622.7
107.5°	226.7	317.7	1076.9	1899.8	1934.3
110°	256.6	339.6	1028.0	1939.7	2059.4



TEST NUMBER: P564108

CATALOG NUMBER: SQ4-PR1-075U-100D-935-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	283.8	364.2	979.0	1914.0	2096.1
115°	327.9	399.4	915.8	1823.7	2069.6
117.5°	370.1	435.9	875.7	1697.0	1975.1
120°	395.9	459.0	858.1	1602.0	1889.5
122.5°	419.0	482.1	845.8	1518.8	1791.6
125°	452.0	515.1	830.9	1405.6	1646.5
127.5°	483.2	543.4	821.0	1311.1	1522.4
130°	499.5	561.0	815.6	1255.0	1447.7
132.5°	518.6	580.1	811.5	1205.6	1379.7
135°	545.4	605.2	807.1	1136.7	1286.3
137.5°	570.6	626.1	803.4	1081.1	1204.4
140°	589.6	641.1	802.0	1044.1	1155.4
142.5°	605.9	653.4	799.3	1011.1	1106.5
145°	630.4	673.6	795.2	968.5	1043.3
147.5°	656.6	693.8	793.2	930.8	990.6
150°	672.9	706.1	791.8	910.1	956.6
152.5°	687.8	718.4	790.4	892.2	930.8
155°	713.6	736.9	790.1	870.5	895.5
157.5°	732.3	751.3	790.1	852.7	870.0
160°	745.9	760.9	790.1	843.1	856.4
162.5°	756.8	769.1	791.5	834.9	845.5
165°	771.4	781.4	793.5	825.9	830.9
167.5°	781.6	789.2	795.2	818.3	819.7
170°	788.4	793.4	795.2	815.6	815.6
172.5°	793.8	796.2	795.2	811.5	810.2
175°	798.6	800.3	795.2	805.4	803.7
177.5°	800.0	800.0	794.5	802.6	800.0
180°	798.6	798.6	798.6	798.6	798.6

(END OF REPORT)