

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563090

Luminaire Tested: **SQ4-PC3-150U-050D-840-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563090  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-150U-050D-840-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: 4000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8074.3 lumens  
Efficiency: N/A  
Efficacy: 145.0 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 55.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563090  
CATALOG NUMBER: SQ4-PC3-150U-050D-840-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P563090

CATALOG NUMBER: SQ4-PC3-150U-050D-840-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	25				
1	92	88	84	81	82	78	75	73	61	59	57	44	43	42	29	28	28	21				
2	84	77	71	66	74	69	64	59	53	50	47	39	37	35	26	24	23	17				
3	76	67	60	55	68	60	54	50	47	43	39	34	32	29	23	21	20	15				
4	70	59	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17	13				
5	64	53	45	39	57	47	41	36	37	32	29	27	24	22	18	16	15	11				
6	59	47	39	34	52	42	36	31	33	28	25	24	21	19	16	14	13	10				
7	54	42	35	29	48	38	31	27	30	25	22	22	19	16	15	13	11	8				
8	50	38	31	26	44	34	28	24	27	22	19	20	17	15	14	12	10	8				
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	13	11	9	7				
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8	6				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6719	6719	6719
5°	6770	6727	6702
10°	6754	6722	6703
15°	6719	6719	6712
20°	6674	6694	6694
25°	6611	6660	6638
30°	6531	6609	6581
35°	6433	6533	6486
40°	6327	6417	6352
45°	6212	6256	6160
50°	6050	6050	5952
55°	5858	5781	5696
60°	5574	5464	5375
65°	5152	5050	5006
70°	4510	4548	4529
75°	3629	4014	4039
80°	2582	3406	3438
85°	1567	2858	2858



TEST NUMBER: P563090

CATALOG NUMBER: SQ4-PC3-150U-050D-840-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	68.9	0.9
10°-20°	197.8	2.4
20°-30°	299.6	3.7
30°-40°	359.1	4.4
40°-50°	366.2	4.5
50°-60°	319.7	4.0
60°-70°	228.8	2.8
70°-80°	117.9	1.5
80°-90°	31.8	0.4
90°-100°	438.6	5.4
100°-110°	1185.8	14.7
110°-120°	1246.8	15.4
120°-130°	1012.7	12.5
130°-140°	794.4	9.8
140°-150°	609.7	7.6
150°-160°	438.5	5.4
160°-170°	267.9	3.3
170°-180°	90.3	1.1
0°-30°	566.3	7.0
0°-40°	925.4	11.5
0°-60°	1611.3	20.0
0°-90°	1989.7	24.6
90°-120°	2871.2	35.6
90°-150°	5287.9	65.5
90°-180°	6085.0	75.4
0°-180°	8074.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	728	728	728	728	728	
5°	731	724	726	724	724	69
15°	703	697	703	703	703	198
25°	649	645	654	652	652	299
35°	571	570	580	576	576	357
45°	476	475	480	473	472	366
55°	364	360	359	354	354	325
65°	236	231	231	229	229	233
75°	102	106	113	113	113	110
85°	15	23	27	28	27	20
90°	2	6	13	14	13	5
95°	68	239	729	378	224	71
105°	220	341	1316	1940	1861	232
115°	388	474	1091	2112	2384	383
125°	531	609	983	1659	1949	474
135°	637	712	957	1340	1517	492
145°	741	796	944	1147	1234	463
155°	836	869	936	1029	1063	386
165°	910	919	940	976	981	256
175°	945	944	941	953	951	90
180°	944	944	944	944	944	

TEST NUMBER: P563090

CATALOG NUMBER: SQ4-PC3-150U-050D-840-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	728.3	728.3	728.3	728.3	728.3
2.5°	732.7	726.3	728.3	726.7	724.0
5°	731.0	723.8	726.3	724.3	723.6
7.5°	725.8	718.5	721.9	720.5	719.8
10°	720.9	713.7	717.5	716.2	715.5
12.5°	714.4	707.7	712.1	710.8	710.7
15°	703.4	697.4	703.4	703.4	702.7
17.5°	689.5	684.1	690.4	690.8	690.4
20°	679.8	673.8	681.8	681.1	681.8
22.5°	667.9	663.0	671.6	669.8	670.5
25°	649.4	644.8	654.2	652.1	652.1
27.5°	627.6	624.3	634.5	632.3	632.3
30°	613.0	609.7	620.4	617.7	617.7
32.5°	596.8	594.6	604.8	601.6	601.6
35°	571.2	569.9	580.0	575.9	575.9
37.5°	544.8	543.6	552.7	547.8	546.3
40°	525.3	524.7	532.8	527.4	527.4
42.5°	505.9	505.3	512.3	505.8	505.8
45°	476.1	474.8	479.5	473.4	472.1
47.5°	443.6	442.3	445.2	438.6	437.9
50°	421.5	420.2	421.5	415.4	414.7
52.5°	398.8	396.5	396.7	390.6	390.5
55°	364.2	359.6	359.4	354.1	354.1
57.5°	327.5	321.4	322.0	317.4	316.7
60°	302.1	295.5	296.1	292.0	291.3
62.5°	277.3	269.7	271.2	266.6	266.5
65°	236.0	230.8	231.3	229.3	229.3
67.5°	196.4	191.5	195.0	193.4	193.3
70°	167.2	164.0	168.6	168.6	167.9
72.5°	140.3	140.1	145.9	145.9	146.3
75°	101.8	106.4	112.6	113.3	113.3
77.5°	68.0	76.2	82.9	83.2	83.1
80°	48.6	57.8	64.1	65.4	64.7
82.5°	32.9	42.7	47.9	49.2	48.6
85°	14.8	22.7	27.0	27.6	27.0
87.5°	4.7	10.3	13.4	13.6	12.4
90°	2.0	6.0	13.2	14.2	13.2
92.5°	28.9	105.1	207.4	90.0	65.2
95°	68.1	238.9	729.4	377.5	224.5
97.5°	109.3	274.0	1136.9	940.9	691.0
100°	140.2	288.2	1263.7	1317.9	1065.6
102.5°	168.6	307.9	1308.4	1603.8	1415.1
105°	220.4	340.6	1315.5	1940.5	1861.0
107.5°	268.4	378.0	1258.0	2150.6	2177.0
110°	305.8	405.1	1206.8	2207.0	2319.2

TEST NUMBER: P563090

CATALOG NUMBER: SQ4-PC3-150U-050D-840-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	339.1	432.1	1159.7	2195.7	2384.2
115°	388.1	474.5	1091.0	2112.1	2384.2
117.5°	436.0	517.1	1045.7	1984.3	2292.8
120°	465.3	544.7	1018.9	1892.6	2207.5
122.5°	492.9	570.8	1002.6	1794.3	2111.6
125°	531.3	608.8	983.3	1659.4	1949.4
127.5°	566.6	642.7	972.0	1549.3	1804.4
130°	586.1	664.6	967.1	1481.3	1711.7
132.5°	606.5	684.1	962.2	1419.9	1632.1
135°	636.9	712.4	956.9	1339.9	1516.7
137.5°	667.6	738.9	952.5	1274.9	1418.9
140°	688.7	755.3	950.8	1233.1	1361.2
142.5°	709.1	771.6	947.6	1195.4	1307.6
145°	740.6	796.2	943.7	1146.9	1234.3
147.5°	769.2	818.5	939.3	1102.9	1170.1
150°	790.3	834.0	937.6	1079.0	1132.7
152.5°	809.8	848.0	936.8	1056.9	1101.0
155°	836.0	868.8	935.6	1028.8	1062.6
157.5°	863.3	886.1	935.8	1009.2	1031.5
160°	878.7	897.6	936.6	996.9	1012.8
162.5°	890.9	906.6	937.4	987.1	999.0
165°	910.2	919.1	939.7	976.3	981.3
167.5°	923.4	929.6	939.9	967.1	969.5
170°	931.5	934.5	940.7	963.0	963.0
172.5°	938.0	938.6	940.7	958.1	957.3
175°	944.7	943.8	940.7	952.8	950.8
177.5°	947.0	944.6	940.5	948.6	946.2
180°	943.7	943.7	943.7	943.7	943.7

(END OF REPORT)