

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564132

Luminaire Tested: **SQ4-PR1-075U-125D-935-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564132
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-075U-125D-935-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13620.4 lumens
Efficiency: N/A
Efficacy: 106.7 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 127.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564132
CATALOG NUMBER: SQ4-PR1-075U-125D-935-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P564132

CATALOG NUMBER: SQ4-PR1-075U-125D-935-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	97	93	89	94	91	87	84	79	77	75	69	67	66	60	58	57	53
2	92	85	79	74	86	80	74	70	70	66	62	61	58	55	53	51	49	45
3	84	75	67	62	79	70	64	59	62	57	53	54	51	47	47	44	42	38
4	77	66	59	53	72	63	56	50	55	50	45	49	44	41	42	39	36	33
5	71	59	51	45	66	56	49	43	50	44	39	44	39	36	38	35	32	29
6	66	53	45	39	61	51	43	38	45	39	35	40	35	31	35	31	28	26
7	61	48	40	35	57	46	38	33	41	35	31	36	31	28	32	28	25	23
8	56	44	36	31	53	42	35	30	37	31	27	33	28	25	29	25	23	20
9	53	40	33	28	49	38	31	27	34	29	24	31	26	22	27	23	20	18
10	49	37	30	25	46	35	28	24	32	26	22	28	24	20	25	21	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15530	15530	15530
5°	15670	15549	15468
10°	15620	15511	15430
15°	15552	15455	15371
20°	15473	15374	15260
25°	15364	15261	15084
30°	15198	15090	14874
35°	14974	14844	14631
40°	14633	14476	14214
45°	14036	13790	13506
50°	12986	12673	12424
55°	11334	11077	10844
60°	9551	9471	9283
65°	8261	8293	8229
70°	7587	7626	7626
75°	7286	7286	7338
80°	6857	6934	6857
85°	5526	6140	6140



TEST NUMBER: P564132

CATALOG NUMBER: SQ4-PR1-075U-125D-935-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	318.4	2.3
10°-20°	910.8	6.7
20°-30°	1373.8	10.1
30°-40°	1636.9	12.0
40°-50°	1613.8	11.8
50°-60°	1233.4	9.1
60°-70°	763.3	5.6
70°-80°	433.5	3.2
80°-90°	133.9	1.0
90°-100°	376.7	2.8
100°-110°	1036.3	7.6
110°-120°	1069.6	7.9
120°-130°	857.0	6.3
130°-140°	673.1	4.9
140°-150°	515.8	3.8
150°-160°	370.9	2.7
160°-170°	226.8	1.7
170°-180°	76.4	0.6
0°-30°	2603.0	19.1
0°-40°	4239.9	31.1
0°-60°	7087.1	52.0
0°-90°	8417.8	61.8
90°-120°	2482.6	18.2
90°-150°	4528.5	33.2
90°-180°	5203.0	38.2
0°-180°	13620.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3366	3366	3366	3366	3366	
5°	3384	3347	3358	3346	3340	321
15°	3256	3222	3236	3224	3219	919
25°	3018	2982	2998	2966	2963	1389
35°	2659	2628	2636	2601	2598	1660
45°	2152	2123	2114	2076	2070	1648
55°	1409	1386	1377	1354	1348	1263
65°	757	751	760	754	754	767
75°	409	409	409	412	412	432
85°	104	110	116	116	116	121
90°	2	7	12	15	15	8
95°	56	206	666	285	182	59
105°	185	285	1142	1739	1623	195
115°	328	399	916	1824	2070	324
125°	452	515	831	1406	1646	403
135°	545	605	807	1137	1286	421
145°	630	674	795	968	1043	395
155°	714	737	790	870	896	328
165°	771	781	794	826	831	217
175°	799	800	795	805	804	76
180°	799	799	799	799	799	

TEST NUMBER: P564132

CATALOG NUMBER: SQ4-PR1-075U-125D-935-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3366.5	3366.5	3366.5	3366.5	3366.5
2.5°	3387.3	3357.9	3366.5	3359.1	3343.3
5°	3383.9	3347.0	3357.8	3346.0	3340.4
7.5°	3357.8	3321.5	3332.2	3320.6	3317.2
10°	3334.6	3300.5	3311.4	3299.6	3294.0
12.5°	3309.1	3272.8	3285.9	3271.8	3266.1
15°	3256.3	3222.3	3236.0	3224.3	3218.6
17.5°	3198.3	3162.0	3175.7	3162.2	3154.8
20°	3151.9	3117.9	3131.6	3111.2	3108.4
22.5°	3100.9	3066.8	3080.6	3053.3	3052.7
25°	3018.5	2981.7	2998.2	2966.3	2963.4
27.5°	2920.5	2886.5	2900.2	2867.7	2864.2
30°	2853.2	2819.2	2832.9	2798.0	2792.3
32.5°	2776.7	2744.9	2756.4	2721.5	2718.1
35°	2659.0	2627.8	2635.8	2600.9	2598.1
37.5°	2525.0	2496.6	2501.2	2462.9	2460.0
40°	2429.9	2401.5	2403.8	2363.1	2360.3
42.5°	2325.5	2297.1	2294.8	2254.1	2251.3
45°	2151.5	2123.2	2113.8	2076.0	2070.3
47.5°	1953.2	1924.8	1907.4	1876.5	1872.6
50°	1809.4	1781.0	1765.9	1739.6	1731.1
52.5°	1653.9	1625.6	1612.8	1588.8	1580.3
55°	1409.2	1386.5	1377.3	1354.0	1348.3
57.5°	1176.7	1161.4	1158.7	1136.0	1133.8
60°	1035.2	1026.7	1026.5	1006.2	1006.2
62.5°	914.5	908.3	912.8	899.4	897.1
65°	756.8	751.1	759.7	753.9	753.9
67.5°	632.1	632.1	637.3	635.0	635.0
70°	562.5	562.5	565.4	565.4	565.4
72.5°	499.9	497.6	505.1	505.1	502.8
75°	408.8	408.8	408.8	411.7	411.7
77.5°	318.4	318.9	321.3	320.6	318.4
80°	258.1	260.9	261.0	258.1	258.1
82.5°	197.8	200.6	200.7	200.0	197.8
85°	104.4	110.1	116.0	116.0	116.0
87.5°	30.5	40.6	48.8	49.4	47.1
90°	1.7	6.7	11.9	15.3	15.3
92.5°	23.4	100.2	173.7	66.7	54.7
95°	56.1	205.6	666.1	284.8	181.8
97.5°	91.4	228.0	1016.4	783.2	552.6
100°	117.2	241.8	1126.5	1137.1	927.7
102.5°	141.7	258.3	1155.1	1410.7	1218.6
105°	185.2	284.9	1141.8	1739.0	1622.7
107.5°	226.7	317.7	1076.9	1899.8	1934.3
110°	256.6	339.6	1028.0	1939.7	2059.4

TEST NUMBER: P564132

CATALOG NUMBER: SQ4-PR1-075U-125D-935-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	283.8	364.2	979.0	1914.0	2096.1
115°	327.9	399.4	915.8	1823.7	2069.6
117.5°	370.1	435.9	875.7	1697.0	1975.1
120°	395.9	459.0	858.1	1602.0	1889.5
122.5°	419.0	482.1	845.8	1518.8	1791.6
125°	452.0	515.1	830.9	1405.6	1646.5
127.5°	483.2	543.4	821.0	1311.1	1522.4
130°	499.5	561.0	815.6	1255.0	1447.7
132.5°	518.6	580.1	811.5	1205.6	1379.7
135°	545.4	605.2	807.1	1136.7	1286.3
137.5°	570.6	626.1	803.4	1081.1	1204.4
140°	589.6	641.1	802.0	1044.1	1155.4
142.5°	605.9	653.4	799.3	1011.1	1106.5
145°	630.4	673.6	795.2	968.5	1043.3
147.5°	656.6	693.8	793.2	930.8	990.6
150°	672.9	706.1	791.8	910.1	956.6
152.5°	687.8	718.4	790.4	892.2	930.8
155°	713.6	736.9	790.1	870.5	895.5
157.5°	732.3	751.3	790.1	852.7	870.0
160°	745.9	760.9	790.1	843.1	856.4
162.5°	756.8	769.1	791.5	834.9	845.5
165°	771.4	781.4	793.5	825.9	830.9
167.5°	781.6	789.2	795.2	818.3	819.7
170°	788.4	793.4	795.2	815.6	815.6
172.5°	793.8	796.2	795.2	811.5	810.2
175°	798.6	800.3	795.2	805.4	803.7
177.5°	800.0	800.0	794.5	802.6	800.0
180°	798.6	798.6	798.6	798.6	798.6

(END OF REPORT)