

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: CORELITE

Report Number: P564348

Luminaire Tested: **SQ4-PR1-125U-050D-935-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P564348  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PR1-125U-050D-935-1D-UNV-STD-W-8  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 12058.4 lumens  
Efficiency: N/A  
Efficacy: 124.6 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35  
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 96.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P564348  
CATALOG NUMBER: SQ4-PR1-125U-050D-935-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P564348

CATALOG NUMBER: SQ4-PR1-125U-050D-935-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28
1	93	89	85	82	83	80	77	74	62	60	58	47	45	44	32	31	31	24
2	85	78	72	67	76	70	65	61	55	51	49	41	39	37	28	27	26	20
3	77	68	61	56	69	61	56	51	48	44	41	36	34	31	25	24	22	17
4	71	61	53	47	63	54	48	43	43	39	35	32	29	27	23	21	19	15
5	65	54	46	40	58	48	42	37	38	34	30	29	26	23	20	18	17	13
6	60	48	40	35	53	43	37	32	35	30	26	26	23	20	18	16	15	12
7	55	43	36	30	49	39	33	28	31	26	23	24	20	18	17	15	13	10
8	51	39	32	27	46	35	29	25	28	24	20	22	18	16	15	13	12	9
9	47	36	29	24	42	32	26	22	26	21	18	20	17	14	14	12	11	8
10	44	33	26	21	40	30	23	19	24	19	16	18	15	13	13	11	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6214	6214	6214
5°	6270	6222	6189
10°	6250	6207	6174
15°	6223	6184	6151
20°	6191	6152	6106
25°	6148	6106	6036
30°	6082	6038	5952
35°	5992	5940	5855
40°	5855	5793	5687
45°	5616	5518	5404
50°	5196	5071	4971
55°	4535	4432	4339
60°	3821	3789	3714
65°	3305	3318	3293
70°	3036	3052	3052
75°	2916	2916	2937
80°	2744	2773	2744
85°	2212	2456	2456



TEST NUMBER: P564348

CATALOG NUMBER: SQ4-PR1-125U-050D-935-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	127.4	1.1
10°-20°	364.5	3.0
20°-30°	549.7	4.6
30°-40°	655.0	5.4
40°-50°	645.8	5.4
50°-60°	493.5	4.1
60°-70°	305.4	2.5
70°-80°	173.5	1.4
80°-90°	55.9	0.5
90°-100°	629.6	5.2
100°-110°	1695.9	14.1
110°-120°	1779.8	14.8
120°-130°	1444.2	12.0
130°-140°	1132.7	9.4
140°-150°	869.6	7.2
150°-160°	625.2	5.2
160°-170°	382.0	3.2
170°-180°	128.8	1.1
0°-30°	1041.6	8.6
0°-40°	1696.6	14.1
0°-60°	2835.9	23.5
0°-90°	3370.7	28.0
90°-120°	4105.2	34.0
90°-150°	7551.7	62.6
90°-180°	8688.0	72.0
0°-180°	12058.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1347	1347	1347	1347	1347	
5°	1354	1339	1344	1339	1337	128
15°	1303	1289	1295	1290	1288	368
25°	1208	1193	1200	1187	1186	556
35°	1064	1052	1055	1041	1040	664
45°	861	850	846	831	828	660
55°	564	555	551	542	540	505
65°	303	301	304	302	302	307
75°	164	164	164	165	165	173
85°	42	44	46	46	46	49
90°	3	10	21	22	22	8
95°	96	342	1032	528	365	100
105°	314	488	1876	2806	2633	330
115°	554	678	1562	3018	3413	545
125°	756	868	1402	2370	2789	675
135°	910	1016	1363	1912	2165	703
145°	1053	1135	1346	1635	1756	660
155°	1195	1238	1334	1467	1514	550
165°	1296	1311	1339	1392	1399	365
175°	1348	1346	1341	1359	1356	128
180°	1346	1346	1346	1346	1346	



TEST NUMBER: P564348

CATALOG NUMBER: SQ4-PR1-125U-050D-935-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1347.1	1347.1	1347.1	1347.1	1347.1
2.5°	1355.4	1343.6	1347.1	1344.1	1337.8
5°	1354.0	1339.3	1343.6	1338.9	1336.6
7.5°	1343.6	1329.1	1333.4	1328.7	1327.3
10°	1334.3	1320.7	1325.0	1320.3	1318.1
12.5°	1324.1	1309.6	1314.8	1309.2	1306.9
15°	1303.0	1289.4	1294.8	1290.2	1287.9
17.5°	1279.8	1265.2	1270.7	1265.3	1262.4
20°	1261.2	1247.6	1253.1	1244.9	1243.8
22.5°	1240.8	1227.2	1232.7	1221.7	1221.5
25°	1207.8	1193.1	1199.7	1186.9	1185.8
27.5°	1168.6	1155.0	1160.5	1147.5	1146.1
30°	1141.7	1128.1	1133.6	1119.6	1117.3
32.5°	1111.1	1098.4	1102.9	1089.0	1087.6
35°	1064.0	1051.5	1054.7	1040.7	1039.6
37.5°	1010.4	999.0	1000.8	985.5	984.4
40°	972.3	961.0	961.9	945.6	944.4
42.5°	930.5	919.2	918.2	902.0	900.8
45°	860.9	849.6	845.8	830.7	828.4
47.5°	781.5	770.2	763.2	750.9	749.3
50°	724.0	712.7	706.6	696.1	692.7
52.5°	661.8	650.5	645.3	635.7	632.3
55°	563.9	554.8	551.1	541.8	539.5
57.5°	470.8	464.7	463.6	454.6	453.7
60°	414.2	410.8	410.7	402.6	402.6
62.5°	365.9	363.4	365.2	359.9	359.0
65°	302.8	300.6	304.0	301.7	301.7
67.5°	252.9	252.9	255.0	254.1	254.1
70°	225.1	225.1	226.3	226.3	226.3
72.5°	200.0	199.1	202.1	202.1	201.2
75°	163.6	163.6	163.6	164.8	164.8
77.5°	127.4	127.6	128.6	128.3	127.4
80°	103.3	104.4	104.4	103.3	103.3
82.5°	79.1	80.3	80.3	80.0	79.1
85°	41.8	44.0	46.4	46.4	46.4
87.5°	12.8	17.7	22.7	23.0	22.1
90°	3.4	10.1	20.6	22.3	22.3
92.5°	41.8	147.8	292.1	140.6	97.7
95°	96.0	342.4	1032.0	527.8	365.2
97.5°	153.3	392.0	1618.7	1352.3	1019.7
100°	197.2	411.7	1805.2	1888.8	1566.9
102.5°	239.7	439.5	1866.9	2290.6	2026.4
105°	313.7	488.1	1875.5	2805.9	2633.3
107.5°	383.7	539.2	1795.6	3070.7	3115.3
110°	430.3	577.8	1722.9	3153.0	3315.6



TEST NUMBER: P564348

CATALOG NUMBER: SQ4-PR1-125U-050D-935-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	479.7	616.5	1653.0	3134.8	3402.0
115°	553.7	677.8	1561.8	3017.7	3413.3
117.5°	621.3	737.6	1491.2	2830.8	3271.3
120°	665.2	777.5	1455.5	2696.7	3149.3
122.5°	703.6	814.5	1429.4	2559.5	3010.8
125°	756.0	868.3	1402.3	2370.2	2789.3
127.5°	806.4	917.1	1385.2	2203.2	2577.4
130°	836.6	947.2	1378.3	2107.6	2436.1
132.5°	866.8	976.1	1371.5	2023.3	2325.0
135°	910.3	1015.9	1362.9	1912.1	2165.2
137.5°	951.8	1053.1	1358.5	1817.8	2025.7
140°	980.6	1077.8	1354.3	1759.8	1947.5
142.5°	1010.8	1101.3	1351.6	1705.6	1863.9
145°	1052.6	1134.8	1345.8	1634.8	1755.5
147.5°	1097.9	1169.3	1339.9	1575.3	1670.1
150°	1128.0	1190.1	1337.2	1537.9	1616.6
152.5°	1155.5	1209.5	1335.8	1507.3	1571.4
155°	1194.9	1238.5	1333.8	1466.8	1513.8
157.5°	1229.5	1263.4	1334.1	1438.4	1469.9
160°	1251.5	1280.0	1335.5	1421.7	1445.2
162.5°	1270.7	1293.8	1336.9	1407.9	1424.6
165°	1296.1	1311.1	1338.9	1392.2	1398.9
167.5°	1316.6	1325.3	1340.6	1380.1	1382.8
170°	1330.3	1333.7	1340.6	1373.2	1373.2
172.5°	1338.6	1339.2	1342.0	1366.3	1366.3
175°	1347.5	1345.8	1340.6	1359.4	1356.1
177.5°	1351.3	1348.6	1341.7	1352.6	1349.9
180°	1345.8	1345.8	1345.8	1345.8	1345.8

(END OF REPORT)