

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563666

Luminaire Tested: **SQ4-PP3-125U-050D-840-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563666
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-125U-050D-840-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7020.4 lumens
Efficiency: N/A
Efficacy: 146.6 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 47.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563666
CATALOG NUMBER: SQ4-PP3-125U-050D-840-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P563666

CATALOG NUMBER: SQ4-PP3-125U-050D-840-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28
1	93	89	85	82	83	80	77	74	62	60	58	47	45	44	32	31	31	24
2	85	78	72	67	76	70	65	61	55	51	48	41	39	37	28	27	26	20
3	77	68	61	56	69	61	55	51	48	44	41	36	34	31	25	23	22	17
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	22	21	19	15
5	65	54	46	40	58	48	42	37	38	33	30	29	26	23	20	18	17	13
6	60	48	40	35	53	43	37	32	34	29	26	26	23	20	18	16	15	11
7	55	43	36	30	49	39	32	28	31	26	23	24	20	18	17	15	13	10
8	51	39	32	26	45	35	29	24	28	23	20	22	18	16	15	13	12	9
9	47	35	28	23	42	32	26	22	26	21	18	20	16	14	14	12	10	8
10	44	32	25	21	39	29	23	19	24	19	16	18	15	13	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7098	7098	7098
5°	7150	7106	7081
10°	7138	7087	7055
15°	7090	7052	7013
20°	7044	7003	6950
25°	6960	6911	6843
30°	6831	6795	6709
35°	6652	6607	6524
40°	6440	6399	6325
45°	6263	6220	6159
50°	6038	6000	5942
55°	5726	5651	5607
60°	5213	5063	5039
65°	4593	4401	4386
70°	3965	3801	3801
75°	3411	3365	3315
80°	3007	3044	2975
85°	2350	2572	2572



TEST NUMBER: P563666

CATALOG NUMBER: SQ4-PP3-125U-050D-840-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.7	1.0
10°-20°	207.7	3.0
20°-30°	311.1	4.4
30°-40°	364.9	5.2
40°-50°	366.1	5.2
50°-60°	312.3	4.4
60°-70°	203.7	2.9
70°-80°	102.2	1.5
80°-90°	30.1	0.4
90°-100°	365.9	5.2
100°-110°	985.7	14.0
110°-120°	1034.5	14.7
120°-130°	839.4	12.0
130°-140°	658.3	9.4
140°-150°	505.4	7.2
150°-160°	363.4	5.2
160°-170°	222.0	3.2
170°-180°	74.9	1.1
0°-30°	591.6	8.4
0°-40°	956.5	13.6
0°-60°	1634.8	23.3
0°-90°	1970.8	28.1
90°-120°	2386.1	34.0
90°-150°	4389.3	62.5
90°-180°	5050.0	71.9
0°-180°	7020.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	769	769	769	769	769	
5°	772	765	767	765	765	73
15°	742	735	738	736	734	209
25°	684	676	679	673	672	314
35°	591	585	587	580	579	369
45°	480	477	477	472	472	370
55°	356	355	351	349	349	316
65°	210	206	202	200	201	210
75°	96	96	94	94	93	104
85°	22	24	24	24	24	26
90°	2	6	12	13	13	5
95°	56	199	600	307	212	58
105°	182	284	1090	1631	1530	192
115°	322	394	908	1754	1984	317
125°	439	505	815	1378	1621	392
135°	529	590	792	1111	1258	408
145°	612	660	782	950	1020	384
155°	694	720	775	853	880	320
165°	753	762	778	809	813	212
175°	783	782	779	790	788	74
180°	782	782	782	782	782	



TEST NUMBER: P563666

CATALOG NUMBER: SQ4-PP3-125U-050D-840-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	769.3	769.3	769.3	769.3	769.3
2.5°	774.1	767.8	769.3	768.1	765.0
5°	772.0	764.7	767.3	764.6	764.6
7.5°	766.7	758.8	761.3	758.6	758.5
10°	761.9	754.0	756.5	753.8	753.1
12.5°	754.9	747.0	750.0	746.8	746.6
15°	742.3	735.1	738.3	735.5	734.2
17.5°	728.2	720.3	724.1	720.3	719.8
20°	717.4	709.5	713.3	707.9	707.9
22.5°	704.4	696.5	700.9	693.9	693.9
25°	683.7	675.8	678.9	672.9	672.2
27.5°	659.0	651.2	654.5	647.7	647.5
30°	641.2	633.9	637.8	630.4	629.7
32.5°	621.8	615.0	617.9	610.4	609.8
35°	590.6	584.7	586.6	579.8	579.2
37.5°	557.9	551.8	553.9	548.1	547.9
40°	534.7	530.7	531.3	526.5	525.2
42.5°	513.1	508.6	509.2	504.4	504.2
45°	480.0	476.8	476.7	472.0	472.0
47.5°	445.0	442.5	441.8	437.8	437.7
50°	420.7	418.7	418.0	414.6	414.0
52.5°	395.4	394.4	392.1	389.3	389.2
55°	356.0	354.7	351.3	349.2	348.6
57.5°	313.2	310.6	306.8	303.8	304.3
60°	282.5	279.9	274.4	273.1	273.1
62.5°	252.8	249.7	244.2	242.3	243.4
65°	210.4	206.4	201.6	200.3	200.9
67.5°	171.8	168.2	163.0	163.0	162.5
70°	147.0	145.0	140.9	140.9	140.9
72.5°	124.9	123.9	121.0	120.9	120.4
75°	95.7	95.7	94.4	93.7	93.0
77.5°	71.7	72.0	71.3	70.6	69.4
80°	56.6	58.0	57.3	56.6	56.0
82.5°	42.6	43.9	43.8	42.6	42.5
85°	22.2	24.2	24.3	24.3	24.3
87.5°	6.3	9.2	11.0	11.2	11.8
90°	2.0	5.9	12.0	13.0	13.0
92.5°	24.3	85.9	169.8	81.7	56.8
95°	55.8	199.0	599.9	306.8	212.2
97.5°	89.1	227.8	940.8	786.0	592.7
100°	114.6	239.3	1049.3	1097.8	910.8
102.5°	139.3	255.4	1085.1	1331.4	1177.8
105°	182.3	283.7	1090.1	1630.9	1530.5
107.5°	223.0	313.4	1043.7	1784.8	1810.7
110°	250.1	335.8	1001.4	1832.6	1927.1



TEST NUMBER: P563666

CATALOG NUMBER: SQ4-PP3-125U-050D-840-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	278.8	358.3	960.8	1822.0	1977.3
115°	321.9	394.0	907.8	1754.0	1983.9
117.5°	361.1	428.7	866.7	1645.4	1901.4
120°	386.6	451.9	846.0	1567.4	1830.5
122.5°	408.9	473.4	830.8	1487.7	1750.0
125°	439.4	504.7	815.1	1377.6	1621.2
127.5°	468.7	533.0	805.1	1280.6	1498.1
130°	486.3	550.6	801.1	1225.0	1416.0
132.5°	503.8	567.3	797.2	1176.0	1351.4
135°	529.1	590.5	792.2	1111.4	1258.5
137.5°	553.2	612.1	789.6	1056.6	1177.4
140°	570.0	626.5	787.2	1022.8	1132.0
142.5°	587.5	640.1	785.6	991.4	1083.3
145°	611.8	659.6	782.2	950.2	1020.4
147.5°	638.1	679.6	778.8	915.6	970.7
150°	655.7	691.7	777.2	893.9	939.6
152.5°	671.6	703.0	776.4	876.1	913.3
155°	694.5	719.9	775.2	852.6	879.9
157.5°	714.7	734.3	775.4	836.0	854.4
160°	727.4	744.0	776.2	826.4	840.0
162.5°	738.6	752.0	777.0	818.3	828.0
165°	753.3	762.1	778.2	809.2	813.1
167.5°	765.3	770.3	779.2	802.2	803.7
170°	773.2	775.2	779.2	798.2	798.2
172.5°	778.0	778.4	780.0	794.2	794.2
175°	783.2	782.2	779.2	790.1	788.2
177.5°	785.4	783.8	779.8	786.2	784.6
180°	782.2	782.2	782.2	782.2	782.2

(END OF REPORT)