

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563930

Luminaire Tested: **SQ4-PR1-025U-125D-840-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-025U-125D-840-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5868.0 lumens
Efficiency: N/A
Efficacy: 118.5 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 49.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563930
CATALOG NUMBER: SQ4-PR1-025U-125D-840-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P563930

CATALOG NUMBER: SQ4-PR1-025U-125D-840-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	115	115	115	115	110	110	110	110	102	102	102	94	94	94	87	87	87	83
1	106	101	97	94	101	97	94	91	90	87	85	84	81	79	77	76	74	71
2	97	89	83	78	93	86	80	75	80	75	71	74	70	67	69	66	63	60
3	89	79	71	65	85	76	69	64	71	65	60	66	61	57	61	58	54	52
4	81	70	62	56	78	68	60	55	63	57	52	59	54	50	55	51	47	45
5	75	63	55	48	72	61	53	47	57	50	45	53	48	43	50	45	41	39
6	69	57	48	42	66	55	47	42	52	45	40	48	43	38	45	41	37	34
7	64	52	43	37	62	50	42	37	47	40	35	44	38	34	42	37	33	31
8	60	47	39	33	57	46	38	33	43	36	32	41	35	31	38	33	29	27
9	56	43	35	30	54	42	35	30	40	33	29	37	32	28	35	30	27	25
10	52	40	32	27	50	39	32	27	37	30	26	35	29	25	33	28	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18053	18053	18053
5°	18215	18076	17981
10°	18158	18032	17937
15°	18078	17966	17869
20°	17987	17871	17739
25°	17861	17741	17534
30°	17668	17542	17291
35°	17407	17255	17008
40°	17010	16828	16523
45°	16316	16031	15702
50°	15095	14732	14442
55°	13176	12876	12606
60°	11103	11009	10791
65°	9603	9641	9566
70°	8821	8864	8864
75°	8470	8470	8530
80°	7970	8060	7970
85°	6426	7135	7135



TEST NUMBER: P563930

CATALOG NUMBER: SQ4-PR1-025U-125D-840-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	185.0	3.2
10°-20°	529.4	9.0
20°-30°	798.5	13.6
30°-40°	951.4	16.2
40°-50°	938.0	16.0
50°-60°	716.9	12.2
60°-70°	443.6	7.6
70°-80°	252.0	4.3
80°-90°	77.5	1.3
90°-100°	73.4	1.3
100°-110°	192.9	3.3
110°-120°	200.0	3.4
120°-130°	160.4	2.7
130°-140°	125.9	2.1
140°-150°	96.6	1.6
150°-160°	69.6	1.2
160°-170°	42.6	0.7
170°-180°	14.4	0.2
0°-30°	1513.0	25.8
0°-40°	2464.4	42.0
0°-60°	4119.3	70.2
0°-90°	4892.4	83.4
90°-120°	466.2	7.9
90°-150°	849.1	14.5
90°-180°	976.0	16.6
0°-180°	5868.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1957	1957	1957	1957	1957	
5°	1967	1945	1952	1945	1942	187
15°	1893	1873	1881	1874	1871	534
25°	1754	1733	1743	1724	1722	807
35°	1546	1527	1532	1512	1510	965
45°	1250	1234	1229	1207	1203	958
55°	819	806	800	787	784	734
65°	440	437	442	438	438	446
75°	238	238	238	239	239	251
85°	61	64	67	67	67	71
90°	1	3	8	4	4	3
95°	10	38	126	65	44	11
105°	35	53	213	324	302	37
115°	62	75	171	341	389	61
125°	86	96	155	263	310	76
135°	102	113	150	212	240	79
145°	119	126	149	181	195	74
155°	134	138	149	163	168	62
165°	145	147	149	154	156	41
175°	150	150	150	152	152	14
180°	150	150	150	150	150	



TEST NUMBER: P563930

CATALOG NUMBER: SQ4-PR1-025U-125D-840-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1956.7	1956.7	1956.7	1956.7	1956.7
2.5°	1968.8	1951.7	1956.7	1952.5	1943.2
5°	1966.8	1945.4	1951.7	1944.8	1941.5
7.5°	1951.7	1930.6	1936.8	1930.0	1928.1
10°	1938.2	1918.4	1924.7	1917.9	1914.6
12.5°	1923.3	1902.2	1909.9	1901.7	1898.4
15°	1892.7	1872.9	1880.9	1874.1	1870.8
17.5°	1859.0	1837.9	1845.8	1838.0	1833.7
20°	1832.0	1812.2	1820.2	1808.4	1806.7
22.5°	1802.3	1782.6	1790.5	1774.7	1774.4
25°	1754.5	1733.0	1742.7	1724.1	1722.4
27.5°	1697.5	1677.7	1685.7	1666.8	1664.8
30°	1658.4	1638.6	1646.6	1626.3	1623.0
32.5°	1613.9	1595.4	1602.1	1581.8	1579.9
35°	1545.5	1527.4	1532.0	1511.7	1510.1
37.5°	1467.6	1451.1	1453.8	1431.5	1429.9
40°	1412.3	1395.9	1397.2	1373.5	1371.9
42.5°	1351.7	1335.2	1333.8	1310.2	1308.5
45°	1250.5	1234.1	1228.6	1206.6	1203.4
47.5°	1135.3	1118.8	1108.6	1090.7	1088.4
50°	1051.7	1035.2	1026.4	1011.1	1006.2
52.5°	961.3	944.9	937.4	923.5	918.5
55°	819.1	805.9	800.5	787.0	783.7
57.5°	683.9	675.0	673.5	660.3	659.0
60°	601.7	596.7	596.6	584.8	584.8
62.5°	531.6	527.9	530.6	522.8	521.5
65°	439.9	436.6	441.6	438.2	438.2
67.5°	367.4	367.4	370.4	369.1	369.1
70°	327.0	327.0	328.6	328.6	328.6
72.5°	290.6	289.2	293.6	293.6	292.2
75°	237.6	237.6	237.6	239.3	239.3
77.5°	185.1	185.4	186.7	186.4	185.1
80°	150.0	151.6	151.7	150.0	150.0
82.5°	114.9	116.6	116.6	116.3	114.9
85°	60.7	64.0	67.4	67.4	67.4
87.5°	17.7	23.4	28.5	27.7	26.4
90°	1.0	2.9	7.7	3.9	3.9
92.5°	4.1	19.5	43.2	19.1	12.4
95°	9.6	38.0	126.4	65.1	44.4
97.5°	16.8	41.7	189.1	150.4	110.8
100°	22.2	44.8	208.4	211.2	164.0
102.5°	26.8	48.0	213.8	263.1	222.7
105°	34.7	52.7	213.2	323.7	302.0
107.5°	42.8	59.4	201.1	355.2	360.5
110°	48.2	63.3	191.1	363.3	386.0

TEST NUMBER: P563930

CATALOG NUMBER: SQ4-PR1-025U-125D-840-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	53.6	68.0	181.8	358.2	392.9
115°	61.8	75.0	170.8	340.7	388.9
117.5°	69.7	81.7	163.3	316.5	369.9
120°	74.3	85.6	160.2	300.3	352.2
122.5°	78.9	90.3	157.9	284.1	335.2
125°	85.9	96.3	155.3	262.6	309.7
127.5°	91.5	102.0	153.2	245.2	285.0
130°	94.6	105.9	152.5	234.3	271.1
132.5°	97.6	109.0	151.7	225.0	258.0
135°	102.3	112.7	150.5	212.0	240.3
137.5°	107.1	117.3	150.3	202.2	225.4
140°	111.0	120.4	149.6	194.4	216.1
142.5°	114.1	122.7	149.6	189.0	207.6
145°	118.7	126.2	148.6	180.8	194.9
147.5°	123.3	130.7	148.6	173.9	185.6
150°	126.4	133.0	148.6	170.0	179.5
152.5°	129.5	134.6	148.6	166.9	174.1
155°	134.1	137.9	148.6	163.2	167.9
157.5°	137.6	141.2	148.6	159.9	163.3
160°	139.9	142.7	148.6	158.3	160.2
162.5°	142.2	144.3	148.6	156.7	158.6
165°	144.7	146.6	148.6	154.4	156.3
167.5°	147.1	148.0	149.6	153.4	154.2
170°	148.6	149.5	149.6	153.4	153.4
172.5°	149.4	149.6	149.6	152.6	151.9
175°	150.5	150.5	149.6	151.5	151.5
177.5°	150.5	150.5	149.8	151.3	150.5
180°	150.5	150.5	150.5	150.5	150.5

(END OF REPORT)