

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564122

Luminaire Tested: **SQ4-PR1-075U-125D-840-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564122
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-075U-125D-840-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7916.6 lumens
Efficiency: N/A
Efficacy: 127.5 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 62.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564122
CATALOG NUMBER: SQ4-PR1-075U-125D-840-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P564122

CATALOG NUMBER: SQ4-PR1-075U-125D-840-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	97	93	89	94	91	87	84	79	77	75	69	67	66	60	58	57	53
2	92	85	79	74	86	80	74	70	70	66	62	61	58	55	53	51	49	45
3	84	75	67	62	79	70	64	59	62	57	53	54	51	47	47	44	42	38
4	77	66	59	53	72	63	56	50	55	50	45	49	44	41	42	39	36	33
5	71	59	51	45	66	56	49	43	50	44	39	44	39	36	38	35	32	29
6	66	53	45	39	61	51	43	38	45	39	35	40	35	31	35	31	28	26
7	61	48	40	35	57	46	38	33	41	35	31	36	31	28	32	28	25	23
8	56	44	36	31	53	42	35	30	37	31	27	33	28	25	29	25	23	20
9	53	40	33	28	49	38	31	27	34	29	24	31	26	22	27	23	20	18
10	49	37	30	25	46	35	28	24	32	26	22	28	24	20	25	21	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18053	18053	18053
5°	18215	18076	17981
10°	18158	18032	17937
15°	18078	17966	17869
20°	17987	17871	17739
25°	17861	17741	17534
30°	17668	17542	17291
35°	17407	17255	17008
40°	17010	16828	16523
45°	16316	16031	15702
50°	15095	14732	14442
55°	13176	12876	12606
60°	11103	11009	10791
65°	9603	9641	9566
70°	8821	8864	8864
75°	8470	8470	8530
80°	7970	8060	7970
85°	6426	7135	7135



TEST NUMBER: P564122

CATALOG NUMBER: SQ4-PR1-075U-125D-840-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	185.0	2.3
10°-20°	529.4	6.7
20°-30°	798.5	10.1
30°-40°	951.4	12.0
40°-50°	938.0	11.8
50°-60°	716.9	9.1
60°-70°	443.6	5.6
70°-80°	252.0	3.2
80°-90°	77.8	1.0
90°-100°	218.9	2.8
100°-110°	602.3	7.6
110°-120°	621.7	7.9
120°-130°	498.1	6.3
130°-140°	391.2	4.9
140°-150°	299.8	3.8
150°-160°	215.6	2.7
160°-170°	131.8	1.7
170°-180°	44.4	0.6
0°-30°	1513.0	19.1
0°-40°	2464.4	31.1
0°-60°	4119.3	52.0
0°-90°	4892.7	61.8
90°-120°	1442.9	18.2
90°-150°	2632.1	33.2
90°-180°	3024.0	38.2
0°-180°	7916.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1957	1957	1957	1957	1957	
5°	1967	1945	1952	1945	1942	187
15°	1893	1873	1881	1874	1871	534
25°	1754	1733	1743	1724	1722	807
35°	1546	1527	1532	1512	1510	965
45°	1250	1234	1229	1207	1203	958
55°	819	806	800	787	784	734
65°	440	437	442	438	438	446
75°	238	238	238	239	239	251
85°	61	64	67	67	67	71
90°	1	4	7	9	9	5
95°	33	120	387	166	106	34
105°	108	166	664	1011	943	113
115°	191	232	532	1060	1203	188
125°	263	299	483	817	957	234
135°	317	352	469	661	748	245
145°	366	392	462	563	606	230
155°	415	428	459	506	520	191
165°	448	454	461	480	483	126
175°	464	465	462	468	467	44
180°	464	464	464	464	464	

TEST NUMBER: P564122

CATALOG NUMBER: SQ4-PR1-075U-125D-840-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1956.7	1956.7	1956.7	1956.7	1956.7
2.5°	1968.8	1951.7	1956.7	1952.5	1943.2
5°	1966.8	1945.4	1951.7	1944.8	1941.5
7.5°	1951.7	1930.6	1936.8	1930.0	1928.1
10°	1938.2	1918.4	1924.7	1917.9	1914.6
12.5°	1923.3	1902.2	1909.9	1901.7	1898.4
15°	1892.7	1872.9	1880.9	1874.1	1870.8
17.5°	1859.0	1837.9	1845.8	1838.0	1833.7
20°	1832.0	1812.2	1820.2	1808.4	1806.7
22.5°	1802.3	1782.6	1790.5	1774.7	1774.4
25°	1754.5	1733.0	1742.7	1724.1	1722.4
27.5°	1697.5	1677.7	1685.7	1666.8	1664.8
30°	1658.4	1638.6	1646.6	1626.3	1623.0
32.5°	1613.9	1595.4	1602.1	1581.8	1579.9
35°	1545.5	1527.4	1532.0	1511.7	1510.1
37.5°	1467.6	1451.1	1453.8	1431.5	1429.9
40°	1412.3	1395.9	1397.2	1373.5	1371.9
42.5°	1351.7	1335.2	1333.8	1310.2	1308.5
45°	1250.5	1234.1	1228.6	1206.6	1203.4
47.5°	1135.3	1118.8	1108.6	1090.7	1088.4
50°	1051.7	1035.2	1026.4	1011.1	1006.2
52.5°	961.3	944.9	937.4	923.5	918.5
55°	819.1	805.9	800.5	787.0	783.7
57.5°	683.9	675.0	673.5	660.3	659.0
60°	601.7	596.7	596.6	584.8	584.8
62.5°	531.6	527.9	530.6	522.8	521.5
65°	439.9	436.6	441.6	438.2	438.2
67.5°	367.4	367.4	370.4	369.1	369.1
70°	327.0	327.0	328.6	328.6	328.6
72.5°	290.6	289.2	293.6	293.6	292.2
75°	237.6	237.6	237.6	239.3	239.3
77.5°	185.1	185.4	186.7	186.4	185.1
80°	150.0	151.6	151.7	150.0	150.0
82.5°	114.9	116.6	116.6	116.3	114.9
85°	60.7	64.0	67.4	67.4	67.4
87.5°	17.7	23.6	28.3	28.7	27.4
90°	1.0	3.9	6.9	8.9	8.9
92.5°	13.6	58.2	100.9	38.8	31.8
95°	32.6	119.5	387.1	165.5	105.7
97.5°	53.1	132.5	590.8	455.2	321.2
100°	68.1	140.6	654.8	660.9	539.2
102.5°	82.4	150.2	671.4	819.9	708.3
105°	107.6	165.6	663.7	1010.8	943.2
107.5°	131.7	184.7	625.9	1104.2	1124.3
110°	149.1	197.4	597.5	1127.4	1197.0

TEST NUMBER: P564122

CATALOG NUMBER: SQ4-PR1-075U-125D-840-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	164.9	211.7	569.1	1112.5	1218.3
115°	190.6	232.1	532.3	1060.0	1202.9
117.5°	215.1	253.3	509.0	986.3	1148.0
120°	230.1	266.8	498.7	931.2	1098.2
122.5°	243.5	280.2	491.6	882.8	1041.3
125°	262.7	299.4	482.9	817.0	957.0
127.5°	280.9	315.8	477.2	762.1	884.9
130°	290.4	326.1	474.1	729.4	841.4
132.5°	301.4	337.1	471.7	700.7	801.9
135°	317.0	351.8	469.1	660.7	747.6
137.5°	331.6	363.9	466.9	628.4	700.0
140°	342.7	372.6	466.1	606.9	671.6
142.5°	352.2	379.8	464.6	587.7	643.1
145°	366.4	391.5	462.2	562.9	606.4
147.5°	381.6	403.2	461.0	541.0	575.8
150°	391.1	410.4	460.2	529.0	556.0
152.5°	399.8	417.6	459.4	518.6	541.0
155°	414.8	428.3	459.2	506.0	520.5
157.5°	425.7	436.7	459.2	495.6	505.7
160°	433.6	442.2	459.2	490.0	497.8
162.5°	439.9	447.0	460.0	485.3	491.4
165°	448.4	454.2	461.2	480.0	482.9
167.5°	454.3	458.7	462.2	475.6	476.4
170°	458.2	461.1	462.2	474.1	474.1
172.5°	461.4	462.8	462.2	471.7	470.9
175°	464.2	465.1	462.2	468.1	467.1
177.5°	465.0	465.0	461.8	466.5	465.0
180°	464.2	464.2	464.2	464.2	464.2

(END OF REPORT)