

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564530

Luminaire Tested: **SQ4-PW1-025U-050D-840-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P564530  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2106-289-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PW1-025U-050D-840-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 4000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2923.9 lumens  
Efficiency: N/A  
Efficacy: 132.3 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 22.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P564530  
CATALOG NUMBER: SQ4-PW1-025U-050D-840-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P564530

CATALOG NUMBER: SQ4-PW1-025U-050D-840-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	71	71	71	67
1	102	97	93	90	96	92	88	85	82	79	77	72	70	68	63	62	61	56
2	93	85	79	74	87	80	75	70	72	67	64	63	60	57	56	53	51	47
3	85	75	67	61	79	71	64	59	63	58	54	56	52	49	50	46	44	40
4	78	66	58	52	73	63	56	50	56	50	46	50	45	42	44	41	38	35
5	71	59	51	45	67	56	49	43	50	44	40	45	40	36	40	36	33	30
6	66	53	45	39	62	51	43	38	46	39	35	41	36	32	36	32	29	26
7	61	48	40	34	57	46	38	33	41	35	31	37	32	28	33	29	26	23
8	57	44	36	30	53	42	35	29	38	32	27	34	29	25	31	26	23	21
9	53	40	32	27	50	38	31	26	35	29	25	31	26	23	28	24	21	19
10	49	37	30	25	47	35	28	24	32	26	22	29	24	21	26	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7062	7062	7062
5°	7108	7052	7020
10°	7051	6994	6956
15°	6977	6899	6873
20°	6892	6786	6774
25°	6796	6673	6653
30°	6653	6552	6509
35°	6464	6373	6334
40°	6263	6165	6140
45°	6019	5939	5913
50°	5769	5721	5683
55°	5500	5500	5413
60°	5165	5264	5076
65°	4726	4962	4609
70°	4165	4567	4057
75°	3558	4085	3461
80°	2758	3438	2795
85°	1789	2646	2361



TEST NUMBER: P564530

CATALOG NUMBER: SQ4-PW1-025U-050D-840-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	72.1	2.5
10°-20°	203.5	7.0
20°-30°	301.8	10.3
30°-40°	353.2	12.1
40°-50°	351.6	12.0
50°-60°	303.6	10.4
60°-70°	218.6	7.5
70°-80°	114.6	3.9
80°-90°	29.2	1.0
90°-100°	73.4	2.5
100°-110°	192.9	6.6
110°-120°	200.0	6.8
120°-130°	160.4	5.5
130°-140°	125.9	4.3
140°-150°	96.6	3.3
150°-160°	69.6	2.4
160°-170°	42.6	1.5
170°-180°	14.4	0.5
0°-30°	577.4	19.7
0°-40°	930.6	31.8
0°-60°	1585.9	54.2
0°-90°	1948.3	66.6
90°-120°	466.2	15.9
90°-150°	849.1	29.0
90°-180°	976.0	33.4
0°-180°	2923.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	765	765	765	765	765	
5°	768	759	761	759	758	73
15°	730	721	722	721	720	206
25°	668	656	656	652	654	307
35°	574	566	566	560	562	359
45°	461	457	455	454	453	356
55°	342	341	342	337	336	305
65°	216	223	227	218	211	215
75°	100	109	115	107	97	107
85°	17	22	25	24	22	22
90°	1	3	8	4	4	1
95°	10	38	126	65	44	11
105°	35	53	213	324	302	37
115°	62	75	171	341	389	61
125°	86	96	155	263	310	76
135°	102	113	150	212	240	79
145°	119	126	149	181	195	74
155°	134	138	149	163	168	62
165°	145	147	149	154	156	41
175°	150	150	150	152	152	14
180°	150	150	150	150	150	

TEST NUMBER: P564530

CATALOG NUMBER: SQ4-PW1-025U-050D-840-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	765.4	765.4	765.4	765.4	765.4
2.5°	769.7	763.4	765.4	763.7	760.0
5°	767.5	758.9	761.4	759.3	758.0
7.5°	759.6	751.7	753.6	751.4	750.6
10°	752.6	744.7	746.5	743.8	742.5
12.5°	744.5	736.1	737.9	735.2	734.4
15°	730.4	721.1	722.3	720.9	719.6
17.5°	713.9	704.5	704.7	702.6	702.3
20°	702.0	692.1	691.2	688.6	689.9
22.5°	689.1	678.7	677.8	674.0	675.9
25°	667.6	656.4	655.5	651.5	653.5
27.5°	642.8	631.7	631.8	626.1	628.3
30°	624.5	613.9	615.0	608.4	611.0
32.5°	605.1	595.6	596.2	589.5	592.1
35°	573.9	566.0	565.8	560.5	562.4
37.5°	542.1	535.1	534.0	530.9	531.4
40°	520.0	514.0	511.9	509.8	509.8
42.5°	496.8	491.3	489.2	487.7	487.2
45°	461.3	457.3	455.2	453.8	453.2
47.5°	426.2	422.5	420.7	419.7	419.1
50°	401.9	399.3	398.6	396.5	395.9
52.5°	377.7	376.1	375.4	372.8	372.1
55°	341.9	341.3	341.9	337.2	336.5
57.5°	304.7	305.7	307.9	301.5	300.0
60°	279.9	282.5	285.3	277.8	275.1
62.5°	254.5	258.7	262.6	254.0	250.3
65°	216.5	223.1	227.3	218.3	211.1
67.5°	179.8	188.0	193.0	183.4	175.2
70°	154.4	163.7	169.3	159.6	150.4
72.5°	132.3	142.6	147.2	138.0	128.8
75°	99.8	109.0	114.6	107.0	97.1
77.5°	70.8	79.5	84.2	77.5	69.3
80°	51.9	61.2	64.7	59.2	52.6
82.5°	36.8	44.5	46.9	43.6	39.1
85°	16.9	22.1	25.0	23.6	22.3
87.5°	4.5	8.6	11.8	11.0	11.6
90°	1.0	2.9	7.7	3.9	3.9
92.5°	4.1	19.5	43.2	19.1	12.4
95°	9.6	38.0	126.4	65.1	44.4
97.5°	16.8	41.7	189.1	150.4	110.8
100°	22.2	44.8	208.4	211.2	164.0
102.5°	26.8	48.0	213.8	263.1	222.7
105°	34.7	52.7	213.2	323.7	302.0
107.5°	42.8	59.4	201.1	355.2	360.5
110°	48.2	63.3	191.1	363.3	386.0

TEST NUMBER: P564530

CATALOG NUMBER: SQ4-PW1-025U-050D-840-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	53.6	68.0	181.8	358.2	392.9
115°	61.8	75.0	170.8	340.7	388.9
117.5°	69.7	81.7	163.3	316.5	369.9
120°	74.3	85.6	160.2	300.3	352.2
122.5°	78.9	90.3	157.9	284.1	335.2
125°	85.9	96.3	155.3	262.6	309.7
127.5°	91.5	102.0	153.2	245.2	285.0
130°	94.6	105.9	152.5	234.3	271.1
132.5°	97.6	109.0	151.7	225.0	258.0
135°	102.3	112.7	150.5	212.0	240.3
137.5°	107.1	117.3	150.3	202.2	225.4
140°	111.0	120.4	149.6	194.4	216.1
142.5°	114.1	122.7	149.6	189.0	207.6
145°	118.7	126.2	148.6	180.8	194.9
147.5°	123.3	130.7	148.6	173.9	185.6
150°	126.4	133.0	148.6	170.0	179.5
152.5°	129.5	134.6	148.6	166.9	174.1
155°	134.1	137.9	148.6	163.2	167.9
157.5°	137.6	141.2	148.6	159.9	163.3
160°	139.9	142.7	148.6	158.3	160.2
162.5°	142.2	144.3	148.6	156.7	158.6
165°	144.7	146.6	148.6	154.4	156.3
167.5°	147.1	148.0	149.6	153.4	154.2
170°	148.6	149.5	149.6	153.4	153.4
172.5°	149.4	149.6	149.6	152.6	151.9
175°	150.5	150.5	149.6	151.5	151.5
177.5°	150.5	150.5	149.8	151.3	150.5
180°	150.5	150.5	150.5	150.5	150.5

(END OF REPORT)