

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P565020

Luminaire Tested: **SQ4-PW1-125U-050D-935-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P565020
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-125U-050D-935-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12041.4 lumens
Efficiency: N/A
Efficacy: 124.4 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 96.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P565020
CATALOG NUMBER: SQ4-PW1-125U-050D-935-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P565020

CATALOG NUMBER: SQ4-PW1-125U-050D-935-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28
1	93	89	85	82	83	79	76	74	62	60	58	46	45	44	32	31	30	24
2	85	77	72	67	75	69	65	60	55	51	48	41	39	37	28	27	26	20
3	77	68	61	55	69	61	55	50	48	44	41	36	33	31	25	23	22	17
4	70	60	53	47	63	54	48	43	43	38	34	32	29	26	22	20	19	14
5	65	53	46	40	58	48	41	36	38	33	30	29	25	23	20	18	16	13
6	59	48	40	34	53	43	36	31	34	29	26	26	22	20	18	16	14	11
7	55	43	35	30	49	39	32	27	31	26	22	23	20	18	16	14	13	10
8	51	39	31	26	45	35	29	24	28	23	20	21	18	16	15	13	11	9
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6075	6075	6075
5°	6114	6066	6039
10°	6066	6016	5984
15°	6001	5934	5912
20°	5929	5838	5827
25°	5847	5740	5723
30°	5723	5637	5599
35°	5561	5482	5450
40°	5387	5303	5282
45°	5177	5110	5087
50°	4963	4921	4888
55°	4732	4732	4657
60°	4442	4528	4368
65°	4065	4268	3965
70°	3584	3928	3489
75°	3060	3515	2978
80°	2372	2959	2404
85°	1535	2271	2027



TEST NUMBER: P565020

CATALOG NUMBER: SQ4-PW1-125U-050D-935-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.0	1.0
10°-20°	350.1	2.9
20°-30°	519.3	4.3
30°-40°	607.7	5.0
40°-50°	604.9	5.0
50°-60°	522.4	4.3
60°-70°	376.0	3.1
70°-80°	197.2	1.6
80°-90°	52.1	0.4
90°-100°	629.6	5.2
100°-110°	1695.9	14.1
110°-120°	1779.8	14.8
120°-130°	1444.2	12.0
130°-140°	1132.7	9.4
140°-150°	869.6	7.2
150°-160°	625.2	5.2
160°-170°	382.0	3.2
170°-180°	128.8	1.1
0°-30°	993.4	8.3
0°-40°	1601.1	13.3
0°-60°	2728.4	22.7
0°-90°	3353.7	27.9
90°-120°	4105.2	34.1
90°-150°	7551.7	62.7
90°-180°	8688.0	72.2
0°-180°	12041.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1317	1317	1317	1317	1317	
5°	1320	1306	1310	1306	1304	125
15°	1257	1241	1243	1240	1238	354
25°	1149	1129	1128	1121	1124	528
35°	987	974	974	964	968	617
45°	794	787	783	781	780	612
55°	588	587	588	580	579	525
65°	372	384	391	376	363	369
75°	172	188	197	184	167	184
85°	29	38	43	41	38	38
90°	3	10	21	22	22	8
95°	96	342	1032	528	365	100
105°	314	488	1876	2806	2633	330
115°	554	678	1562	3018	3413	545
125°	756	868	1402	2370	2789	675
135°	910	1016	1363	1912	2165	703
145°	1053	1135	1346	1635	1756	660
155°	1195	1238	1334	1467	1514	550
165°	1296	1311	1339	1392	1399	365
175°	1348	1346	1341	1359	1356	128
180°	1346	1346	1346	1346	1346	

TEST NUMBER: P565020

CATALOG NUMBER: SQ4-PW1-125U-050D-935-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1316.9	1316.9	1316.9	1316.9	1316.9
2.5°	1324.3	1313.4	1316.9	1314.0	1307.6
5°	1320.4	1305.6	1309.9	1306.4	1304.1
7.5°	1306.9	1293.3	1296.5	1292.7	1291.4
10°	1294.9	1281.2	1284.4	1279.7	1277.4
12.5°	1280.9	1266.4	1269.6	1264.9	1263.5
15°	1256.6	1240.7	1242.6	1240.3	1238.0
17.5°	1228.3	1212.1	1212.5	1208.7	1208.3
20°	1207.8	1190.8	1189.3	1184.7	1186.9
22.5°	1185.6	1167.6	1166.1	1159.6	1162.8
25°	1148.7	1129.4	1127.8	1120.9	1124.3
27.5°	1106.0	1086.9	1086.9	1077.3	1080.9
30°	1074.4	1056.3	1058.2	1046.7	1051.2
32.5°	1041.0	1024.6	1025.7	1014.2	1018.7
35°	987.4	973.8	973.5	964.3	967.7
37.5°	932.6	920.6	918.7	913.4	914.3
40°	894.6	884.4	880.6	877.2	877.2
42.5°	854.6	845.3	841.7	839.1	838.2
45°	793.6	786.8	783.2	780.8	779.7
47.5°	733.3	726.9	723.8	722.1	721.0
50°	691.5	687.0	685.7	682.2	681.1
52.5°	649.7	647.0	645.8	641.4	640.2
55°	588.3	587.1	588.3	580.1	579.0
57.5°	524.2	526.0	529.8	518.8	516.1
60°	481.5	486.0	490.8	477.9	473.4
62.5°	437.9	445.1	451.8	437.0	430.7
65°	372.4	383.8	391.0	375.6	363.2
67.5°	309.3	323.4	332.1	315.5	301.4
70°	265.7	281.6	291.2	274.6	258.7
72.5°	227.6	245.3	253.2	237.5	221.6
75°	171.7	187.6	197.2	184.1	167.1
77.5°	121.8	136.8	144.8	133.3	119.3
80°	89.3	105.2	111.4	101.8	90.5
82.5°	63.4	76.5	80.8	75.0	67.3
85°	29.0	38.1	42.9	40.6	38.3
87.5°	8.1	15.8	21.8	22.1	23.0
90°	3.4	10.1	20.6	22.3	22.3
92.5°	41.8	147.8	292.1	140.6	97.7
95°	96.0	342.4	1032.0	527.8	365.2
97.5°	153.3	392.0	1618.7	1352.3	1019.7
100°	197.2	411.7	1805.2	1888.8	1566.9
102.5°	239.7	439.5	1866.9	2290.6	2026.4
105°	313.7	488.1	1875.5	2805.9	2633.3
107.5°	383.7	539.2	1795.6	3070.7	3115.3
110°	430.3	577.8	1722.9	3153.0	3315.6

TEST NUMBER: P565020

CATALOG NUMBER: SQ4-PW1-125U-050D-935-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	479.7	616.5	1653.0	3134.8	3402.0
115°	553.7	677.8	1561.8	3017.7	3413.3
117.5°	621.3	737.6	1491.2	2830.8	3271.3
120°	665.2	777.5	1455.5	2696.7	3149.3
122.5°	703.6	814.5	1429.4	2559.5	3010.8
125°	756.0	868.3	1402.3	2370.2	2789.3
127.5°	806.4	917.1	1385.2	2203.2	2577.4
130°	836.6	947.2	1378.3	2107.6	2436.1
132.5°	866.8	976.1	1371.5	2023.3	2325.0
135°	910.3	1015.9	1362.9	1912.1	2165.2
137.5°	951.8	1053.1	1358.5	1817.8	2025.7
140°	980.6	1077.8	1354.3	1759.8	1947.5
142.5°	1010.8	1101.3	1351.6	1705.6	1863.9
145°	1052.6	1134.8	1345.8	1634.8	1755.5
147.5°	1097.9	1169.3	1339.9	1575.3	1670.1
150°	1128.0	1190.1	1337.2	1537.9	1616.6
152.5°	1155.5	1209.5	1335.8	1507.3	1571.4
155°	1194.9	1238.5	1333.8	1466.8	1513.8
157.5°	1229.5	1263.4	1334.1	1438.4	1469.9
160°	1251.5	1280.0	1335.5	1421.7	1445.2
162.5°	1270.7	1293.8	1336.9	1407.9	1424.6
165°	1296.1	1311.1	1338.9	1392.2	1398.9
167.5°	1316.6	1325.3	1340.6	1380.1	1382.8
170°	1330.3	1333.7	1340.6	1373.2	1373.2
172.5°	1338.6	1339.2	1342.0	1366.3	1366.3
175°	1347.5	1345.8	1340.6	1359.4	1356.1
177.5°	1351.3	1348.6	1341.7	1352.6	1349.9
180°	1345.8	1345.8	1345.8	1345.8	1345.8

(END OF REPORT)