

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P565188

Luminaire Tested: **SQ4-PW1-150U-125D-935-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P565188
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-150U-125D-935-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18845.1 lumens
Efficiency: N/A
Efficacy: 112.3 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 167.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P565188
CATALOG NUMBER: SQ4-PW1-150U-125D-935-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P565188

CATALOG NUMBER: SQ4-PW1-150U-125D-935-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44
1	97	92	89	85	88	85	82	79	70	68	66	57	56	54	45	44	43	38
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	40	38	37	32
3	80	71	64	58	73	65	59	54	55	50	46	45	41	38	35	33	31	27
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	32	29	27	23
5	67	56	48	42	62	52	45	39	43	38	34	36	32	29	29	26	23	20
6	62	50	42	36	57	46	39	34	39	34	30	32	28	25	26	23	21	18
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14
9	50	37	30	25	45	35	28	24	30	24	21	25	21	18	20	17	15	13
10	46	34	27	22	42	32	25	21	27	22	19	23	19	16	19	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15182	15182	15182
5°	15280	15160	15092
10°	15158	15036	14955
15°	14998	14831	14776
20°	14818	14591	14562
25°	14611	14346	14301
30°	14303	14087	13994
35°	13896	13700	13619
40°	13463	13253	13201
45°	12939	12769	12712
50°	12403	12299	12215
55°	11824	11824	11637
60°	11102	11316	10916
65°	10160	10667	9907
70°	8956	9816	8721
75°	7648	8785	7441
80°	5932	7396	6009
85°	3837	5679	5065



TEST NUMBER: P565188

CATALOG NUMBER: SQ4-PW1-150U-125D-935-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	309.9	1.6
10°-20°	875.0	4.6
20°-30°	1297.8	6.9
30°-40°	1518.6	8.1
40°-50°	1511.8	8.0
50°-60°	1305.5	6.9
60°-70°	939.7	5.0
70°-80°	492.8	2.6
80°-90°	125.6	0.7
90°-100°	754.6	4.0
100°-110°	2040.2	10.8
110°-120°	2145.0	11.4
120°-130°	1742.3	9.2
130°-140°	1366.7	7.3
140°-150°	1049.0	5.6
150°-160°	754.4	4.0
160°-170°	460.8	2.4
170°-180°	155.4	0.8
0°-30°	2482.7	13.2
0°-40°	4001.3	21.2
0°-60°	6818.7	36.2
0°-90°	8376.8	44.5
90°-120°	4939.8	26.2
90°-150°	9097.7	48.3
90°-180°	10468.0	55.5
0°-180°	18845.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3291	3291	3291	3291	3291	
5°	3300	3263	3274	3265	3259	313
15°	3140	3101	3106	3100	3094	885
25°	2871	2822	2818	2801	2810	1320
35°	2468	2434	2433	2410	2418	1543
45°	1983	1966	1957	1951	1949	1530
55°	1470	1467	1470	1450	1447	1312
65°	931	959	977	939	908	922
75°	429	469	493	460	418	460
85°	72	95	107	101	96	96
90°	4	10	23	24	23	10
95°	117	411	1255	649	386	123
105°	379	586	2263	3339	3202	399
115°	668	816	1877	3634	4102	659
125°	914	1047	1692	2855	3354	815
135°	1096	1226	1646	2305	2609	847
145°	1274	1370	1624	1973	2124	797
155°	1438	1495	1610	1770	1828	663
165°	1566	1581	1617	1680	1688	441
175°	1625	1624	1618	1639	1636	154
180°	1624	1624	1624	1624	1624	

TEST NUMBER: P565188

CATALOG NUMBER: SQ4-PW1-150U-125D-935-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3291.1	3291.1	3291.1	3291.1	3291.1
2.5°	3309.6	3282.4	3291.1	3283.8	3267.9
5°	3299.8	3262.9	3273.7	3264.9	3259.2
7.5°	3266.1	3232.1	3240.1	3230.7	3227.3
10°	3236.0	3202.0	3209.9	3198.2	3192.5
12.5°	3201.2	3164.9	3172.8	3161.1	3157.7
15°	3140.3	3100.6	3105.5	3099.6	3093.9
17.5°	3069.6	3029.3	3030.1	3020.8	3019.7
20°	3018.5	2976.0	2972.1	2960.7	2966.3
22.5°	2962.8	2918.0	2914.1	2898.1	2906.0
25°	2870.6	2822.4	2818.4	2801.2	2809.7
27.5°	2763.9	2716.3	2716.4	2692.2	2701.3
30°	2685.1	2639.7	2644.5	2615.7	2627.1
32.5°	2601.6	2560.7	2563.3	2534.5	2545.9
35°	2467.6	2433.6	2432.8	2409.8	2418.3
37.5°	2330.7	2300.7	2295.9	2282.6	2284.9
40°	2235.6	2210.1	2200.8	2192.1	2192.1
42.5°	2135.9	2112.6	2103.4	2097.0	2094.7
45°	1983.3	1966.3	1957.3	1951.4	1948.6
47.5°	1832.6	1816.7	1808.8	1804.7	1801.8
50°	1728.2	1716.8	1713.7	1704.9	1702.1
52.5°	1623.8	1617.0	1613.9	1602.9	1600.0
55°	1470.1	1467.3	1470.1	1449.8	1446.9
57.5°	1310.1	1314.6	1324.0	1296.6	1289.8
60°	1203.3	1214.7	1226.5	1194.4	1183.1
62.5°	1094.3	1112.5	1129.1	1092.2	1076.3
65°	930.8	959.1	977.2	938.8	907.6
67.5°	773.0	808.2	829.9	788.5	753.3
70°	664.0	703.7	727.8	686.3	646.6
72.5°	568.9	613.1	632.7	593.5	553.8
75°	429.1	468.8	492.9	460.1	417.5
77.5°	304.5	341.9	361.9	333.2	298.1
80°	223.3	263.0	278.4	254.5	226.2
82.5°	158.3	191.2	201.8	187.5	168.2
85°	72.5	95.2	107.3	101.4	95.7
87.5°	19.3	36.5	48.6	49.0	50.9
90°	3.5	10.3	22.7	24.4	22.7
92.5°	49.6	180.9	356.9	154.9	112.2
95°	117.1	411.0	1254.9	649.4	386.3
97.5°	188.1	471.4	1956.1	1618.8	1188.8
100°	241.2	495.8	2174.2	2267.5	1833.4
102.5°	290.1	529.7	2251.1	2759.3	2434.6
105°	379.3	586.0	2263.3	3338.6	3201.9
107.5°	461.8	650.4	2164.4	3700.0	3745.4
110°	526.1	697.0	2076.3	3797.0	3990.1

TEST NUMBER: P565188

CATALOG NUMBER: SQ4-PW1-150U-125D-935-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	583.4	743.4	1995.2	3777.6	4102.0
115°	667.6	816.3	1877.1	3633.7	4102.0
117.5°	750.1	889.6	1799.1	3413.9	3944.7
120°	800.5	937.2	1753.0	3256.1	3797.9
122.5°	848.0	982.0	1725.0	3087.0	3632.9
125°	914.1	1047.4	1691.8	2854.9	3353.9
127.5°	974.9	1105.8	1672.2	2665.5	3104.4
130°	1008.5	1143.5	1663.9	2548.5	2945.0
132.5°	1043.4	1177.0	1655.5	2442.9	2807.9
135°	1095.8	1225.7	1646.4	2305.2	2609.4
137.5°	1148.6	1271.3	1638.7	2193.5	2441.3
140°	1185.0	1299.5	1635.9	2121.5	2342.0
142.5°	1219.9	1327.6	1630.3	2056.6	2249.7
145°	1274.1	1369.8	1623.7	1973.1	2123.5
147.5°	1323.4	1408.2	1616.0	1897.5	2013.1
150°	1359.7	1434.9	1613.2	1856.5	1948.7
152.5°	1393.3	1458.9	1611.8	1818.3	1894.2
155°	1438.4	1494.8	1609.7	1770.0	1828.1
157.5°	1485.2	1524.5	1610.0	1736.4	1774.7
160°	1511.8	1544.3	1611.4	1715.2	1742.5
162.5°	1532.8	1559.8	1612.8	1698.2	1718.7
165°	1566.0	1581.4	1616.7	1679.8	1688.3
167.5°	1588.7	1599.3	1617.0	1664.0	1668.1
170°	1602.7	1607.8	1618.4	1656.9	1656.9
172.5°	1613.9	1614.9	1618.4	1648.4	1647.1
175°	1625.4	1623.7	1618.4	1639.3	1635.9
177.5°	1629.3	1625.2	1618.1	1632.0	1627.9
180°	1623.7	1623.7	1623.7	1623.7	1623.7

(END OF REPORT)