

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: CORELITE

Report Number: P519014

Luminaire Tested: **SQ4-WB-025U-075D-935-1D-UNV-STD-W-8**

Issue Date: 4/29/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P519014  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2009-966-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 4/29/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-WB-025U-075D-935-1D-UNV-STD-W-8  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6013.0 lumens  
Efficiency: N/A  
Efficacy: 92.6 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02  
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 64.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P519014  
CATALOG NUMBER: SQ4-WB-025U-075D-935-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P519014

CATALOG NUMBER: SQ4-WB-025U-075D-935-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	76	76	76	72
1	104	101	97	94	99	96	93	90	86	84	82	78	76	75	70	69	68	64
2	96	90	84	80	91	86	81	77	78	74	71	70	68	65	64	62	60	56
3	89	81	74	69	85	77	71	66	70	66	62	64	60	57	58	55	53	50
4	83	73	65	60	78	70	63	58	64	58	54	58	54	51	53	50	47	44
5	77	66	58	53	73	63	56	51	58	52	48	53	49	45	49	45	42	40
6	71	60	52	47	68	58	51	46	53	47	43	49	44	41	45	41	38	36
7	67	55	47	42	63	53	46	41	49	43	39	45	40	37	42	38	35	33
8	62	51	43	38	59	49	42	37	45	40	35	42	37	34	39	35	32	30
9	58	47	40	35	56	45	39	34	42	36	32	39	34	31	36	32	29	27
10	55	43	36	32	52	42	35	31	39	34	30	36	32	28	34	30	27	25

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13718	13718	13718
5°	13546	13498	13576
10°	12798	12915	13214
15°	11814	12089	12631
20°	10729	11133	11869
25°	9623	10148	11058
30°	8604	9167	10217
35°	7524	8068	9222
40°	6333	6836	7983
45°	5226	5678	6665
50°	4363	4757	5553
55°	3704	4082	4586
60°	3166	3539	3659
65°	2520	2977	2364
70°	2235	2323	1443
75°	2069	1884	884
80°	1907	1732	762
85°	1725	1588	619



TEST NUMBER: P519014

CATALOG NUMBER: SQ4-WB-025U-075D-935-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	272.7	4.5
10°-20°	709.4	11.8
20°-30°	918.9	15.3
30°-40°	899.8	15.0
40°-50°	688.8	11.5
50°-60°	459.0	7.6
60°-70°	250.5	4.2
70°-80°	104.4	1.7
80°-90°	30.9	0.5
90°-100°	126.2	2.1
100°-110°	331.8	5.5
110°-120°	344.1	5.7
120°-130°	276.0	4.6
130°-140°	216.6	3.6
140°-150°	166.2	2.8
150°-160°	119.7	2.0
160°-170°	73.2	1.2
170°-180°	24.7	0.4
0°-30°	1901.1	31.6
0°-40°	2800.9	46.6
0°-60°	3948.6	65.7
0°-90°	4334.4	72.1
90°-120°	802.1	13.3
90°-150°	1460.9	24.3
90°-180°	1679.0	27.9
0°-180°	6013.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2974	2974	2974	2974	2974	
5°	2925	2896	2915	2922	2932	272
15°	2474	2465	2531	2600	2645	691
25°	1891	1896	1994	2081	2172	869
35°	1336	1342	1433	1529	1638	831
45°	801	816	870	936	1022	625
55°	461	480	508	527	570	418
65°	231	250	273	238	217	240
75°	116	116	106	72	50	124
85°	33	33	30	19	12	35
90°	2	5	13	7	7	3
95°	17	65	218	112	76	19
105°	60	91	367	557	520	63
115°	106	129	294	586	669	105
125°	148	166	267	452	533	131
135°	176	194	259	365	413	136
145°	204	217	256	311	335	128
155°	231	237	256	281	289	106
165°	249	252	256	266	269	70
175°	259	259	257	261	261	25
180°	259	259	259	259	259	

TEST NUMBER: P519014

CATALOG NUMBER: SQ4-WB-025U-075D-935-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2973.6	2973.6	2973.6	2973.6	2973.6
2.5°	2980.9	2954.3	2961.0	2960.8	2952.7
5°	2925.3	2895.9	2914.8	2921.6	2931.8
7.5°	2816.7	2794.5	2829.0	2854.5	2875.2
10°	2732.2	2713.0	2757.0	2794.1	2820.9
12.5°	2634.1	2618.0	2672.4	2722.3	2757.2
15°	2473.8	2464.9	2531.2	2600.1	2644.8
17.5°	2302.4	2298.0	2374.1	2454.5	2511.7
20°	2185.5	2184.2	2267.7	2351.4	2417.7
22.5°	2067.5	2070.3	2158.1	2245.1	2320.6
25°	1890.6	1895.7	1993.7	2080.6	2172.4
27.5°	1727.0	1729.3	1830.6	1922.3	2020.3
30°	1615.3	1621.7	1721.0	1815.9	1918.0
32.5°	1503.6	1511.0	1608.2	1706.4	1810.5
35°	1336.1	1342.5	1432.6	1529.0	1637.5
37.5°	1163.3	1172.0	1252.0	1343.2	1449.9
40°	1051.6	1064.4	1135.1	1221.0	1325.6
42.5°	944.1	959.9	1025.5	1107.0	1201.4
45°	801.1	816.4	870.3	936.2	1021.6
47.5°	678.0	695.6	736.9	793.6	866.6
50°	608.0	624.6	662.8	704.8	773.7
52.5°	546.4	563.0	597.1	629.4	688.1
55°	460.6	479.7	507.6	526.8	570.2
57.5°	390.1	408.5	430.6	439.3	465.5
60°	343.2	363.6	383.6	382.6	396.6
62.5°	300.4	317.7	337.7	323.9	324.6
65°	230.9	250.1	272.7	238.3	216.6
67.5°	186.6	190.7	214.0	166.2	140.4
70°	165.7	165.7	172.2	128.7	107.0
72.5°	145.9	145.9	139.9	104.6	81.9
75°	116.1	116.1	105.7	72.5	49.6
77.5°	89.5	88.5	80.9	54.1	36.0
80°	71.8	71.8	65.2	42.7	28.7
82.5°	56.1	56.1	50.6	33.4	21.4
85°	32.6	32.6	30.0	19.4	11.7
87.5°	11.8	12.5	13.1	7.6	6.5
90°	1.7	4.9	13.3	6.6	6.6
92.5°	7.0	33.6	74.4	32.9	21.2
95°	16.6	65.3	217.5	112.1	76.4
97.5°	28.9	71.7	325.4	258.8	190.6
100°	38.2	77.1	358.6	363.4	282.2
102.5°	46.2	82.5	367.9	452.6	383.1
105°	59.8	90.6	366.9	556.9	519.6
107.5°	73.7	102.3	346.0	611.1	620.2
110°	83.0	109.0	328.7	625.1	664.0

TEST NUMBER: P519014

CATALOG NUMBER: SQ4-WB-025U-075D-935-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	92.3	117.0	312.8	616.3	676.0
115°	106.2	129.0	293.8	586.2	669.0
117.5°	119.9	140.6	280.9	544.6	636.5
120°	127.8	147.3	275.6	516.7	605.9
122.5°	135.8	155.3	271.6	488.7	576.7
125°	147.7	165.6	267.3	451.7	532.9
127.5°	157.4	175.6	263.6	421.9	490.4
130°	162.7	182.2	262.3	403.2	466.5
132.5°	168.0	187.5	261.0	387.1	443.9
135°	176.0	193.8	259.0	364.7	413.4
137.5°	184.3	201.8	258.6	347.9	387.8
140°	190.9	207.1	257.3	334.5	371.9
142.5°	196.2	211.2	257.3	325.1	357.3
145°	204.2	217.2	255.7	311.0	335.3
147.5°	212.2	224.8	255.7	299.3	319.4
150°	217.5	228.8	255.7	292.5	308.8
152.5°	222.8	231.5	255.7	287.1	299.5
155°	230.8	237.2	255.7	280.7	288.9
157.5°	236.7	242.9	255.7	275.0	280.9
160°	240.7	245.6	255.7	272.3	275.6
162.5°	244.7	248.3	255.7	269.7	272.9
165°	249.0	252.3	255.7	265.7	268.9
167.5°	253.0	254.6	257.3	264.0	265.3
170°	255.7	257.3	257.3	264.0	264.0
172.5°	257.0	257.3	257.3	262.6	261.3
175°	259.0	259.0	257.3	260.6	260.6
177.5°	259.0	259.0	257.6	260.3	259.0
180°	259.0	259.0	259.0	259.0	259.0

(END OF REPORT)